

**Overview**

- 1,6 mm
- NPN break function (NC)
- flylead connector M8
- -25 ... 75 °C
- IP 67



Picture similar



**Technical data**

**General data**

Mounting type	Flush
Nominal sensing distance Sn	1.6 mm
Hysteresis	2 ... 20 % of Sr
Output indicator	LED red

**Electrical data**

Switching frequency	3 kHz
Voltage supply range +Vs	6 ... 30 VDC
Current consumption max. (no load)	12 mA
Output circuit	NPN break function (NC)
Voltage drop Vd	< 2 VDC
Output current	< 200 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

**Mechanical data**

Type	Cylindrical smooth
Material (sensing face)	LCP
Housing material	Stainless steel
Dimension	4 mm

**Mechanical data**

Housing length	25 mm
Connection types	Flylead connector M8


**Ambient conditions**

Operating temperature	-25 ... +75 °C
Protection class	IP 67

**Cable**

Head A: Connection	M8
Head A: Gender	Male
Head A: Angle cable outlet	0°
Head A: Coding	A
Head A: No. of poles	3
Head A: Degree of protection	IP65, IP66K, IP67
Cable length	200 mm
Length tolerance	+ 10 % - 0 %
Shielded	No
External sheath: Material	PUR
Cable diameter	2.8 mm
AWG	28
Wire cross section	0.09 mm <sup>2</sup>

**Dimension drawing**




**Pin assignment**



- Standard cable length 200 mm (L)

**Dimensions connector**



**Connection diagram**

