

O200.GL-PV1T.72CV/E022_F060_H006

Diffuse sensors with background suppression - miniature

Article number: 11231152

产品一览

- Outstanding reliability and unrivalled immunity against ambient light
- Line beam for complete detection of irregular, perforated objects
- Precise detection thanks to laser light source
- qTeach - tamper-proof, simple teach-in with ferromagnetic tool
- Quick mounting by means of M3 threaded bushes made of stainless steel



图片与实际产品相似



技术数据

基本参数

类型	背景抑制型
版本	线状光斑
光源	脉冲红色激光二极管
感应距离 Tw	20 ... 120 mm
感应范围 Tb	3 ... 122 mm
Smallest object recognizable typ.	8 mm at 60 mm
调节/镜头受污指示灯	闪烁输出指示灯
上电指示灯	绿色LED
输出指示灯	黄色LED
感应距离调节	qTeach
激光等级	1
焦距	60 mm
波长	680 nm
交互影响抑制	是
光束类型	线
光轴校准	< 1,5°

电气参数

响应时间 / 释放时间	≤ 2 ms
Jitter	≤ 2 ms
电源电压范围 +Vs	10 ... 30 VDC

电气参数

最大电流消耗 (无负载)	20 mA (@ 10 VDC)
典型电流消耗	10 mA (@ 24 VDC)
压降 Vd	< 2 VDC
输出功能	亮通 / 暗通 功能
输出电路	PNP 互补
输出电流	< 50 mA
短路保护	是
反极性保护	是


机械参数

宽度 / 直径	8 mm
高度 / 长度	25,1 mm
深度	15,8 mm
类型	矩形
Mechanical mounting	带M3螺纹的袖子(不锈钢)
外壳材质	塑料 (ASA、PMMA)
前端光学元件	PMMA
连接方式	电缆 · 4针 · 2 m
Cable characteristics	PVC / PVC 4 x 0,08 mm²

环境条件

防护等级	IP 67
工作温度	-20 ... +50 °C

尺寸图




激光警告


CLASS 1 LASER PRODUCT

IEC 60825-1/2014
Complies with 21 CFR 1040.10 and
1040.11 except for conformance with
IEC 60825-1 Ed. 3., as described in
Laser Notice No. 56, dated May 8, 2019


接线图



典型光束特性



感应距离示意图



Hysteresis curve

