

Overview

- Outstanding reliability and unrivalled immunity against ambient light
- Baumer PinPoint LED: Small, homogeneous light spot with sharp edges
- qTeach - tamper-proof, simple teach-in with ferromagnetic tool
- Intuitive Xpress Teach / 1-Step Teach method
- Quick mounting by means of M3 threaded bushes made of stainless steel



Picture similar



Technical data


General data		Electrical data	
Type	Background suppression	Current consumption typ.	16 mA (@ 24 VDC)
Sensing distance Tw	20 ... 120 mm	Voltage drop Vd	<2 VDC
Sensing range Tb	3 ... 132 mm	Output function	Light / dark operate
Smallest object recognizable typ.	0.25 mm at 40 mm	Output circuit	NPN complementary
Power on indication	LED green	Output current	50 mA
Alignment / soiled lens indicator	Flashing output indicator	Short circuit protection	Yes
Output indicator	LED yellow	Reverse polarity protection	Yes
Sensing distance adjustment	qTeach / 1-Step Teach-in	Mechanical data	
Suppression of reciprocal influence	Yes	Width / diameter	8 mm
Alignment optical axis	< 1,5°	Height / length	25.1 mm
Light Source		Depth	15.8 mm
Light source	Pulsed PinPoint LED	Design	Rectangular
Wave length	644 nm	Mechanical mounting	Threaded sleeves M3 (stainless steel)
Electrical data		Housing material	Plastic (ASA, PMMA)
Response time / release time	< 0.5 ms	Front (optics)	PMMA
Voltage supply range +Vs	10 ... 30 VDC	Connection types	Flylead connector M8 4 pin, L=200 mm
Current consumption max. (no load)	40 mA (@ 10 VDC)	Cable characteristics	PVC / PVC 4 x 0.08 mm ²
		Ambient conditions	
		Protection class	IP 67
		Operating temperature	-25 ... +50 °C

O200.GP-NV1T.72NV/H006_T003


Diffuse sensors with background suppression - miniature

Article number: 11212666


Dimension drawing




Connection diagram




Pin assignment



Sensing distance diagram



Hysteresis curve



Beam characteristic (typically)

