

## Overview

- 0 ... 8 mm
- voltage output
- cable, 2 m
- 40 ... 85 °C
- Protection class IP68 / IP69K



*Picture similar*



## Technical data

### General data

Mounting type	Flush
Special type	Linearized Vehicle
Measuring distance Sd	0 ... 8 mm
Sensitivity	0,5 V/mm
Resolution	< 0.008 mm (stat.) < 0.01 mm (dynam.)
Repeat accuracy	0.016 mm
Linearity error	± 120 µm
Temperature drift	± 8 % (Full Scale)
Approvals/certificates	EN 60947-5-2 / EN 60947-5-7 EN 13309:2010 EN ISO 14982:2009 ISO 13766:2006

### Electrical data

Response time (factory characteristic)	< 1 ms
Voltage supply range +Vs	4.75 ... 5.25 VDC
Current consumption max. (no load)	12 mA
Output circuit	Voltage output

### Electrical data

Output signal	0,5 ... 4,5 VDC
Load resistance	> 4500 Ohm
Short circuit protection	Yes
Off-Highway Electromagnetic immunity	ISO 11452-4: 200mA ISO 11452-2: 100V/m Based on UN / ECE R10 Rev 5 ch. 6.8 (no ECE type approval available)
Off-Highway Emission	EN 55011 Based on UN / ECE R10 Rev 5 ch. 6.5, 6.6 (no ECE type approval available)


### Mechanical data

Type	Cylindrical threaded
Housing material	Brass nickel plated
Dimension	18 mm
Housing length	50 mm
Connection types	Cable, L=2 m
Tightening torque max.	40 Nm (A: 28 Nm, B: 28 Nm)


### Ambient conditions

Operating temperature	-40 ... +85 °C
Protection class	IP 68 (sensing face/sensor) IP 68 (1,5 m, 24 h) IP 69K (sensing face)


#### Dimension drawing



#### Quasi flush mounted 1/3 Sd (typical)



#### Connection diagram



#### Flush mounted (typical)

