

Overview

- 5 ... 10 mm
- voltage output
- cable, 2 m
- 60 °C
- IP 67



Picture similar



Technical data

General data

Mounting type	Flush
Measuring distance Sd	5 ... 10 mm
Reference distance	7.1 ... 7.9 mm
Measuring speed	< 1.5 mm / ms
Repeat accuracy	0.02 mm
Linearity error	± 200 µm
Temperature coefficient	1 µm / (K mm)

Electrical data

Voltage supply range +Vs	15 ... 30 VDC
Current consumption max. (no load)	20 mA
Output circuit	Voltage output
Output signal	1 ... 9 VDC
Load resistance	> 1000 Ohm

Electrical data

Residual output ripple	< 0.5 % Vs
Short circuit protection	Yes
Reverse polarity protection	Yes

Mechanical data


Design	Cylindrical threaded
Material (sensing face)	PBT
Housing material	Brass nickel plated
Dimension	30 mm
Housing length	60 mm
Connection types	Cable, L=2 m
Tightening torque max.	200 Nm (Front: 140 Nm)

Ambient conditions

Operating temperature	0 ... +60 °C
Protection class	IP 67

IWRM 30U9501

Dimension drawing



Connection diagram

