LFFS

Point level detection based on frequency deviation technology for high-temperature hygienic applications

LFFS-###.0

Overview

- Process temperatures up to 200 °C
- Housing design with 360° status indicatorFor hygienic and industrial applications
- 3-A- and FDA-compliant, EHEDG-certified
- With ATEX, WHG and cULus approval













Technical data		
Performance characteristic	s	Ou
Measuring principle	CleverLevel level switches (Frequency Sweep)	Sw
Hysteresis	± 1 mm	
Media characteristics	DC > 1.5	
Step response time	0.1 s , typ. 0.2 s , max.	Vol
Damping	0 10 s , adjustable	
Repeatability	± 1 mm	
Process conditions		
Process temperature	Refer to section "Operating conditions"	Cui
Process pressure	Refer to section "Operating conditions"	Off
Process connection		Sho
Connection variants	Refer to section "Dimensional drawings"	Но
Mounting position	Any, top, bottom, side	Sty
Wetted parts material	PEEK Natura AISI 316L (1.4404) EPDM, optional	Ove Ma
Surface roughness wetted parts	Ra ≤ 0.8 µm	Coi
Ambient conditions		Cal
Operating temperature range	-40 85 °C	
Storage temperature range	-40 85 °C	Po
Degree of protection (EN 60529)	IP 67 , with appropriate cable	Vol
Humidity	< 98 % RH , condensing	loa
Vibration (sinusoidal) (EN 60068-2-6)	1.6 mm p-p (2 25 Hz), 4 g (25 100 Hz), 1 octave / min.	Pov
Output signal		Fac
Output type	PNP	Out
	NPN Digital (push-pull)	Sw

Output signal	
Switching logic	Normally open (NO) Normally closed (NC) Active high Active low
Voltage drop	PNP: $(+Vs -2.5 V) \pm 0.5 V$, Rload = $1 k\Omega$ NPN: $(+2.5 V) \pm 0.5 V$, Rload = $1 k\Omega$ Digital (push-pull): $(+Vs -2.5 V) \pm 0.5 V$, Rload = $1 k\Omega$ Digital (push-pull): $(+2.5 V) \pm 0.5 V$, Rload = $1 k\Omega$
Current rating	50 mA , max.
Off leak current	< 100 μA , max.
Short circuit protection	Yes
Housing	
Style	Field housing, Ø55 mm
Overall size	Refer to section "Dimensional drawings"
Material	AISI 304 (1.4301)
Electrical connection	
Connector	M12-A, 4-pin, nickel plated brass M12-A, 4-pin, stainless steel
Cable gland	M16x1.5, nickel plated brass M16x1.5, polyamid M16x1.5, stainless steel
Power supply	
Voltage supply range	12.5 36 V DC
Current consumption (no load)	35 mA , max.
Power-up time	< 2 s
Reverse polarity protection	Yes
Factory settings	
Output polarity	AUTO
Switching logic SW1	PNP

LFFS

Point level detection based on frequency deviation technology for high-temperature hygienic applica-

LFFS-###.0

Technical data			
Factory settings		ATEX II 1G Ex ia IIC T5	
Switching range (dielectric	< 75.3 % , DC > 2	Temperature class, T1 T5	-40 < Tamb < 85 °C
constant DC)		Recommended barrier	PROFSI3-B25100-ALG-LS
Trigger level	80.4 %	ATEX II 3G Ex ec IIC T5	
Range hysteresis	2.4 %	Voltage supply range	12.5 30 V DC
Damping	0.1 s	Current rating, In	100 mA
ATEX II 1D Ex tD A20 IP67 1	Г100 °C	Degree of protection for	IP 67
Voltage supply range	12.5 30 V DC	cable accessories	
Current rating, In	100 mA	Temperature class, T1 T5	-40 < Tamb < 85 °C
Degree of protection for	IP 67	Compliance and approvals	
cable accessories		EMC Emission	EN 61326, installed in a closed metal tank
Temperature class T100 °C	-40 < Tamb < 85 °C	EMC Immunity	EN 61326, installed in a closed metal tank
ATEX II 1G Ex ia IIC T5		Hygiene	Refer to section "Compliance and ap-
Voltage supply range	24 30 V DC		provals"
Maximum values for barrier selection, Ui	30 V DC , max.	Safety	cULus listed, E365692 WHG (overfill, leakage)
Maximum values for barrier selection, li	100 mA	Explosion protection	ATEX II 1D Ex tD A20 IP67 T100 °C ATEX II 1G Ex ia IIC T5
Maximum values for barrier selection, Pi	750 mW	Pharma	ATEX II 3 G Ex ec IIC T5 Refer to section "Compliance and ap-
Internal capacitance, Ci	33 nF		provals"
Internal inductance, Li	10 μH		

Operating condition	ons					
			Continuou	Continuous Temporary (t < 1 h)		
Ordering key	Process connection	BCID	Process temperature @ Tamb < 60 °C	Process pressure	Process temperature max. @ Tamb < 60 °C	Process pressure @ Process temperature max.
			(° C)	(bar)	(° C)	(bar)
LFFS-##1.#	G 1/2 A hygienic	A03	-40 115	-1 10	140	-1 5
LFFS-##2.#	BHC 3A DN 38	B01	-40 115	-1 40	140	-1 40
LFFS-##3.#	G 1/2 A hygienic, sliding connection, length 100 mm	A03	-40 150	-1 16	N/A	N/A
LFFS-##4.#	G 1/2 A hygienic, sliding connection, length 250 mm	A03	-40 200	-1 16	N/A	N/A

For further information on permissible process and ambient temperatures, please refer to the operating instructions.

LFFS

Point level detection based on frequency deviation technology for high-temperature hygienic applications

LFFS-###.0

Compliance and	approvals							
Ordering key	Process connection	BCID	EN 1935/2004 EN 10/2011 EN 2023/2006	FDA	3-A	EHEDG EL-Class I	USP Class VI	WHG (overfill, leakage)
LFFS-##1.#	G 1/2 A hygienic	A03	•	•	•	•	•	•
LFFS-##2.#	BHC 3A DN 38	B01	•	•	•	•		•
LFFS-##3.#	G 1/2 A hygienic, sliding connection, length 100 mm	A03	•	•		•		•
LFFS-##4.#	G 1/2 A hygienic, sliding connection, length 250 mm	A03	•	•		•		•

Information on product characteristics may relate to defined product options.


The requirements of the respective 3-A Sanitary Standard will be only fulfilled in combination with appropriate mounting accessories. Those are marked with the 3-A logo.

The EHEDG certification is only valid in combination with appropriate mounting accessories. Those are marked with the "EHEDG Certified" logo.

Ø 55

Dimensional drawings (mm)

Housing




28


Housing with cable gland M16x1.5

Housing with connector M12-A, 4-pin


Process connection



G 1/2 A hygienic (BCID: A03)



BHC 3A DN 38, including O-ring ZPX2-123 (BCID: B01)



G 1/2 A hygienic, sliding connection, 100 mm adjustable, including compression ring kit ZPX1-006 (BCID: A03)


LFFS

Point level detection based on frequency deviation technology for high-temperature hygienic applications

LFFS-###.0

Dimensional drawings (mm)

Process connection



G 1/2 A hygienic, sliding connection, 250 mm adjustable, including compression ring kit ZPX1-006 (BCID: A03)

LFFS

Point level detection based on frequency deviation technology for high-temperature hygienic applications

LFFS-###.0

ectrical connection Output type	Electrical connection	Equivalent circuit	Function	Pin assignment
	4 3		+Vs	1
	(• •)	+Vs	SW1	4
	1 2	Ŭ ſ	Teach-in	2
PNP		SW1 (NO) —	GND (0 V)	3
Iormally open (NO)	5 4 (A) (A)	o3W1 (NO)		
			+Vs	1
	6 (C) (C) (C) 3	GND (0 V)	SW1	5
			Teach-in	4
			GND (0 V)	2
	4 3		+Vs	1
	(• •)	+Vs	SW1	4
	1 2		Teach-in	2
NPN	PN - J	<u> </u>	GND (0 V)	3
ormally open (NO)	100 601	SW1 (NO)		
			+Vs	1
	6 (O) () 3	GND (0 V)	SW1	5
	2 3 2		Teach-in	4
			GND (0 V)	2
	4 3		+Vs	3
	(••)	+Vs	SW1	4
	1 2		Teach-in	2
Digital (push-pull)	5 4 (ALI)	SW1 (AH)	GND (0 V)	1
Active high	\$ 4 \$ \$ \$ \$	SWI (AH)		
		ΠÍ	+Vs	2
	6 (O) () 3	GND (0 V)	SW1	5
	2 1	0 ,	Teach-in	4
			GND (0 V)	1

LFFS

Point level detection based on frequency deviation technology for high-temperature hygienic applications

LFFS-###.0

Output type	Electrical connection	Equivalent circuit	Function	Pin assignment
	4 3		+Vs	3
		• • · · · · · · · · · · · · · · · · · ·	SW1	4
	(• •)		Teach-in	2
PNP			GND (0 V)	1
Normally closed (NC)	5 4	SW1 (NC)	CIVE (0 V)	<u> </u>
			+Vs	2
	6 (C) (C) (C) 3	GND (0 V)	SW1	5
	2 3		Teach-in	4
			GND (0 V)	1
	4 3		+Vs	3
		o ^{+Vs}	SW1	4
	1 2	<u> </u>	Teach-in	2
NPN	E 4	SW1 (NC) —	GND (0 V)	1
Normally closed (NC)				
			+Vs	2
	6 (() () () 3	GND (0 V)	SW1	5
	2 3 4 1	_	Teach-in	4
			GND (0 V)	1
	4 3		+Vs	1
	$(\bullet \ \bullet)$	+Vs	SW1	4
	1 2		Teach-in	2
Digital (push-pull)	E 4		GND (0 V)	3
Active low		SW1 (AL)		
		<u> </u>	+Vs	1
	6 (O) (3	GND (0 V)	SW1	5
	2 3 1	0 3.12 (8 4)	Teach-in	4
	- \		GND (0 V)	2

Ordering information Ordering key - Configuration possibilities see website

	LFFS	- #	#	# .
Product				
	LFFS			
Compliance and approvals				
Standard		0		
ATEX II 1G Ex ia IIC T5 Ga		1		
ATEX II 1D Ex tD A20 IP67 T100 °C		2		
ATEX II 3G Ex ec IIC T5		3		
UL listed, E365692		Α		
EAC (TR CU 020/2011)		В		
Electrical Connection				
M12-A, 4-pin, nickel plated brass			1	
Cable gland, M16x1.5, nickel plated brass			2	
Cable gland, M16x1.5, polyamid			3	
M12-A, 4-pin, stainless steel			4	
Cable gland, M16x1.5, stainless steel			5	



LFFS

Point level detection based on frequency deviation technology for high-temperature hygienic applications

LFFS-###.0

Ordering information			
Ordering key - Configuration possibilities see website			
	LFFS - #	# # .	. #
Process Connection			
G 1/2 A hygienic, PEEK-tip (A03)		1	
BHC 3A DN 38, PEEK-tip (B01) ⁽¹⁾		2	
G 1/2 A hygienic, PEEK-tip (A03), sliding connection, 100 mm adjustable, incl. Compression ring kit ZPX1-006		3	
G 1/2 A hygienic, PEEK-tip (A03), sliding connection, 250 mm adjustable, incl. Compression ring kit ZPX1-006		4	
Configuration			
Factory settings			0
Customer-specific			С

(1) Including O-ring ZPX2-123