

# LXC-250C

Camera Link®, 25 Megapixel, Color

Article number: 11162827

## Overview

- 5120 × 5120 px
- Onsemi PYTHON 25K
- APS-H CMOS
- 32 fps
- Camera Link® Full



GEN*i*CAM



## Technical data

### Sensor information

Sensor	onsemi PYTHON 25K
Mono/Color	Color
Color filter	RGB Bayer Mosaic
Sensor type	APS-H CMOS
Shutter type	Global shutter
Resolution	5120 × 5120 px
Pixel size	4.5 × 4.5 μm
Exposure time	0.03 ... 1000 ms

### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 5120 × 5120 px, max. 32 fps
Pixel formats	BayerGB8 BayerGB10

### Image preprocessing

Analog controls	Gain (0 ... 23,5 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Raw Bayer
Color processing	NA

### Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

### Camera features

Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	1 output line
Internal image buffer	512 MB

### Interfaces and connectors

Data interface	Camera Link Full, connector: 2 x Standard SDR26 (Mini CL)
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

### Mechanical data

Lens mount	M58-mount (F-mount, M42, C-mount via adapter)
Width	60 mm
Height	60 mm
Depth	45.12 mm
Weight	≤ 235 g (M58-mount)
Material	housing: aluminum

### Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 38 ... 57 V (PoCL)
--------------------------	--

# LXC-250C

Camera Link®, 25 Megapixel, Color

Article number: 11162827

## Technical data

### Electrical data

Power consumption approx. 7,8 W @ 24 VDC  
approx. 7,8 W @ 12 VDC (PoCL)

### Non-volatile memory

Flash memory size 128 kB

### Environmental conditions

Operating temperature +5 ... +66 °C @ T = measurement point

### Environmental conditions

Humidity 10 ... 90 % (non-condensing)

Protection class IP 40

### Conformity

Conformity CE  
RoHS  
EAC

## Dimension drawing

