

产品一览

- 200 ... 1000 mm
- 脉冲红色激光二极管
- 自学习: 按键 / 外部
- 电缆 · 8针 · 2 m
- 20 ... 60 °C
- IP 67



图片与实际产品相似



技术数据

基本参数

测量距离 Sd	200 ... 1000 mm
调节	自学习: 按键 / 外部
最小自学习范围	> 20 mm
上电指示灯	绿色LED
镜头受污指示灯	红色LED
分辨率	120 ... 3000 µm
线性误差	± 0,36 ... 9 mm
光束类型	线
光束宽度	3 ... 1 mm
光束高度	8 ... 25 mm
温漂	< 0,04 % Sde/K

光源

光源	脉冲红色激光二极管
波长	650 nm
激光等级	2

电气参数

响应时间 / 释放时间	< 3,5 ms
电源电压范围 +Vs	12 ... 28 VDC
最大电流消耗 (无负载)	100 mA
输出信号	4 ... 20 mA / 0 ... 10 VDC
负载电阻 (Analog I)	< (+Vs - 6 V) / 0,02 A

电气参数

负载电阻 (Analog U)	> 100 kOhm
输出电流	< 100 mA
报警输出	PNP
反极性保护	是, Vs到 GND


机械参数

宽度 / 直径	20,6 mm
高度 / 长度	65 mm
深度	50 mm
类型	矩形
外壳材质	压铸锌
前端光学元件	玻璃
连接方式	电缆 · 8针 · 2 m


环境条件

抗环境光干扰能力	< 60 kLux
工作温度	-20 ... +60 °C
防护等级	IP 67
正弦振动	IEC 60068-2-6:2008 30 g at f = 10 - 2000 Hz, cycles per axis
半正弦振动	IEC 60068-2-29:2009 75 g / 6 ms, 4000 jolts per axis and direction


尺寸图




接线图



线性误差



典型光束特性




激光警告



LASER RADIATION
DO NOT STARE INTO BEAM
Wavelength: 640...670nm
IEC 60825-1, Ed. 3, 2014
CLASS 2 LASER PRODUCT

IEC 60825-1/2014 Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019

分辨率



激光线校准

