

LXG-200C

Dual GigE, 20 Megapixel, Color

Article number: 11117849

Overview

- 5120 × 3840 px
- ams (CMOSIS) CMV20000
- 35 mm CMOS
- 12 fps
- Dual Gigabit Ethernet
- available



GEN<i>i>CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV20000
Resolution	5120 × 3840 px
Exposure time	0,1 ... 1000 ms
Color filter	RGB Bayer Mosaic
Pixel size	6.4 × 6.4 μm
Shutter type	Global shutter
Sensor type	35 mm CMOS

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 5120 × 3840 px, max. 12 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 5120 × 3840 px, max. 32 fps
Pixel formats	BayerGB8 BayerGB12 BayerGB12 Packed

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Raw Bayer

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

Camera features

Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB

Interfaces and connectors

Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mbits/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

Mechanical data

Lens mount	M58-mount (F-mount, M42, C-mount via adapter)
Width	60 mm
Height	60 mm
Depth	54,25 mm
Weight	≤ 290 g (M58-mount)
Material	housing: aluminum

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
--------------------------	--

LXG-200C

Dual GigE, 20 Megapixel, Color

Article number: 11117849

Technical data

Electrical data

Power consumption approx. 7,2 W @ 24 VDC
approx. 6,0 W @ 48 VDC (PoE)

Non-volatile memory

Flash memory size 128 kB

Environmental conditions

Operating temperature +5 ... +65 °C @ T = measurement point
Humidity 10 ... 90 % (non-condensing)

Environmental conditions

Protection class IP 40

Conformity

Conformity CE
RoHS
KC (MSIP-REI-BkR-LXG-200M)
EAC

Dimension drawing

