

LXG-20C

Dual GigE, 2 Megapixel, Color

Article number: 11137904

Overview

- 2048 × 1088 px
- ams (CMOSIS) CMV2000 V3
- 2/3" CMOS
- 111 fps
- Dual Gigabit Ethernet



Picture similar



GEN*i*CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV2000 V3
Mono/Color	Color
Sensor type	2/3" CMOS
Shutter type	Global shutter
Resolution	2048 × 1088 px
Pixel size	5.5 × 5.5 µm
Exposure time	0.03 ... 1000 ms

Data quality (EMVA 1288 typical)

Dark noise	14.4 e-
Saturation capacity	9848 e-
Dynamic range	56.3 dB
Signal-to-noise ratio	39.9 dB
Quantum efficiency	39.1 % @ 465 nm 40.8 % @ 536 nm 39.4 % @ 631 nm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2048 × 1088 px, max. 111 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2048 × 1088 px, max. 337 fps
Pixel formats	BayerGB8 BayerGB10 BayerGB10 Packed

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Raw Bayer
Color processing	NA

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB

Interfaces and connectors

Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mbits/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins

LXG-20C

Dual GigE, 2 Megapixel, Color

Article number: 11137904

Technical data

Interfaces and connectors

Power supply via M8 / 8 pins

Mechanical data

Lens mount C-mount

Width 60 mm

Height 60 mm

Depth 52.4 mm

Weight ≤ 340 g

Material housing: aluminum

Electrical data

Voltage supply range +Vs 12 ... 24 V DC (external power supply)
36 ... 57 V DC (Power over Ethernet)

Power consumption Approx. 6.2 W @ 24 VDC
Approx. 5.2 W @ 48 VDC (PoE)

Non-volatile memory

Flash memory size 128 kB

Environmental conditions

Operating temperature +5 ... +64 °C @ T = measurement point

Humidity 10 ... 90 % (non-condensing)

Protection class IP 40

Conformity

Conformity CE
RoHS
EAC

Dimension drawing

