

## LXG-80M

Dual GigE, 8 Megapixel, Monochrome

Article number: 11125117

### Overview

- 3360 × 2496 px
- ams (CMOSIS) CMV8000
- 4/3" CMOS
- 29 fps
- Dual Gigabit Ethernet



GEN<i>i>CAM



### Technical data

#### Sensor information

Sensor	ams (CMOSIS) CMV8000
Mono/Color	Mono
Sensor type	4/3" CMOS
Shutter type	Global shutter
Resolution	3360 × 2496 px
Pixel size	5.5 × 5.5 µm
Exposure time	0.04 ... 1000 ms

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 3360 × 2496 px, max. 29 fps Binning 2×2, 1680 × 1248 px, max. 29 fps Binning 1×2, 3360 × 1248 px, max. 29 fps Binning 2×1, 1680 × 2496 px, max. 29 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 3360 × 2496 px, max. 61 fps
Pixel formats	Mono8 Mono12 Mono12 Packed

#### Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono

#### Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand

#### Camera features

Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB

#### Interfaces and connectors

Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mb/s/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

#### Mechanical data

Lens mount	M58-mount (F-mount, M42, C-mount via adapter)
Width	60 mm
Height	60 mm
Depth	54.25 mm
Weight	≤ 290 g (M58-mount)
Material	housing: aluminum

## LXG-80M

Dual GigE, 8 Megapixel, Monochrome

Article number: 11125117

### Technical data

#### Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	approx. 7,2 W @ 24 VDC approx. 7,2 W @ 48 VDC (PoE)

#### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

#### Environmental conditions

Operating temperature	+5 ... +66 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

#### Conformity

Conformity	CE RoHS EAC BIS-CRS (R-41207004)
------------	---

### Dimension drawing

