



中国船级社
CHINA CLASSIFICATION SOCIETY

证书编号/Certificate No.
GB23PTB00015

型式认可证书
CERTIFICATE OF TYPE APPROVAL

兹证明本证书所述制造厂具备按照下列标准的要求生产本证书所列产品的能力和条件。

This is to certify that the manufacturer stated in the certificate meets the requirements of the standards listed below and is available with the ability and conditions to produce the products described in the certificate.

制造厂/Manufacturer

Baumer A/S

地址/Address

Runetoften 19, 8210 Aarhus V Denmark

产品名称/Product

液位开关
Level Switch
传感器
Sensor

附加标志/Notations

无/Nil.

认可标准/Approval Standard

1. 中国船级社《钢质海船入级规范》(2023)及其变更通告第7篇第2章
Chapter 2, Part Seven of China Classification Society Rules for Classification of Sea-going Steel Ships 2023 and its Change Notices

用于/Intended for

船舶/Ships



证书有效期至/This Certificate is valid until 2027年03月08日/Mar. 08,2027

发证机构/Issued by 中国船级社哥本哈根办事处
CCS Copenhagen Office

签发日期/Date 2023年09月15日
Sep. 15,2023

本证书根据中国船级社规范和相关规定签发。所有证书页为一个整体，必须同时使用。纸质证书每页均须由本社盖章方为有效，电子证书含数字签名方为有效，本证书复印件无效。任何单位和个人不应摘录或节选本证书的部分内容。有关方对所持证书的真实性有疑问时，可以向本社检验机构咨询。This Certificate is issued pursuant to the Rules of the Society and related regulation. All pages of the certificate are taken as a whole and are used simultaneously. No paper certificate page is valid without bearing the stamp of the Society, no electronic certificates is valid without the digital signature, and no copied form of the certificate is regarded as valid. Any part of the certificate is not to be extracted or abridged by any unit or individual in any form. Related parties who are doubted about the authenticity of the certificate may inquire of the Society or its offices.



Form No: T01.

联系方式/Contact Us, 见本社官方网站/See official web site of the Society (<http://www.ccs.org.cn>)

UTN:P023-26182150

产品明细/Product Description**传感器/Sensor (M0001)**

名称/Name	属性(值)/Value	单位/Unit
产品名称/Product Name	液位开关 Level Swith	
型号/Type	LBFS	
电源/Power Source	12~30	VDC
输出信号/Output Signal	max. 20	mA
外壳防护等级/Degree of Protection of Enclosure	IP 67 (Standard: EN 60529/IEC 60529) IP 69K (Standard: ISO 20653:2013)	

批准的图纸/Approved Drawings

图纸批准号/ Drawings Approval No. : HB19PPP20017

产品认可试验报告/ Approval Test Report

试验报告编号/ Test Report No. : Baumer no. 5505-109 Rev. A1
试验报告日期/ Test Report Date : 2011-10-18

试验报告编号/ Test Report No. : Baumer no. 5505-113 Rev. A1
试验报告日期/ Test Report Date : 2011-10-18

试验报告编号/ Test Report No. : Baumer no. 5505-137 Rev. A1
试验报告日期/ Test Report Date : 2012-02-08

试验报告编号/ Test Report No. : DELTA no. DANAK-1911536
试验报告日期/ Test Report Date : 2011-08-23

试验报告编号/ Test Report No. : Baumer no. 5505-080 Rev. B1
试验报告日期/ Test Report Date : 2010-08-20

试验报告编号/ Test Report No. : Baumer no. 5505-110 Rev. A1
试验报告日期/ Test Report Date : 2011-10-18

试验报告编号/ Test Report No. : Baumer no. 5505-091 Rev. 04
试验报告日期/ Test Report Date : 2013-10-24

试验报告编号/ Test Report No. : 81258746
试验报告日期/ Test Report Date : 2017-08-28

试验报告编号/ Test Report No. : DELTA no. DANAK-1911537
试验报告日期/ Test Report Date : 2011-08-23

试验报告编号/ Test Report No. : Baumer no. 5505-114 Rev. A1
试验报告日期/ Test Report Date : 2011-10-18

试验报告编号/ Test Report No. : Baumer no. 5505-111 Rev. A1
试验报告日期/ Test Report Date : 2011-10-21

试验报告编号/ Test Report No. : Baumer no. 5505-112 Rev. A1
试验报告日期/ Test Report Date : 2011-10-21

试验报告编号/ Test Report No. : DELTA no. DANAK-1911632
试验报告日期/ Test Report Date : 2011-10-24

试验报告编号/ Test Report No. : GOM-2106-9844-EE01MAR-V01
试验报告日期/ Test Report Date : 2021-07-22
试验单位/ Laboratory: Eurofins Product Service GmbH
试验单位地址/ Test Address:

试验报告编号/ Test Report No. : 0153968
试验报告日期/ Test Report Date : 2021-05-29
试验单位/ Laboratory: RISE Research Institutes of Sweden AB

试验单位地址/ Test Address:

试验报告编号/ Test Report No. : P21-0071-1 rev. 1
试验报告日期/ Test Report Date : 2021-07-09
试验单位/ Laboratory: EKTOS Testing & Reliability Services A/S
试验单位地址/ Test Address:

试验报告编号/ Test Report No. : 9.10P-13624
试验报告日期/ Test Report Date : 2021-08-19
试验单位/ Laboratory: FORCE Technology
试验单位地址/ Test Address:

认可后的产品检验方式/ Method of Product Inspection after Approval

按照规范只认可不进行产品检验的产品/The product approved only in term of the rules:
认可后的产品检验由制造厂按本社批准的产品检验计划进行检验, 经检验合格后由制造厂签发合格证明, 并连同该产品的本社认可证书复印件一并交付用户, 制造厂对产品符合公约、法规、本社规范和本社认可的标准规定负责。
After approval, product inspection should be carried out by the Manufacturer in accordance with the product inspection scheme approved by the Society. Upon satisfactory inspection, and the Quality Certificate issued by the Manufacturer should be provided to the purchaser together with the copy of the approval certificate issued by the Society. The manufacturer should take responsibility for the product being in compliance with the convention, statutory regulation, the Society rules and the standard accepted by the Society.

认可保持条件/ Maintenance Requirements of Approval

1. 型式认可后, 如果产品及其重要零部件的设计、所用材料或制造方法有所改变, 且影响到产品的主要特性、特征; 或产品的性能指标有所更改, 且超过认可的范围, 则有关图纸和文件应经检验机构审批。并在检验机构认为必要时, 经本社检验人员见证有关试验和进行检查, 其结果应能证实仍符合认可条件。

After type approval, if there are changes to the design, materials used or manufacturing method of the product and important components and such changes affect major characteristics and properties of the product, or property indexes of the product are changed and exceed the scope of approval, related drawings and documents are to be examined and approved by the concerned survey office. Where deemed necessary by the survey office, the surveyor to the Society will go to witness relevant tests and conduct inspection and the results should be able to demonstrate compliance with the approval conditions.

2. 工厂的质量管理体系应保持有效运行, 并且与认可时一致。如果质量管理体系发生改变, 应经原体系认证机构审核并报本社批准。

The quality management system of the factory shall be ensure effective operation, and shall be the same as the situation of approval. If there are any changes to the quality management system, auditing of the original certification organization for quality management system and the society's approval shall be obtained.

3. 认可证书有效期内, 如果出现可能导致本社取消认可的情况, 工厂应及时采取有效的纠正措施。

Within the validity of the approval certificate, if cases occur that may cause the Society to withdraw the approval, the manufacturer should take corrective actions in a prompt and effective manner.

4. 在认可证书有效期内, 本社检验人员可在未经事先通知的情况下对工厂的产品制造过程进行审核, 以验证产品的生产是否符合业经本社批准的图纸和文件。工厂应予以配合。

Within the validity of the approval certificate, the surveyor to the Society may pay unannounced audit to the manufacturing process of the product in order to confirm whether it is in compliance with the drawings and documents approved by the Society. The factory should provide an active cooperation and necessary for the surveyor.

5. 如果属于获得型式认可B 模式证书, 且无需颁发船用产品证书/等效证明文件的情况, 证书获得者应接受本社每年一次的定期审核, 定期审核日为认可证书期满之日对应的每一周年日, 检查工作可在周年日的前后三个月内进行。

If belong to the situation of the product has type approval mode B certificate, and marine product certificate/equivalent document is not necessary, those who have obtained the certificate should be subject to periodical audit every year. The periodical audit should be carried out within 3 months before and after the anniversary date which corresponds to the date of expiry of the relevant.

备注/Remarks

1. 本社已审核了产品厂无石棉声明, 但本社的审核不免除产品厂按照合同关系向订货方保证产品无石棉的责任。The declaration of asbestos-free submitted by manufacturer has been reviewed by the Society. However, liability of the manufacturer to guarantee the products are asbestos-free to purchaser under contract will not be exempted.

2. 本证书由原型式认可证书 (No. GB19PTB00010) 换新并替代原证书。

This certificate is renewed from and supersedes the previous Type Approval Certificate No. GB19PTB00010.

3. 本认可产品的防爆性能参数基于制造厂提交的防爆合格证 (签发机构: TUV NORD CERT GmbH, 证书号: IECEX TUN 21.0011X/TUV 11 ATEX 076877X, 防爆标准: Directive 2014/34/EU), 非中国船级社认可。

The Ex-Proof parameters of the approved/inspected products originate from Ex- Certificate received from manufacturer (Issuing Body: TUV NORD CERT GmbH, Ex- Certificate No.: IECEX TUN 21.0011X/TUV 11 ATEX 076877X, Standards for Ex-Proof: Directive 2014/34/EU), not approved/inspected by CCS.

4. 本认可产品应持有有效的防爆合格证, 否则本证书将自动失效。

This Type Approval Certification will be invalid if the approved products do not hold valid Ex-Certificate.

5. The products comply with the test requirements of IACS UR E10 Rev8.

中国船级社哥德堡办事处

CCS Gothenburg Office

注: 本证书含有附页, 共1页

Note: The certificate is attached with additional 1 page(s)

Baumer Level Switch model LBFS, including the following variants:

	LBFS	-	#	#	#	#	#	#
Product	LBFS							
Level switches								
Compliance and approvals								
Standard				0				
ATEX II 1G Ex ia IIC T5 Ga				1				
ATEX II 1D Ex ta IIIC T100 °C				2				
ATEX II 3G Ex ec IIC T5				3				
ATEX II 1G Ex ia IIC T5/T4 Ga/ATEX II 1D Ex ta IIIC T100°C Da				4				
cUL listed, E365692				A				
Electrical Connection								
M12-A, 4-pin, polycarbonate (with LED)					1			
Cable outlet 5 m, 4-wire, PVC					2			
M12-A, 4-pin, stainless steel (without LED)					3			
Process Connection								
G 1/2 A ISO 228-1 (G07)							1	
G 3/4 A ISO 228-1 (G10)							2	
G 1 A ISO 228-1 (G11)							3	
G 1/2 A hygienic (A03)							4	
G 1/2 A ISO 228-1 for reverse assembly (in-shell thread) (T10)							5	
3/4-14 NPT (N03)							6	
M18x1 (M11)							7	
G 1/2 A DIN 3852 form E, NBR gasket (G51)							A	
G 1/2 A DIN 3852 form E, FKM gasket (G51)							B	
G 1/2 A ISO 228-1 with cooling neck (G07)							G	
G 1/2 A hygienic gasket, FKM, with cooling neck (A03)							J	
G 1/2 A hygienic, length 82 mm (A03)							K	
G 1/2 A hygienic, sliding connection, length 250 mm (A03)							L	
1/2-14 NPT (N02)							N	
1/2-14 NPT with cooling neck (N02)							M	
G 1/2 A DIN 3852 form E, FKM gasket, with cooling neck (G51)							E	
G 1/2 A hygienic gasket, VMQ70, with cooling neck (A03)							S	
Process connection material								
Stainless Steel 1.4301 - AISI 304								1
Stainless Steel 1.4404 - AISI 316L								2
Output Configuration								
PNP output								1
NPN output								2
Configuration								
Factory settings								0
Customer-specific								C

(1) Process connection "5": Including gasket ZPX3-14B0 (glass/aramide fiber with NBR)

(2) Process connection "7": Including the two M18 nut