

# MHAP 200

Absolute encoder / Singleturn 8...17 Bit / Magnetic sensing / Through hollow shaft max.  $\varnothing$ 180 mm  
 Additional 1...262144 pulses or 1...16384 sinewave cycles per turn

## Overview

- Absolute encoder with magnetic sensing and without bearings
- Sensor head with integrated FPGA signal processing
- Absolute resolution max. 17 bit singleturn
- Additional incremental output
- Robust and wearless
- Electronics is fully encapsulated
- High protection
- Large tolerances: axial  $\pm 1$  mm, radial max. 0.5 mm
- Simple mounting, easy adaptation
- Several mounting possibilities
- Magnetic rotor included in delivery



## Technical data

### Technical data - electrical ratings

Voltage supply	4.5...30 VDC
Consumption w/o load	$\leq 300$ mA
Sensing method	Magnetic
Interference immunity	EN 61000-6-2
Emitted interference	EN 61000-6-3
Approval	CE UL approval / E217823

### Technical data - electrical ratings (square-wave)

Pulses per revolution	1 ... 262144
Phase shift	$90^\circ \pm 10^\circ$
Duty cycle	40...60 %
Output frequency	$\leq 2$ MHz
Output signals	A+, A-, B+, B-
Output stages	HTL TTL/RS422

### Technical data - electrical ratings (SinCos)

Sinewave cycles per revolution	1 ... 16384
Phase shift	$90^\circ \pm 5^\circ$
Output signals	A+, A-, B+, B-
Output stages	SinCos 1 Vpp
Difference of SinCos amplitude	$\leq 20$ mV
Harmonics typ.	-40 dB
DC offset	$\leq 20$ mV
Bandwidth	400 kHz (-3 dB)

### Technical data - electrical ratings (SSI)

Interface	SSI
Steps per revolution	$\leq 131072 / 17$ bit
Code	Gray or binary
Code sequence	CW default
Additional outputs	Square-wave TTL (RS422) Square-wave universal HTL/TTL SinCos


### Technical data - mechanical design

Sensor head	FPGA signal processing
Size (flange)	$\varnothing 203.1$ mm
Shaft type	$\varnothing 50...180$ mm (through hollow shaft)
Axial tolerance	$\pm 1$ mm (wheel/head)
Radial tolerance	0.1...0.5 mm (wheel/head)
Protection EN 60529	IP 67
Operating speed	$\leq 4000$ rpm
Material	Housing sensing head: aluminium alloy Wheel: stainless steel (1.4104)
Operating temperature	-20...+85 °C
Resistance	IEC 60068-2-6 Vibration 30 g, 55-2000 Hz IEC 60068-2-27 Shock 300 g, 2 ms
Accuracy of magnetic measure	$\pm 200$ "
Connection	Flange connector M23, 17-pin

# MHAP 200

Absolute encoder / Singleturn 8...17 Bit / Magnetic sensing / Through hollow shaft max.  $\varnothing$ 180 mm  
Additional 1...262144 pulses or 1...16384 sinewave cycles per turn

## Terminal assignment



Flange connector M23,  
male, 17-pin,  
clockwise (CW)

Pin	Assignment
1	dnu
2	dnu
3	dnu
4	dnu
5	dnu
6	dnu
7	+UB
8	SSI Clk+
9	SSI Clk-
10	0V ( $\perp$ )
11	Internal shield
12	dnu (B+ *)
13	dnu (B- *)
14	SSI Data+
15	dnu (A+ *)
16	dnu (A- *)
17	SSI Data-

\* With additional output incremental


## Terminal significance

+UB	Voltage supply
0V ( $\perp$ )	Ground
SSI Data+	SSI data+
SSI Data-	SSI data-
SSI Clk+	SSI clock+
SSI Clk-	SSI clock-
A+	Additional output output signal channel 1
A-	Additional output output signal channel 1 inverted
B+	Additional output output signal channel 2 (offset by 90° to channel 1)
B-	Additional output output signal channel 2 inverted
dnu	Do not use

## Output signals


### Additional output HTL/TTL

At positive rotating direction (see dimension)




### Additional output SinCos

At positive rotating direction (see dimension)




## Data transfer

### Without parity bit



### With parity bit



T = 0.5...10  $\mu$ s



Tm = 15  $\mu$ s

Clock frequency  $\leq$  2 MHz

# MHAP 200

Absolute encoder / Singleturn 8...17 Bit / Magnetic sensing / Through hollow shaft max.  $\varnothing 180$  mm  
Additional 1...262144 pulses or 1...16384 sinewave cycles per turn


## Dimensions



# MHAP 200

Absolute encoder / Singleturn 8...17 Bit / Magnetic sensing / Through hollow shaft max.  $\varnothing 180$  mm  
Additional 1...262144 pulses or 1...16384 sinewave cycles per turn

## Dimensions



# MHAP 200

 Absolute encoder / Singleturn 8...17 Bit / Magnetic sensing / Through hollow shaft max. ø180 mm  
 Additional 1...262144 pulses or 1...16384 sinewave cycles per turn

**Ordering reference**

	MHAP200	B	5	####	S	#	##	#	#	#####	D
<b>Product</b>	MHAP200										
Encoder without bearings - absolute	MHAP200										
<b>Bandaging</b>											
Encoder wheel standard bandage		B									
<b>Pole width</b>											
1 pole = 5 mm			5								
<b>Mounting type / hollow shaft (ø mm)<sup>(2)</sup></b>											
Screw or shrink fit mounting / ø90 mm					G90						
Screw or shrink fit mounting / ø130 mm					G130						
Screw or shrink fit mounting / ø180 mm					G180						
Clamping set mounting / ø70 mm					Z70						
Clamping set mounting / ø100 mm					Z100						
Clamping set mounting / ø150 mm					Z150						
Clamping ring mounting / ø110 mm					K110						
Clamping ring mounting / ø150 mm					K150						
<b>Absolute share</b>											
SSI					S						
<b>Code</b>											
Binary code						B					
Gray code						G					
<b>Resolution Singleturn (bit)<sup>(2)</sup></b>											
13								13			
17								17			
<b>Parity bit</b>											
Odd									O		
Even									E		
None									N		
<b>Voltage supply / output stage (incremental output)</b>											
4.5...30 VDC / SinCos										P	
4.5...30 VDC / TTL										R	
5...30 VDC / 5 VDC = TTL, 10...30 VDC = HTL universal										U	
Without additional output signals										Z	
<b>Pulse number/sinewave cycles (incremental output)<sup>(2)</sup></b>											
Without additional output signals											0
128											128
256											256
512											512
1024											1024
2048											2048
4096											4096
8192											8192
16384											16384
32768 <sup>(1)</sup>											32768
262144 <sup>(1)</sup>											262144
<b>Connection</b>											
1x flange connector M23, tangential 17-pin, male, CW											D

(1) No SinCos output possible

(2) Other versions on request.