


## POG 9 G

Twin encoder with two electrically separated systems

Solid shaft with EURO flange B10 300...5000 pulses per revolution

### Overview

- Twin encoder featuring two separate systems
- TTL output driver for cable length up to 550 m
- Very high resistance to shock
- EURO flange B10 / solid shaft  $\varnothing 11$  mm



### Technical data

#### Technical data - electrical ratings

Voltage supply	9...30 VDC 5 VDC $\pm 5$ %
Consumption w/o load	$\leq 100$ mA
Pulses per revolution	300 ... 5000
Phase shift	$90^\circ \pm 20^\circ$
Duty cycle	40...60 %
Reference signal	Zero pulse, width $90^\circ$
Output frequency	$\leq 120$ kHz $\leq 300$ kHz (on request)
Output signals	K1, K2, K0 + inverted Error output (option EMS)
Output stages	HTL-P (power linedriver) TTL/RS422
Sensing method	Optical
Interference immunity	EN 61000-6-2
Emitted interference	EN 61000-6-3
Approval	CE UL approval / E217823

#### Technical data - mechanical design

Size (flange)	$\varnothing 115$ mm
Shaft type	$\varnothing 11$ mm solid shaft

#### Technical data - mechanical design

Admitted shaft load	$\leq 250$ N axial $\leq 350$ N radial
Flange	EURO flange B10
Protection EN 60529	IP 56
Operating speed	$\leq 12000$ rpm (mechanical)
Operating torque typ.	2 Ncm
Rotor moment of inertia	200 gcm <sup>2</sup>
Material	Housing: aluminium die-cast Shaft: stainless steel
Operating temperature	-30...+100 °C -25...+100 °C (>3072 pulses)
Resistance	IEC 60068-2-6 Vibration 10 g, 10-2000 Hz IEC 60068-2-27 Shock 300 g, 1 ms
Corrosion protection	IEC 60068-2-52 Salt mist for ambient conditions C4 according to ISO 12944-2
Explosion protection	II 3 G Ex ec IIC T4 Gc (gas) II 3 D Ex tc IIIB T135°C Dc (dust) (only with option ATEX)
Connection	2x terminal box
Weight approx.	2 kg

### Optional

- Function control with EMS (Enhanced Monitoring System)

## POG 9 G


Twin encoder with two electrically separated systems

Solid shaft with EURO flange B10 300...5000 pulses per revolution

### Terminal assignment


#### View A (see dimension)

Connecting terminal terminal box



#### Option EMS: View A (see dimension)

Connecting terminal terminal box




### Terminal significance

+UB	Voltage supply
0V (⊥)	Ground
⊥	Earth ground (housing)
K1	Output signal channel 1
K1	Output signal channel 1 inverted
K2	Output signal channel 2 (offset by 90° to channel 1)
K2	Output signal channel 2 inverted
K0	Zero pulse (reference signal)
K0	Zero pulse inverted
Err	Error output (option EMS)

### Output signals

#### HTL/TTL

At positive rotating direction (see dimension)



### Option EMS: Status LED / error output

Flash light red*	Error of signal sequence, zero pulse or pulses (Error output = HIGH-LOW alternation)
Red	Overload output transistors (Error output = LOW)
Flash light green	Device o.k., rotating (Error output = HIGH)
Green	Device o.k., stopped (Error output = HIGH)
No light	No voltage supply connection or wrong connection (Error output = LOW)


\* Only at rotating device

## POG 9 G

Twin encoder with two electrically separated systems

Solid shaft with EURO flange B10 300...5000 pulses per revolution

### Dimensions



## POG 9 G

Twin encoder with two electrically separated systems

Solid shaft with EURO flange B10 300...5000 pulses per revolution

### Ordering reference

	POG9	##	G	DN	####	###	/	DN	####	###
<b>Product</b>										
Twin encoder	POG9									
<b>EMS - Enhanced Monitoring System</b>										
Without EMS										
With EMS		.2								
<b>Redundant encoder</b>										
With redundant encoder			G							
<b>Output signals</b>										
K1, K2, K0				DN						
<b>Pulse number<sup>(1)</sup></b>										
300					300					
500					500					
512					512					
1000					1000					
1024					1024					
1200					1200					
2048					2048					
2500					2500					
3072					3072					
4096					4096					
5000					5000					
<b>Voltage supply / output stage</b>										
9...30 VDC / output stage HTL with inverted signals						I				
5 VDC / output stage TTL with inverted signals						TTL				
9...30 VDC / output stage TTL with inverted signals						R				
<b>Output signals (G)</b>										
K1, K2, K0								DN		
<b>Pulse number (G)<sup>(1)</sup></b>										
300									300	
500									500	
512									512	
1000									1000	
1024									1024	
1200									1200	
2048									2048	
2500									2500	
3072									3072	
4096									4096	
5000									5000	
<b>Voltage supply / output stage (G)</b>										
9...30 VDC / output stage HTL with inverted signals									I	
5 VDC / output stage TTL with inverted signals									TTL	
9...30 VDC / output stage TTL with inverted signals									R	

(1) Other pulse numbers on request.

### Accessories

#### Mounting accessories

- Spring disk coupling K 35 (shaft ø6...12 mm)
- Spring disk coupling K 50 (shaft ø11...16 mm)
- Spring disk coupling K 60 (shaft ø11...22 mm)

## POG 9 G

Twin encoder with two electrically separated systems

Solid shaft with EURO flange B10 300...5000 pulses per revolution

### Accessories

#### Diagnostic accessories

11075858	Analyzer for encoders HENQ 1100
11075880	Analyzer for encoders HENQ 1100 B