

# UF200.P50-GP2J.72CU

Article number: 11708330

### Overview

- Fastest limit value detection due to extremely short response times
- Acquisition of two independent limit values
- Flexible parameterization and additional diagnostic data thanks to IO-
- Shortest blind zone in its class
- High performance in compact housing



Picture similar







Technical data	
General data	
Scanning range Sd	15 500 mm
Scanning range close limit Sdc	15 500 mm
Scanning range far limit Sde	15 500 mm
Version	IO-Link dual channel Multiplex version
Hysteresis typ.	4 % Sde
Repeat accuracy	0.5 mm
Temperature drift	< 2 % of distance to target Sde
Power-up drift	Compensated after 15 min.
Response time ton/toff min	< 16 ms
Response time ton/toff standard	< 40 ms
Sonic frequency	290 kHz
Adjustment	qTeach, IO-Link
Light indicator	Yellow LED / red LED
Power on indication	LED green
Alignment measuring axis	< 2°
Electrical data	
Voltage supply range +Vs	12 30 VDC
Current consumption typ.	16 mA
Output circuit	Push-pull
Output current	<100 mA
Voltage drop Vd	<3 VDC
Residual ripple	< 10 % Vs
Short circuit protection	Yes
Reverse polarity protection	Yes, Vs to GND
Communication interface	
Interface	IO-Link V1.1

Communication interface	
Baud rate	38,4 kBaud (COM 2)
Cycle time	≥ 8 ms
Process data length	48 Bit
Process data structure	Bit 0 = SSC1 (distance) Bit 1 = SSC2 (distance) Bit 2 = quality Bit 3 = alarm Bit 5 = SSC4 (counter) Bit 8-15 = scale factor Bit 16-47 = 32 Bit measurement
IO-Link port type	Class A
Additional data	Distance Excess gain Operating cycles Operating hours Boot cycles Operating voltage Device temperature Histograms
Adjustable parameters	Switching point Switching hysteresis Measured value filtering Time filters LED status indicators Output logic Output circuit Counter Beam forming Analog output characteristic Deactivate the sensor element Find Me function
Mechanical data	
Design	Rectangular
Housing material	Plastic (ASA, PMMA)




# UF200.P50-GP2J.72CU

Article number: 11708330

Technical data	
Mechanical data	
Width / diameter	20.5 mm
Height / length	41 mm
Depth	15 mm
Connection types	Cable 4 pin. 2 m

Ambient conditions	
Operating temperature	-25 +65 °C
Storage temperature	-25 +75 °C
Protection class	IP 67

# Dimension drawing 20.5 Teach Verzinnt P 15 Teach 15 Teach 11.8



 $\begin{tabular}{ll} \textbf{object distance (So) from sensor front (mm)} \\ \textbf{standard target with } 30 \times 30 \ mm, \ directed rectangular to sensor's reference axis \\ \end{tabular}$ 

## **Connection diagram**

