

## VCXG-22C.R

Gigabit Ethernet, 2,1 Megapixel, Color

Article number: 11209587

### Overview

- 1920 x 1080 px
- Sony IMX290
- 1/2.8" CMOS
- 58 fps
- Gigabit Ethernet



GEN<i>CAM



### Technical data

#### Sensor information

Sensor	Sony IMX290
Mono/Color	Color
Sensor type	1/2.8" CMOS
Shutter type	Rolling shutter Global reset shutter
Resolution	1920 × 1080 px
Pixel size	2.9 × 2.9 µm
Exposure time	0.015 ... 60000 ms

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 1920 × 1080 px, max. 58 fps Binning 2×2, 960 × 540 px, max. 89 fps Binning 2×1, 960 × 1080 px, max. 58 fps Binning 1×2, 1920 × 540 px, max. 89 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1920 × 1080 px, max. 89 fps
Pixel formats	BayerRG8 BayerRG10 BayerRG12 BayerRG12 Packed Mono8 Mono10 Mono12 Mono12 Packed RGB8 BGR8

#### Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
-----------------	---

#### Image preprocessing

Color models	Mono Raw Bayer RGB BGR
--------------	---------------------------------

#### Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto
Image Pre-processing	Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand

## VCXG-22C.R

Gigabit Ethernet, 2,1 Megapixel, Color

Article number: 11209587

### Technical data

#### Camera features

Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Process Synchronization	Events Timer Trigger Delay Debouncer Counter Trigger via Action CMD (GigE) Chunk data inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
Internal image buffer	95 MB 16 images (Trigger Mode) 1 image (Free Running Mode)

#### Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via M8 / 8 pins or Power over Ethernet (PoE)

#### Mechanical data

Lens mount	C-mount
------------	---------

#### Mechanical data

Width	29 mm
Height	29 mm
Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, baked varnish (until 02-2020 nickel-chrome-plated), IP 40

#### Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	approx. 2,0 W @ 12 VDC and 58 fps approx. 2,5 W @ 48 VDC (PoE) and 58 fps

#### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

#### Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

#### Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

#### Conformity

Conformity	CE RoHS EAC
------------	-------------------

### Dimension drawing

