

**Overview**

- SmartReflect - Safe barrier principle without reflector
- Baumer PinPoint LED: Small, homogeneous light spot with sharp edges
- qTeach - tamper-proof, simple teach-in with ferromagnetic tool
- Intuitive Xpress Teach / 1-Step Teach method
- Quick mounting by means of M3 threaded bushes made of stainless steel




Picture similar




**Technical data**

General data		Electrical data	
Type	Light barrier	Current consumption max. (no load)	40 mA (@ 10 VDC)
Version	Standard object detection	Current consumption typ.	16 mA (@ 24 VDC)
Background position Sde	25 ... 180 mm	Voltage drop Vd	<2 VDC
Scanning range Sa	90% ... 85% Sde	Output function	Light / dark operate
Smallest object recognizable typ.	2.5 mm	Output circuit	NPN complementary
Power on indication	LED green	Output current	50 mA
Alignment / soiled lens indicator	Flashing output indicator	Short circuit protection	Yes
Output indicator	LED yellow	Reverse polarity protection	Yes
Sensing distance adjustment	qTeach / 1-Step Teach-in	Mechanical data	
Suppression of reciprocal influence	Yes	Width / diameter	8 mm
Alignment optical axis	< 1,5°	Height / length	25.1 mm
Light Source		Depth	15.8 mm
Light source	Pulsed PinPoint LED	Design	Rectangular
Wave length	644 nm	Mechanical mounting	Threaded sleeves M3 (stainless steel)
Electrical data		Housing material	Plastic (ASA, PMMA)
Response time / release time	< 0.5 ms	Front (optics)	PMMA
Voltage supply range +Vs	10 ... 30 VDC	Connection types	Flylead connector M8 4 pin, L=200 mm
		Cable characteristics	PVC / PVC 4 x 0.08 mm <sup>2</sup>
		Ambient conditions	
		Protection class	IP 67
		Operating temperature	-25 ... +50 °C


**Dimension drawing**



**Connection diagram**



**Pin assignment**



**Beam characteristic (typically)**

