

**Overview**

- 50 ... 60 mm
- pulsed red laser diode
- analog
- Teach-in: button / external
- connector M8 4 pin
- 50 °C
- IP 67



Picture similar



**Technical data**

**General data**

Measuring distance Sd	50 ... 60 mm
Adjustment	Teach-in: button / external
Teach-in range min.	> 1 mm
Power on indication	LED green
Soiled lens indicator	LED red
Resolution	< 15 µm
Linearity error	< 0.045 mm
Beam type	Line
Interference suppression	< 30 ms
Object reflectivity	> 0.5 %
Temperature drift	< 0,07 % Sde/K

**Light Source**

Light source	Pulsed red laser diode
Wave length	650 nm
Laser class	1

**Electrical data**

Response time / release time	< 2 ms
Voltage supply range +Vs	12 ... 28 VDC

**Electrical data**

Current consumption max. (no load)	100 mA
Output circuit	Analog
Output signal	4 ... 20 mA
Load resistance	< (+Vs - 6 V) / 0,02 A
Short circuit protection	Yes
Reverse polarity protection	Yes, Vs to GND

**Mechanical data**

Width / diameter	13.4 mm
Height / length	48.2 mm
Depth	40 mm
Type	Rectangular
Housing material	Aluminum
Front (optics)	Glass
Connection types	Connector M8 4 pin

**Ambient conditions**


Ambient light immunity	< 100 kLux
Protection class	IP 67
Operating temperature	0 ... +50 °C

# OADM 1317730/S35A

Distance sensors - miniature

Article number: 11017045

## Dimension drawing




▪ \* emitter axis

## Laser warning


**CLASS 1 LASER  
PRODUCT**

IEC 60825-1/2014  
Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019


## Connection diagram



## Resolution



## Linearity error



## Beam characteristic (typically)

