

Overview

- step analysis
- 16 ... 120 mm
- pulsed red laser diode
- NPN
- Teach-in
- connector M8 4 pin
- 50 °C
- IP 67



Picture similar



Technical data

General data

Type	Step analysis
Sensing distance Tw	16 ... 120 mm
Teach-in range min.	> 0.2 mm
Adjustment	Teach-in
Power on indication	LED green
Output indicator	LED red
Light source	Pulsed red laser diode
Laser class	2
Wave length	650 nm
Beam diameter	0.5 ... 0.2 mm

Electrical data

Response time	< 5 ms
Voltage supply range +Vs	12 ... 28 VDC
Current consumption max. (no load)	80 mA
Current consumption typ.	40 mA
Output circuit	NPN

Electrical data

Output current	< 100 mA
Output pulse length	10 ms
Voltage drop Vd	< 2.8 VDC
Reverse polarity protection	Yes, Vs to GND
Short circuit protection	Yes


Mechanical data

Width / diameter	12.4 mm
Height / length	37 mm
Depth	34.5 mm
Type	Rectangular
Front (optics)	Glass
Housing material	Die-cast zinc
Connection types	Connector M8 4 pin

Ambient conditions


Operating temperature	0 ... +50 °C
Protection class	IP 67

Dimension drawing



- * emitter axis

Laser warning



Connection diagram

