

## Overview

- diffuse contrast sensor
- 3 ... 150 mm
- pulsed red laser diode
- NPN
- potentiometer, 5 turn
- connector M8 4 pin
- -10 ... 50 °C
- IP 67



Picture similar



## Technical data

### General data

Type	Diffuse contrast sensor
Version	Line beam
Light source	Pulsed red laser diode
Sensing distance Tw	3 ... 150 mm
Optimum operating distance	35 ... 45 mm
Repeat accuracy	< 0.2 mm at laser focus
Power on indication	LED green
Light indicator	LED yellow
Sensitivity adjustment	Potentiometer, 5 turn
Laser class	1
Distance to focus	40 mm
Wave length	650 nm

### Electrical data

Response time / release time	< 0.05 ms
Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	50 mA

### Electrical data

Current consumption typ.	40 mA
Voltage drop Vd	< 1.8 VDC
Output function	Light / dark operate
Output circuit	NPN
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

### Mechanical data

Width / diameter	10.4 mm
Height / length	27 mm
Depth	16.3 mm
Type	Rectangular
Housing material	Plastic (ASA)
Front (optics)	PMMA
Connection types	Connector M8 4 pin

### Ambient conditions


Protection class	IP 67
Operating temperature	-10 ... +50 °C

# OZDK 10N5150/S35A

Diffuse contrast sensors - miniature

Article number: 10162952

## Dimension drawing




- \* emitter axis

## Laser warning

**CLASS 1 LASER  
PRODUCT**

IEC 60825-1/2014  
Complies with 21 CFR 1040.10 and  
1040.11 except for conformance with  
IEC 60825-1 Ed. 3., as described in  
Laser Notice No. 56, dated May 8, 2019

## Connection diagram



## Beam characteristic (typically)

