

OZDM 16P3001/S14

Diffuse sensors with intensity difference - standard

Article number: 10124714

Overview

- intensity difference
- < 250 mm
- pulsed red laser diode
- PNP
- potentiometer, 14 turn
- connector M12 4 pin
- -10 ... 50 °C
- IP 67



Picture similar



Technical data

General data

Type	Intensity difference
Light source	Pulsed red laser diode
Sensing distance Tw	< 250 mm
Optimum operating distance	40 ... 80 mm
Detectable remission difference (on grey)	> 8 %
Repeat accuracy	< 0,1 mm at laser focus
Output indicator	LED yellow
Sensitivity adjustment	Potentiometer, 14 turn
Laser class	1
Distance to focus	80 mm
Wave length	675 nm

Electrical data

Response time / release time	< 0,05 ms
Voltage supply range +Vs	12 ... 30 VDC
Current consumption max. (no load)	65 mA

Electrical data

Current consumption typ.	60 mA
Voltage drop Vd	< 2 VDC
Output function	Dark operate
Output circuit	PNP
Output current	< 200 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

Mechanical data

Width / diameter	15,4 mm
Height / length	50 mm
Depth	50 mm
Type	Rectangular
Housing material	Die-cast zinc
Front (optics)	Glass
Connection types	Connector M12 4 pin

Ambient conditions


Operating temperature	-10 ... +50 °C
Protection class	IP 67

OZDM 16P3001/S14


Diffuse sensors with intensity difference - standard

Article number: 10124714


Dimension drawing



Connection diagram



Relative receiving signal



Laser warning

CLASS 1 LASER PRODUCT

IEC 60825-1/2014
Complies with 21 CFR 1040.10 and
1040.11 except for conformance with
IEC 60825-1 Ed. 3., as described in
Laser Notice No. 56, dated May 8, 2019

Beam characteristic (typically)

