

The new toolbox for edge measurement

Always the right edge sensor

OE60



High-performance edge sensor

- Best-in-class precision down to 1 µm
- Transmitter-receiver principle
- All-in-one: compact and easy to integrate

OE40



Performance edge sensor

- Precision up to 5 µm
- Through-beam principle
- Detecting even transparent edges
- Plug-and-play without alignment thanks to reflector bracket


OXM




Smart 2D profile sensors

- Smart function toolbox for profile evaluation in the sensor
- 30 µm resolution in X-direction
- Free configuration in the intuitive web interface


Highlights



Edge detection most diversified materials with 1 µm precision.



Design-in flexibility thanks to different functional principles.



Easy integration and digital secondary data via standardized interface like IO-Link, EtherCat and Modbus RTU.

The portfolio at a glance

	High-performance edge sensor OE60	Performance edge sensor OE40	Smart 2D profile sensors OXM
Product overview	 Article no. 11722571	 Article no. 11722385, 11722383, 11722384	 Article no. 11264668
Function	Edge position	Edge position, transparent edges, width, gap	Free configuration of up to 7 measurement values
Measuring range	10 mm	24 mm	300 mm
Max. distance	300 mm (transmitter to receiver)	200 mm (towards object)	500 mm (towards object)
Precision level	1 µm	5 µm	30 µm
Interface	Modbus RTU	IO-Link V1.1.3	PROFINET, Ethernet/IP, IO-Link
Accessories	Optional controller unit OE60C with EtherCat interface Article no. 11264668	USB-C IO-Link Master Article no. 11234828	

