

VEXU-24C

USB 3.0, 2,3 Megapixel, Color

Article number: 11151568

Overview

- 1920 × 1200 px
- Sony IMX249
- 1/1.2" CMOS
- 38 fps
- USB 3.0



GEN<i>i>CAM



Technical data

Sensor information

Sensor	Sony IMX249 Gen1
Mono/Color	Color
Sensor type	1/1.2" CMOS
Shutter type	Global shutter
Resolution	1920 × 1200 px
Pixel size	5.86 × 5.86 μm
Exposure time	0.057 ... 60000 ms

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 1920 × 1200 px, max. 38 fps Binning 2×2, 960 × 600 px, max. 38 fps Binning 2×1, 960 × 1200 px, max. 38 fps Binning 1×2, 1920 × 600 px, max. 38 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1920 × 1200 px, max. 38 fps
Pixel formats	BayerRG8 BayerRG12

Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Raw Bayer

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Acquisition / Interface	Adjustable Framerate
Synchronization	free running trigger
Trigger sources	Hardware Software
Process Synchronization	Debouncer
Additional Functions	User Set
Internal image buffer	0 MB
Interfaces and connectors	
Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
Process interface	M8 / 4 pins (SACC-DSI-M 8MS-4CON-L180)
Power supply	via USB 3.0 interface

Mechanical data

Lens mount	CS-mount
Width	29 mm
Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, nickel-plated, IP 40

VEXU-24C

USB 3.0, 2,3 Megapixel, Color

Article number: 11151568

Technical data

Electrical data

Power consumption	approx. 1,5 W @ 38,0 fps
Operating voltage	5 VDC (via USB3.0 interface)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +65 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)

Environmental conditions

Protection class	IP 40
------------------	-------

Digital I/Os

Lines	1 input line 1 output line
-------	-------------------------------

Conformity

Conformity	CE RoHS EAC
------------	-------------------

Dimension drawing

