UF200.D25-UAMJ.72N

Article number: 11708355

Overview

- Best measuring performance due to precise measuring principle
- Parallel output signal to the IO-Link channel through Dual Channel Flexible parameterization and additional diagnostic data thanks to IO-
- Shortest blind zone in its class
- High performance in compact housing
- Metal connector



Picture similar







Technical data General data		Communication interface	
Scanning range Sd	10 250 mm	Baud rate	, 38,4 kB;
Scanning range close limit	10 250 mm	Cycle time	25 ms
Sdc	10 230 11111	Process data length	48 Bit
Scanning range far limit Sde	10 250 mm	Process data structure	Bit 0 = S Bit 1 = S
Version	IO-Link dual channel		Bit 2 = q
Hysteresis typ.	4 % Sde		Bit 3 = a
Repeat accuracy	0.5 mm		Bit 5 = S Bit 8-15
Resolution	< 0.3 mm		Bit 16-13
Response time ton/toff standard	< 25 ms	IO-Link port type	Class A
Response time ton/toff min	< 10 ms	Additional data	Distance Excess
Temperature drift	< 2 % of distance to target Sde		Operatir
Power-up drift	Compensated after 15 min.		Operatir
Sonic frequency	370 kHz		Boot cyc
Adjustment	qTeach, line-Teach, IO-Link		Operatir Device t
ight indicator	LED yellow		Histogra
Power on indication	LED green	Adjustable parameters	Switchin
Alignment measuring axis	< 2°		Switchin
Electrical data			Measure Time filte
Voltage supply range +Vs	12 30 VDC		LED sta
Current consumption typ.	12 mA		Output I
Output circuit	Voltage output		Output
Output signal	0 10 V / 10 0 V		Counter Beam fo
_oad resistance	> 10 kOhm	Be	
Residual ripple	< 10 % Vs		Deactiva
Short circuit protection	Yes		Find Me
Reverse polarity protection	Yes, Vs to GND	Mechanical data	
Communication interface		Design	Rectang
Interface	IO-Link V1.1	Housing material	Plastic (

Communication interface	
Baud rate	38,4 kBaud (COM 2)
Cycle time	≥ 5 ms
Process data length	48 Bit
Process data structure	Bit 0 = SSC1 (distance) Bit 1 = SSC2 (distance) Bit 2 = quality Bit 3 = alarm Bit 5 = SSC4 (counter) Bit 8-15 = scale factor Bit 16-47 = 32 Bit measurement
IO-Link port type	Class A
Additional data	Distance Excess gain Operating cycles Operating hours Boot cycles Operating voltage Device temperature Histograms
Adjustable parameters	Switching point Switching hysteresis Measured value filtering Time filters LED status indicators Output logic Output circuit Counter Beam forming Analog output characteristic Deactivate the sensor element Find Me function
Mechanical data	
Design	Rectangular
Housing material	Plastic (ASA, PMMA)


UF200.D25-UAMJ.72N

Article number: 11708355

Technical data	
Mechanical data	
Width / diameter	20.5 mm
Height / length	41 mm
Depth	15 mm
Connection types	Connector M8 4 pin


Ambient conditions	
Operating temperature	-25 +65 °C
Storage temperature	-25 +75 °C
Protection class	IP 67

Dimension drawing 20.5 15 Teach 4 27.5 50.2




object distance (So) from sensor front (mm) standard target with 15 x 15 mm, directed rectangular to sensor's reference axis

Connection diagram



Pin assignment



www.baumer.com