


VEXU-24M

USB 3.0, 2,3 Megapixel, Monochrome

Article number: 11151567

Overview

- 1920 × 1200 px
- Sony IMX249
- 1/1.2" CMOS
- 38 fps
- USB 3.0



GEN*i*CAM



Technical data

Sensor information

Sensor	Sony IMX249 Gen1
Mono/Color	Mono
Sensor type	1/1.2" CMOS
Shutter type	Global shutter
Resolution	1920 × 1200 px
Pixel size	5.86 × 5.86 µm
Exposure time	0.057 ... 60000 ms

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 1920 × 1200 px, max. 38 fps Binning 2×2, 960 × 600 px, max. 38 fps Binning 2×1, 960 × 1200 px, max. 38 fps Binning 1×2, 1920 × 600 px, max. 38 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1920 × 1200 px, max. 38 fps
Pixel formats	Mono8 Mono12

Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Acquisition / Interface	Adjustable Framerate

Synchronization	free running trigger
-----------------	-------------------------

Trigger sources	Hardware Software
-----------------	----------------------

Process Synchronization	Debouncer
-------------------------	-----------

Additional Functions	User Set
----------------------	----------

Internal image buffer	0 MB
-----------------------	------

Interfaces and connectors

Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
----------------	--

Process interface	M8 / 4 pins (SACC-DSI-M 8MS-4CON-L180)
-------------------	--

Power supply	via USB 3.0 interface
--------------	-----------------------

Mechanical data

Lens mount	CS-mount
Width	29 mm
Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, nickel-plated, IP 40

VEXU-24M

USB 3.0, 2,3 Megapixel, Monochrome

Article number: 11151567

Technical data

Electrical data

Power consumption	approx. 1,5 W @ 38,0 fps
Operating voltage	5 VDC (via USB3.0 interface)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +65 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)

Environmental conditions

Protection class	IP 40
------------------	-------

Digital I/Os

Lines	1 input line 1 output line
-------	-------------------------------

Conformity

Conformity	CE RoHS EAC
------------	-------------------

Dimension drawing

