

VLG-22C

Gigabit Ethernet, 2,0 Megapixel, Color

Article number: 11099360

Overview

- 2040 × 1084 px
- ams (CMOSIS) CMV2000
- 2/3" CMOS
- 55 fps
- Gigabit Ethernet



GEN*i*CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV2000
Mono/Color	Color
Sensor type	2/3" CMOS
Shutter type	Global shutter
Resolution	2040 × 1084 px
Pixel size	5.5 × 5.5 µm
Exposure time	0.015 ... 1000 ms

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2040 × 1084 px, max. 55 fps
Pixel formats	Mono8 BayerRG8 BayerRG12 RGB8 Packed BGR8 Packed YUV411 Packed YUV422 Packed YUV444 Packed

Image preprocessing

Analog controls	Gain (0 ... 18 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	RGB YUV Mono
Color processing	Integrated color processor for high quality color calculation

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 512 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor output line ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	120 MB

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
Process interface	SACC-DSI-M8FS-3CON-M10-L180 SH
Power supply	SACC-DSI-M 8MS-6CON-L180 SH

Mechanical data

Lens mount	C-mount
Width	33 mm
Height	33 mm

VLG-22C

Gigabit Ethernet, 2,0 Megapixel, Color

Article number: 11099360

Technical data

Mechanical data

Depth	48 mm
Weight	≤ 150 g
Material	zinc die casting, nickel-plated, IP 40

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply)
	36 ... 57 V DC (Power over Ethernet)
Power consumption	approx. 3,5 W @ 12 VDC and 55,0 fps approx. 3,8 W @ 48 VDC (PoE) and 55,0 fps

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +50 °C
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Digital I/Os

Lines	1 input line 3 output lines
-------	--------------------------------

Conformity

Conformity	CE RoHS
------------	------------

Dimension drawing

