

VLG-22M.I

Gigabit Ethernet, 2,0 Megapixel, Monochrome

Article number: 11104900

Overview

- 2040 × 1084 px
- ams (CMOSIS) CMV2000
- 2/3" CMOS
- 55 fps
- Gigabit Ethernet



GEN<i>i>CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV2000
Mono/Color	Mono
Sensor type	2/3" CMOS
Shutter type	Global shutter
Resolution	2040 × 1084 px
Pixel size	5.5 × 5.5 µm
Exposure time	0.015 ... 1000 ms

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2040 × 1084 px, max. 55 fps
Pixel formats	Mono8 Mono12 Mono12 Packed

Image preprocessing

Analog controls	Gain (0 ... 18 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 512 trigger signals
Sequencer	Automated control for series of images using different sets of parameters

Camera features

Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	120 MB

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mb/s/sec, Fast Ethernet, Transfer Rate 100 Mb/s/sec, Connector: SACC-CI-M12FS-8CON-L180-10G
Process interface / power supply	SACC-CI-M12MS-8CON-SH TOR 32 / 8 pins

Mechanical data

Lens mount	C-mount
Width	46 mm
Height	46 mm
Depth	49.8 mm
Weight	≤ 185 g ≤ 220 g (incl. tube)
Material	aluminum, IP 65 / 67

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
--------------------------	--

VLG-22M.I

Gigabit Ethernet, 2,0 Megapixel, Monochrome

Article number: 11104900

Technical data

Electrical data

Power consumption	approx. 3,5 W @ 12 VDC and 55,0 fps approx. 3,8 W @ 48 VDC (PoE) and 55,0 fps
-------------------	--

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +50 °C
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40 IP 54 (with mounted tube and cable) IP 65 (with mounted tube and cable) IP 67 (with mounted tube and cable) IP 69K (with stainless steel housing accessory)

Digital I/Os

Lines	1 input line 3 output lines
-------	--------------------------------

Conformity

Conformity	CE RoHS
------------	------------

Dimension drawing

