

VLG-23C.I

Gigabit Ethernet, 2,3 Megapixel, Color

Article number: 11143092

Overview

- 1920 × 1200 px
- Sony IMX174
- 1/1.2" CMOS
- 53 fps
- Gigabit Ethernet
- Phase-Out starting 08/20, alternative via sales



GEN*i*CAM



Technical data

Sensor information

Sensor	Sony IMX174 Gen1
Resolution	1920 × 1200 px
Exposure time	0,045 ... 60000 ms
Pixel size	5.86 × 5.86 µm
Shutter type	Global shutter
Sensor type	1/1.2" CMOS

Acquisition formats

Image formats, interface	Full Frame, 1920 × 1200 px, max. 53 fps frame rate max.
Pixel formats	Mono8 BayerRG8 BayerRG12 RGB8 Packed BGR8 Packed YUV411 Packed YUV422 Packed YUV444 Packed

Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	RGB YUV Mono
Color processing	Integrated color processor for high quality color calculation

Camera features

Synchronization	free running trigger
-----------------	----------------------

Camera features

Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 512 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor output line ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	120 MB

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mb/s/sec, Fast Ethernet, Transfer Rate 100 Mb/s/sec, Connector: SACC-CI-M12FS-8CON-L180-10G
Process interface / power supply	SACC-CI-M12MS-8CON-SH TOR 32 / 8 pins

Mechanical data

Lens mount	C-mount
Width	46 mm
Height	46 mm
Depth	49,8 mm

VLG-23C.I

Gigabit Ethernet, 2,3 Megapixel, Color

Article number: 11143092

Technical data

Mechanical data

Weight	≤ 185 g ≤ 220 g (incl. tube)
Material	aluminum, IP 65 / 67

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	approx. 3,5 W @ 12 VDC und 53,0 fps approx. 3,8 W @ 48 VDC (PoE) and 53,0 fps

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +50 °C
-----------------------	---------------

Environmental conditions

Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40 IP 54 (with mounted tube and cable) IP 65 (with mounted tube and cable) IP 67 (with mounted tube and cable) IP 69K (with stainless steel housing accessory)

Digital I/Os

Lines	1 input line 3 output lines
-------	--------------------------------

Conformity

Conformity	CE RoHS
------------	------------

Dimension drawing

