

VLXT-126C.I

Gigabit Ethernet, 12,2 Megapixel, Color

Article number: 11702304

Overview

- 4096 × 2992 px
- Sony IMX535
- 1/1.1" CMOS
- 100 fps
- 10 GigE



Picture similar



GEN<i>i>CAM



Technical data

Sensor information

Sensor	Sony IMX535 Gen4
Mono/Color	Color
Sensor type	1/1.1" CMOS
Shutter type	Global shutter
Resolution	4096 × 2992 px
Pixel size	2.74 × 2.74 μm
Exposure time	0.001 ... 60000 ms

Data quality (EMVA 1288 typical)

Dark noise	2.41 e-
Saturation capacity	9155 e-
Dynamic range	69.5 dB
Signal-to-noise ratio	39.6 dB
Quantum efficiency	42.1 % @ 465 nm 48.2 % @ 535 nm 38.2 % @ 630 nm 42 % @ 467 nm 49 % @ 533 nm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 4096 × 2992 px, max. 100 fps Binning 2×2, 2048 × 1496 px, max. 119 fps Binning 1×2, 4096 × 1496 px, max. 119 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 4096 × 2992 px, max. 119 fps

Acquisition formats

Pixel formats	BayerRG8 BayerRG10 BayerRG12 BayerRG12 Packed Mono8 Mono10 Mono12 Mono12 Packed RGB8 BGR8
---------------	----------------------------------------------------------------------------------------------------------------------

Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono Raw Bayer RGB BGR

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image) Multi ROI
-----------------	------------------------------------------------------------------------------------------------------------------------------------------------------------

VLXT-126C.I

Gigabit Ethernet, 12,2 Megapixel, Color

Article number: 11702304

Technical data

VLXT-126C.I

Gigabit Ethernet, 12,2 Megapixel, Color

Article number: 11702304


Camera features		Camera features	
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto	Internal image buffer	1024 MB 84 images (Trigger Mode) 1 image (Free Running Mode)
Image Pre-processing	Image Flipping (X/Y) Color Processing (RGB, BGR, Mono) Advanced 5x5 Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma Shading Correction Edge Sharpening Noise Reduction	Interfaces and connectors	
Acquisition / Interface	Burst Mode Adjustable Framerate Short Exposure Time Enable Device Link Throughput Limit Internal Image Buffer	Data interface	10 Gigabit Ethernet, Transfer rate 10000 Mbits/sec, Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer rate 100 Mbits/sec, Connector: M12 / 8-pol x-coded (SACC-CI-M12FS-8CON-L180-10G)
Synchronization	free running trigger	Process interface	M12 / 12 pins a-coded (SACC-CI-M12MS-12CON-L180)
Trigger sources	Hardware Software ActionCommand	Power supply	via M12/12 pins a-coded
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals	Mechanical data	
Process Synchronization	Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Action CMD Request ID Trigger ID inside Chunk Additional Output Modes (e.g. Trigger Ready) PWM (PWM Duration / PWM Duty Cycle) Selectable Output format (e.g. Tri State, Push Pull) Chunk data inside transferred image Encoder support via Counter End trigger source 4 power outputs with up to 120 W (max. 48 V / 2.5 A)	Lens mount	C-mount
Time synchronization IEEE 1588	IEEE 1588 / Master and Slave function IEEE 1588 / Scheduled Action CMD IEEE 1588 / Synchronized Acquisition Framerate	Width	60 mm
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data	Height	60 mm
Lens control	Corning liquid lens	Depth	99.7 mm
Sequencer	Automated control for series of images using different sets of parameters	Weight	≤ 485 g
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y	Material	aluminum, hard-anodized
		Electrical data	
		Voltage supply range +Vs	19.2 ... 28.8 V DC (external power supply)
		Power consumption	Approx. 12.6 W @ 24 VDC and 100 fps
		Non-volatile memory	
		Flash memory size	128 kB
		Environmental conditions	
		Operating temperature	0 ... +60 ° @ T = measurement point
		Humidity	10 ... 90 % (non-condensing)
		Protection class	IP 40 IP 54 (with mounted tube and cable) IP 65 (with mounted tube and cable) IP 67 (with mounted tube and cable)
		Digital I/Os	
		Lines	2 input lines 4 power output lines with pulse width modulation (PWM) (max. 48 V / max. 2,5 A) RS232
		Output line sources	Off Exposure Active Timer1 Readout Active User0 User1 User2 TriggerReady
		Conformity	
		Conformity	CE RoHS UL recognized

VLXT-126C.I

Gigabit Ethernet, 12,2 Megapixel, Color


Article number: 11702304

Dimension drawing




Principle

Optional accessories for protection class IP 65/67:



tube adapter

- hard-anodized, incl. sealing and screws
 \varnothing 49,5 mm (VCXG.I 11185373)
 \varnothing 65 mm (VCXG.I 11185377)
 \varnothing 95 mm (VCXG.I 11704311)
 \varnothing 65 mm (VLXT 11193125)
 \varnothing 95 mm (VLXT.EF 11704315)



tube

- hard-anodized, cover glass PMMA
 \varnothing 49,5 mm, Length 44 mm (11185370)
 \varnothing 65 mm, Length 58 mm (11185374)
 \varnothing 95 mm, length 70 mm (11704312)
- hard-anodized, tempered laminated safety glass
 \varnothing 49,5 mm, Length 44 mm (11701124)
 \varnothing 65 mm, Length 58 mm (11701125)