

## V CXG-13C

Gigabit Ethernet, 1,3 Megapixel, Color

Article number: 11164974

### Overview

- 1280 x 1024 px
- onsemi PYTHON1300
- 1/2" CMOS
- 94 fps
- Gigabit Ethernet
- available on request



GEN<i>i>CAM



### Technical data

#### Sensor information

Sensor	onsemi PYTHON1300
Mono/Color	Color
Sensor type	1/2" CMOS
Shutter type	Global shutter
Resolution	1280 × 1024 px
Pixel size	4.8 × 4.8 μm
Exposure time	0.02 ... 1000 ms

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 1280 × 1024 px, max. 94 fps Binning 2×2, 640 × 512 px, max. 148 fps Binning 2×1, 640 × 1024 px, max. 148 fps Binning 1×2, 1280 × 512 px, max. 148 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1280 × 1024 px, max. 146 fps
Pixel formats	BayerRG8 BayerRG10 Mono8 Mono10 RGB8 BGR8

#### Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Mono Raw Bayer RGB

#### Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto
Image Pre-processing	Image Flipping (X/Y) Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

# V CXG-13C

Gigabit Ethernet, 1,3 Megapixel, Color

Article number: 11164974

## Technical data

### Camera features

Process Synchronization	Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunk data inside transferred image Encoder support via Counter End trigger source
-------------------------	---

Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
----------------------	--

Internal image buffer	60 MB 16 images (Trigger Mode) 1 image (Free Running Mode)
-----------------------	--

### Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
----------------	---

Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
-------------------	--

Power supply	via M8 / 8 pins or Power over Ethernet (PoE)
--------------	--

### Mechanical data

Lens mount	C-mount
------------	---------

### Mechanical data

Width	29 mm
Height	29 mm
Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, baked varnish (until 02-2020 nickel-chrome-plated), IP 40

### Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	approx. 2,5 W @ 12 VDC and 94 fps approx. 3,2 W @ 48 VDC (PoE) and 94 fps

### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

### Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

### Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

### Conformity

Conformity	CE RoHS KC (MISP-REI-BKR-V CXG-13M) EAC
------------	--

## Dimension drawing

