

ZVI-HELIOS-95 IP65 w 80° SC M8

ZVI-HELIOS-95 IP65 w 80° SC M8

Article number: 11703773

Overview

- flashable LED ring light
- white
- radiation angle 80°
- SC type - optimized for pulsed operation (illumination controller is required)
- stainless steel M8/4-pin connector (cable has to be ordered separately)
- diameter: 99 mm
- IP65 protection with special housing design to improve washdown properties (elimination of cooling fins, concave cover glass)



Technical data

General data

Manufacturer Büchner Lichtsysteme GmbH

Illumination data

Color white
Illumination characteristic direct
Illumination mode flashable

Electrical data

Connectors M8/4-pin male connector, stainless steel
Illumination control SC type: for use in conjunction with a controller
Operating voltage 24 VDC
Current 0.45 A
Current at flash mode ≤ 6.4 A
Duty cycle 0-10%

Electrical data

Maximum flash duration 1 ms

Mechanical data

Construction design ring light
Inner diameter 36 mm
External diameter 99 mm
Height 22.7 mm
Material of cover glass acrylic
Material aluminium milled, silver anodized

Environmental conditions

Operating temperature max. 50 °C
Conformity CE
RoHS
Protection class IP 65

ZVI-HELIOS-95 IP65 w 80° SC M8

ZVI-HELIOS-95 IP65 w 80° SC M8

Article number: 11703773

Dimension drawing

