

Overview

- Computar lens
- 12 mm
- F 2,6-16
- format 1"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount C-mount

Dimensions 39 mm × 51,4 mm

Max. outer diameter 39 mm (without knurled screws)
49 mm (with knurled screws)

Max. length (excl. thread) 43.5 mm

Weight ≤ 98.4 g

Filter thread M 37,5 × 0,5

Lens data

Lens resolution 20 MP

Focal length 12 mm

Lens data

Focal range ≥ 12 mm ... < 25 mm

Format 1"

Aperture F2,6-16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 56.7 °

Vertical angle of view 44.1 °

Diagonal angle of view 67.4 °

At image format 12,8 × 9,6 mm

Environmental conditions

Operating temperature -10 ... +50 °C