

Overview

- Computar lens
- 25 mm
- F 2,8-16
- format 1,1"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount C-mount

Dimensions 39,5 mm × 34 mm

Max. outer diameter 39.5 mm (without knurled screws)
49.5 mm (with knurled screws)

Max. length (excl. thread) 37.7 mm

Weight ≤ 79 g

Filter thread M 34,0 × 0,5

Lens data

Lens resolution 12 MP

Focal length 25 mm

Lens data

Focal range ≥ 25 mm ... < 50 mm

Format 1,1"

Aperture F2,8-16

Aperture control Manual

M.O.D. 0.3 m

Horizontal angle of view 31.7 °

Vertical angle of view 23.5 °

Diagonal angle of view 38.7 °

At image format 16 × 12 mm

Environmental conditions

Operating temperature -10 ... +50 °C