

VCXG-82M

Gigabit Ethernet, 8 Megapixel, Monochrome

Article number: 11702861

Overview

- 2848 x 2832 px
- Sony IMX546
- 2/3" CMOS
- 15 fps
- Gigabit Ethernet



GEN*i*CAM



Technical data

Sensor information

Sensor	Sony IMX546 Gen4
Mono/Color	Mono
Sensor type	2/3" CMOS
Shutter type	Global shutter
Resolution	2848 × 2832 px
Pixel size	2.74 × 2.74 µm
Exposure time	0.001 ... 60000 ms

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2848 × 2832 px, max. 15 fps Binning 2×2, 1424 × 1416 px, max. 55 fps Binning 2×1, 1424 × 2832 px, max. 16 fps Binning 1×2, 2848 × 1416 px, max. 16 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2848 × 2832 px, max. 16 fps
Pixel formats	Mono8 Mono10 Mono12 Mono12 Packed

Image preprocessing

Analog controls	Gain (0 ... 18 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Mono

Camera features

Basic Functions	Exposure Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto
Image Pre-processing	Image Flipping (X/Y) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

VCXG-82M

Gigabit Ethernet, 8 Megapixel, Monochrome

Article number: 11702861

Technical data

Camera features

Process Synchronization	Events
	Timer
	Trigger Delay
	Debouncer
	Counter
	Sequencer
	Trigger via Action CMD (GigE)
	Additional Output Modes (e.g. Trigger Ready)
	Chunk data inside transferred image
	Encoder support via Counter End trigger source
Additional Functions	User Set
	Integrated temperature sensor
	Readable additional information (e.g. sensor information)
	Save Custom Data
Internal image buffer	185 MB
	8 image (Trigger Mode)
	1 image (Free Running Mode)

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mb/s/sec, Fast Ethernet, Transfer Rate 100 Mb/s/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via M8 / 8 pins or Power over Ethernet (PoE)

Mechanical data

Lens mount	C-mount
Width	29 mm
Height	29 mm

Mechanical data

Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, baked varnish

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply)
	36 ... 57 V DC (Power over Ethernet)
Power consumption	approx. 2.3 W @ 12 VDC and 15 fps approx. 3.0 W @ 48 VDC (PoE) and 15 fps

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40 (with mounted lens and cable)

Digital I/Os

Lines	1 input line
	1 output line
	2 general purpose lines

Output line sources	Off
	Exposure Active
	Timer1
	Readout Active
	User0
	User1
	User2
	TriggerReady

Conformity

Conformity	CE RoHS
------------	------------

VCXG-82M

Gigabit Ethernet, 8 Megapixel, Monochrome

Article number: 11702861

Dimension drawing

