

## VCXG-91C

Gigabit Ethernet, 8,8 Megapixel, Color

Article number: 11173819

### Overview

- 4096 x 2160 px
- Sony IMX267
- 1" CMOS
- 13 fps
- Gigabit Ethernet



GEN*i*CAM



### Technical data

#### Sensor information

Sensor	Sony IMX267 Gen2
Mono/Color	Color
Sensor type	1" CMOS
Shutter type	Global shutter
Resolution	4096 × 2160 px
Pixel size	3.45 × 3.45 µm
Exposure time	0.001 ... 60000 ms

#### Data quality (EMVA 1288 typical)

Dark noise	2.06 e-
Saturation capacity	8915 e-
Dynamic range	70.3 dB
Signal-to-noise ratio	39.5 dB
Quantum efficiency	45.4 % @ 465 nm 57.4 % @ 536 nm 52.7 % @ 631 nm

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 4096 × 2160 px, max. 13 fps Binning 2×2, 2048 × 1080 px, max. 21 fps Binning 2×1, 2048 × 2160 px, max. 21 fps Binning 1×2, 2048 × 1080 px, max. 21 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 4096 × 2160 px, max. 21 fps

#### Acquisition formats

Pixel formats	BayerRG8 BayerRG10 BayerRG12 BayerRG12 Packed Mono8 Mono10 Mono12 Mono12 Packed RGB8 BGR8
---------------	--

#### Image preprocessing

Color models	Mono Raw Bayer RGB
--------------	--------------------------

#### Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto

# VCXG-91C

Gigabit Ethernet, 8,8 Megapixel, Color

Article number: 11173819

## Technical data

### Camera features

Image Pre-processing	Image Flipping (X/Y) Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Short Exposure Time Enable Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Process Synchronization	Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunk data inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
Internal image buffer	26 MB 1 image (Trigger Mode) 1 image (Free Running Mode)

### Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
----------------	---

### Interfaces and connectors

Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via M8 / 8 pins or Power over Ethernet (PoE)

### Mechanical data

Lens mount	C-mount
Width	29 mm
Height	29 mm
Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, baked varnish (until 02-2020 nickel-chrome-plated), IP 40

### Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	approx. 3,0 W @ 12 VDC and 13 fps approx. 3,6 W @ 48 VDC (PoE) and 13 fps

### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

### Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

### Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

### Conformity

Conformity	CE RoHS EAC BIS-CRS (R-41207004)
------------	---

## VCXG-91C

Gigabit Ethernet, 8,8 Megapixel, Color

Article number: 11173819

### Dimension drawing

