




EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at www.standard1288.org and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 7, 21.08.2018, SN 0018(AEON).

Measurements performed by Technical and Application Support Center, Baumer Optronic GmbH.

Vendor	Baumer
Model	VCXG.2-201M.R.I
Serial number	700010089073
Sensor diagonal	15.78 mm
Lens category	C-Mount
Resolution	5472 × 3648, 12 bit
Pixel size (h×v)	2.40 μm × 2.40 μm
Sensor	Sony IMX183
Sensor type	CMOS
Shutter type	Rolling shutter
Overlap cap.	Overlapped
Max. frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
Operation point 1	
Wavelength centroid	533.3 nm
Wavelength FWHM	30.3 nm
Gain, black-level	1.0 / 43.0
Optional data measured	
None	






Summary Sheet for Operation Point 1 at a Wavelength of 533 nm

Type of data	Single	Gain, black-level	1.0 / 43.0
Exposure control	By irradiance	Environmental temperature	23.1 °C
Exposure time	1.62 ms	Camera body temperature	25.6 °C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	Mono12	Wavelength, centr., FWHM	533 nm, 30.3 nm


Photon Transfer

Photon transfer mACC300218, 533 nm, 27.07.2023



Signal-to-Noise Ratio

SNR mACC300218, 533 nm, 27.07.2023



Quantum efficiency	η	77.4%
Overall system gain	K	0.267 DN/e ⁻
	$1/K$	3.740 e ⁻ /DN
Temporal dark noise	σ_d	3.00 e ⁻
	$\sigma_{y,\text{dark}}$	0.85 DN
Signal-to-noise ratio	SNR_{max}	121
		41.7 dB
		6.9 bit
	$1/\text{SNR}_{\text{max}}$	0.83 %
Absolute sensitivity threshold	$\mu_{p,\text{min}}$	4.81 p
	$\mu_{p,\text{min,area}}$	0.836 p/ μm^2
	$\mu_{e,\text{min}}$	3.73 e ⁻
	$\mu_{e,\text{min,area}}$	0.647 e ⁻ / μm^2
Saturation capacity	$\mu_{p,\text{sat}}$	18935 p
	$\mu_{p,\text{sat,area}}$	3287 p/ μm^2
	$\mu_{e,\text{sat}}$	14662 e ⁻
	$\mu_{e,\text{sat,area}}$	2545 e ⁻ / μm^2
Dynamic range	DR	3933
		71.9 dB
		11.9 bit
Spatial nonuniformities	DSNU_{1288}	0.21 e ⁻
		0.06 DN
	PRNU_{1288}	0.57 %
Linearity error	LE_{min}	-0.57%
	LE_{max}	1.61%
Dark current	$\mu_{c,\text{mean}}$	0.60 ± 0.01 e ⁻ /s
		0.16 DN/s
	$\mu_{c,\text{var}}$	0.64 ± 0.01 e ⁻ /s
	T_d	— °C