

## VEXG-25M

Gigabit Ethernet, 2,3 Megapixel, Monochrome

Article number: 11166637

### Overview

- 1920 × 1200 px
- ON Semiconductor PYTHON2000
- 2/3" CMOS
- 41 fps
- Gigabit Ethernet
- available



GEN*i*CAM



### Technical data

#### Sensor information

Sensor	ON Semiconductor PYTHON2000
Mono/Color	Mono
Resolution	1920 × 1200 px
Exposure time	0,04 ... 1000 ms
Pixel size	4.8 × 4.8 μm
Shutter type	Global shutter
Sensor type	2/3" CMOS

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 1920 × 1200 px, max. 41 fps Binning 2×2, 960 × 600 px, max. 41 fps Binning 2×1, 960 × 1200 px, max. 41 fps Binning 1×2, 1920 × 600 px, max. 41 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1920 × 1200 px, max. 41 fps
Pixel formats	Mono8 Mono10

#### Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Mono

#### Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Acquisition / Interface	Adjustable Framerate
Synchronization	free running trigger
Trigger sources	Hardware Software
Process Synchronization	Debouncer
Additional Functions	User Set
Internal image buffer	7 MB 1 image (Trigger Mode) 1 image (Free Running Mode)

#### Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 4 pins (SACC-DSI-M 8MS-4CON-L180)
Power supply	via M8 / 4 pins

#### Mechanical data

Lens mount	CS-mount
Width	29 mm

## VEXG-25M

Gigabit Ethernet, 2,3 Megapixel, Monochrome

Article number: 11166637

### Technical data

#### Mechanical data

Height	29 mm
Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, nickel-plated, IP 40

#### Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply)
Power consumption	approx. 2,8 W @ 12 VDC and 41 fps

#### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

#### Environmental conditions

Operating temperature	+5 ... +65 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

#### Digital I/Os

Lines	1 input line 1 output line
-------	-------------------------------

#### Conformity

Conformity	CE RoHS EAC
------------	-------------------

### Dimension drawing

