


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)" (see www.standard1288.org or the *Zenodo EMVA 1288 community*) release 3.0 with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 3, 15.08.2015, SN 0001(Baumer) . The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding specification and calibration report.

Measurements performed by Technical and Application Support Center, Baumer Optronik GmbH.



Vendor	Baumer
Model	VCXU-13M
Serial number	700001917258
Sensor diagonal	7.87 mm
Lens category	C-Mount
Resolution	1280 × 1024, 10 bit
Pixel size	4.80 μm × 4.80 μm
Sensor	OnSemi PYTHON1300
Sensor type	CMOS
Shutter type	Global shutter
Overlap capabilities	Overlapped
Maximum frame rate	0.0 Hz
Interface type	U3V

Type of data presented	Single
Operation point 1	
Wavelength centroid	535.8 nm
Wavelength FWHM	32.0 nm
Gain / BlackLevel	1.0 / 4
Optional data measured	
None	



EMVA 1288 Summary Sheet for Operating Point 1

Type of data	Single	Gain / BlackLevel	1.0 / 4
Exposure control	By irradiance	Environmental temperature	24.7°C
Exposure time	811.00 μ s	Camera body temperature	34.2°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	Mono10	Wavelength, centr., FWHM	536 nm, 32.0 nm



Quantum efficiency

 η 53.5%

Overall system gain

 K 0.118 DN/e⁻
 $1/K$ 8.483 e⁻/DN

Temporal dark noise & DSNU

 $\sigma_{y,\text{dark}}$ 1.19 DN
DSNU₁₂₈₈ 1.05 DN
 σ_d 9.78 e⁻
DSNU₁₂₈₈ 8.94 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 83
38.4 dB
6.4 bit
 $1/\text{SNR}_{\text{max}}$ 1.20 %
PRNU₁₂₈₈ 1.45 %

Nonlinearity

LE 0.44%
LE_{min} -0.26%
LE_{max} 0.61%

Sensitivity & saturation

 $\mu_{p,\text{min}}$ 19.8 p
0.86 p/ μm^2
 $\mu_{p,\text{sat}}$ 12997 p
564 p/ μm^2
 $\mu_{e,\text{min}}$ 10.6 e⁻
0.46 e⁻/ μm^2
 $\mu_{e,\text{sat}}$ 6952 e⁻
302 e⁻/ μm^2

Dynamic range

DR 656
56.3 dB
9.4 bit

Dark current

 $\mu_{c,\text{mean}}$ 29.4 DN/s
 $\mu_{c,\text{mean}}$ 249.3 e⁻/s
 $\mu_{c,\text{var}}$ 159.7 e⁻/s