


VEXG-25M

Gigabit Ethernet, 2,3 Megapixel, Monochrome

Article number: 11166637

Overview

- 1920 × 1200 px
- onsemi PYTHON2000
- 2/3" CMOS
- 41 fps
- Gigabit Ethernet



GEN*i*CAM



Technical data

Sensor information

Sensor	onsemi PYTHON2000
Mono/Color	Mono
Sensor type	2/3" CMOS
Shutter type	Global shutter
Resolution	1920 × 1200 px
Pixel size	4.8 × 4.8 μm
Exposure time	0.04 ... 1000 ms

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 1920 × 1200 px, max. 41 fps Binning 2×2, 960 × 600 px, max. 41 fps Binning 2×1, 960 × 1200 px, max. 41 fps Binning 1×2, 1920 × 600 px, max. 41 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1920 × 1200 px, max. 41 fps
Pixel formats	Mono8 Mono10

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Mono

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Acquisition / Interface	Adjustable Framerate
Synchronization	free running trigger
Trigger sources	Hardware Software
Process Synchronization	Debouncer
Additional Functions	User Set
Internal image buffer	7 MB 1 image (Trigger Mode) 1 image (Free Running Mode)

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mb/s/sec, Fast Ethernet, Transfer Rate 100 Mb/s/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 4 pins (SACC-DSI-M 8MS-4CON-L180)
Power supply	via M8 / 4 pins

Mechanical data

Lens mount	CS-mount
Width	29 mm

VEXG-25M

Gigabit Ethernet, 2,3 Megapixel, Monochrome

Article number: 11166637

Technical data

Mechanical data

Height	29 mm
Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, nickel-plated, IP 40

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply)
Power consumption	approx. 2,8 W @ 12 VDC and 41 fps

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +65 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Digital I/Os

Lines	1 input line 1 output line
-------	-------------------------------

Conformity

Conformity	CE RoHS EAC
------------	-------------------

Dimension drawing

