

## VEXG-52C.R

Gigabit Ethernet, 5,0 Megapixel, Color

Article number: 11185977

### Overview

- 2592 × 1944 px
- onsemi MT9P031
- 1/2.5" CMOS
- 14 fps
- Gigabit Ethernet



GEN<i>i>CAM



### Technical data

#### Sensor information

Sensor	onsemi MT9P031
Mono/Color	Color
Sensor type	1/2.5" CMOS
Shutter type	Rolling shutter Global reset shutter
Resolution	2592 × 1944 px
Pixel size	2.2 × 2.2 µm
Exposure time	0.02 ... 1000 ms

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2592 × 1944 px, max. 14 fps Binning 2×2, 1296 × 972 px, max. 14 fps Binning 2×1, 1296 × 1944 px, max. 14 fps Binning 1×2, 2592 × 972 px, max. 14 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2592 × 1944 px, max. 14 fps
Pixel formats	BayerRG8 BayerRG12 BayerRG12 Packed

#### Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Raw Bayer

#### Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	White Balance Auto
Image Pre-processing	Color Enhancement (with optimized ColorTransformationMatrix)
Synchronization	free running trigger
Trigger sources	Hardware Software
Process Synchronization	Debouncer
Additional Functions	User Set
Internal image buffer	15 MB 1 image (Trigger Mode) 1 image (Free Running Mode)

#### Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mb/s/sec, Fast Ethernet, Transfer Rate 100 Mb/s/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 4 pins (SACC-DSI-M 8MS-4CON-L180)
Power supply	via M8 / 4 pins

#### Mechanical data

Lens mount	CS-mount
------------	----------

# VEXG-52C.R

Gigabit Ethernet, 5,0 Megapixel, Color

Article number: 11185977

## Technical data

### Mechanical data

Width	29 mm
Height	29 mm
Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, nickel-plated, IP 40

### Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply)
Power consumption	approx. 2,0 W @ 12 VDC and 14 fps

### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

### Environmental conditions

Operating temperature	+5 ... +60 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

### Digital I/Os

Lines	1 input line 1 output line
-------	-------------------------------

### Conformity

Conformity	CE BIS-CRS (R-41207004)
------------	----------------------------

## Dimension drawing

