

## VLXT-06M.I.JP

Gigabit Ethernet, 0,5 Megapixel, Monochrome

Article number: 11700830

### Overview

- 800 × 620 px
- Sony IMX426
- 1/1.7" CMOS
- 1578 fps
- 10 GigE
- JPEG



GEN<i>i>CAM



### Technical data

#### Sensor information

Sensor	Sony IMX426 Gen3
Mono/Color	Mono
Sensor type	1/1.7" CMOS
Shutter type	Global shutter
Resolution	800 × 620 px
Pixel size	9 × 9 µm
Exposure time	0.001 ... 60000 ms

#### Data quality (EMVA 1288 typical)

Dark noise	21.66 e-
Saturation capacity	99279 e-
Dynamic range	72.6 dB
Signal-to-noise ratio	50 dB
Quantum efficiency	73.2 % @ 536 nm 73.1 % @ 533 nm

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 800 × 620 px, max. 1578 fps Binning 2×2, 400 × 310 px, max. 1578 fps Binning 2×1, 400 × 620 px, max. 1578 fps Binning 1×2, 800 × 310 px, max. 1578 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 800 × 620 px, max. 1578 fps
Pixel formats	Mono8 Mono10 Mono12 Mono12 Packed

#### Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
-----------------	---

Color models	Mono
--------------	------

Image processing	JPEG
------------------	------

#### Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto
Image Pre-processing	Image Flipping (X/Y) LUT / Gamma JPEG Image Compression
Acquisition / Interface	Burst Mode Adjustable Framerate Short Exposure Time Enable Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

# VLXT-06M.I.JP

Gigabit Ethernet, 0,5 Megapixel, Monochrome

Article number: 11700830

## Technical data

### Camera features

Process Synchronization	Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Action CMD Request ID Trigger ID inside Chunk Additional Output Modes (e.g. Trigger Ready) PWM (PWM Duration / PWM Duty Cycle) Selectable Output format (e.g. Tri State, Push Pull) Chunk data inside transferred image Encoder support via Counter End trigger source 4 power outputs with up to 120 W (max. 48 V / 2.5 A)
Time synchronization IEEE 1588	IEEE 1588 / Master and Slave function IEEE 1588 / Scheduled Action CMD IEEE 1588 / Synchronized Acquisition Framerate
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
Lens control	Corning liquid lens
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor output line ROI Offset x ROI Offset y
Internal image buffer	1024 MB 2096 images (Trigger Mode) 1 image (Free Running Mode)

### Interfaces and connectors

Data interface	10 Gigabit Ethernet, Transfer rate 10000 Mb/s, Gigabit Ethernet, Transfer rate 1000 Mb/s, Fast Ethernet, Transfer rate 100 Mb/s, Connector: M12 / 8-pol x-coded (SACC-CI-M12FS-8CON-L180-10G)
----------------	---

### Interfaces and connectors

Process interface	M12 / 12 pins a-coded (SACC-CI-M12MS-12CON-L180)
Power supply	via M12/12 pins a-coded

### Mechanical data

Lens mount	C-mount
Width	60 mm
Height	60 mm
Depth	99.7 mm
Weight	≤ 485 g
Material	aluminum

### Electrical data

Voltage supply range +Vs	19.2 ... 28.8 V DC (external power supply)
Power consumption	approx. 11.3 W @ 24 VDC and 1578.0 fps

### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

### Environmental conditions

Operating temperature	0 ... +60 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40 IP 54 (with mounted tube and cable) IP 65 (with mounted tube and cable) IP 67 (with mounted tube and cable)

### Digital I/Os

Lines	2 input lines 4 power output lines with pulse width modulation (PWM) (max. 48 V / max. 2.5 A) RS232
-------	---

### Conformity


Conformity	CE RoHS EAC KC (R-R-BkR-VLXT-71MI) UL recognized
------------	--

## VLXT-06M.I.JP

Gigabit Ethernet, 0,5 Megapixel, Monochrome


Article number: 11700830

### Dimension drawing




### Principle

Optional accessories for protection class IP 65/67:




- hard-anodized, incl. sealing and screws  
Ø 49.5 mm (VCXG.I 11185373)  
Ø 65 mm (VCXG.I 11185377)  
Ø 65 mm (VLXT 11193125)

tube



- hard-anodized, cover glass PMMA  
Ø 49.5 mm, length 44 mm (11185370)  
Ø 65 mm, length 58 mm (11185374)
- hard-anodized, tempered laminated safety glass  
Ø 49.5 mm, length 44 mm (11701124)  
Ø 65 mm, length 58 mm (11701125)

distance ring



- hard-anodized, incl. sealing  
Ø 49.5 mm, length 6 mm (11185372)  
Ø 49.5 mm, length 12 mm (11185371)  
Ø 49.5 mm, length 36 mm (11211571)  
Ø 65 mm, length 6 mm (11185376)  
Ø 65 mm, length 12 mm (11185375)  
Ø 65 mm, length 36 mm (111988906)