

## VLXT-126M.I

Gigabit Ethernet, 12,2 Megapixel, Monochrome

Article number: 11702303

### Overview

- 4096 × 2992 px
- Sony IMX535
- 1/1.1" CMOS
- 100 fps
- 10 GigE



GEN*i*CAM



### Technical data

#### Sensor information

Sensor	Sony IMX535 Gen4
Mono/Color	Mono
Sensor type	1/1.1" CMOS
Shutter type	Global shutter
Resolution	4096 × 2992 px
Pixel size	2.74 × 2.74 µm
Exposure time	0.001 ... 60000 ms

#### Data quality (EMVA 1288 typical)

Dark noise	2.44 e-
Saturation capacity	9285 e-
Dynamic range	69.6 dB
Signal-to-noise ratio	39.7 dB
Quantum efficiency	65.4 % @ 535 nm 66.4 % @ 533 nm

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 4096 × 2992 px, max. 100 fps Binning 2×2, 2048 × 1496 px, max. 336 fps Binning 2×1, 2048 × 2992 px, max. 119 fps Binning 1×2, 4096 × 1496 px, max. 119 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 4096 × 2992 px, max. 119 fps

#### Acquisition formats

Pixel formats	Mono8 Mono10 Mono12 Mono12 Packed
---------------	--

#### Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
-----------------	---

Color models	Mono
--------------	------

#### Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image) Multi ROI
-----------------	--

Auto Functions	Exposure Auto Gain Auto
----------------	----------------------------

Image Pre-processing	Image Flipping (X/Y) LUT / Gamma Shading Correction Edge Sharpening Noise Reduction
----------------------	---

Acquisition / Interface	Burst Mode Adjustable Framerate Short Exposure Time Enable Device Link Throughput Limit Internal Image Buffer
-------------------------	---

# VLXT-126M.I

Gigabit Ethernet, 12,2 Megapixel, Monochrome

Article number: 11702303

## Technical data

### Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Process Synchronization	Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Action CMD Request ID Trigger ID inside Chunk Additional Output Modes (e.g. Trigger Ready) PWM (PWM Duration / PWM Duty Cycle) Selectable Output format (e.g. Tri State, Push Pull) Chunk data inside transferred image Encoder support via Counter End trigger source 4 power outputs with up to 120 W (max. 48 V / 2.5 A)
Time synchronization IEEE 1588	IEEE 1588 / Master and Slave function IEEE 1588 / Scheduled Action CMD IEEE 1588 / Synchronized Acquisition Framerate
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
Lens control	Coming liquid lens
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor output line ROI Offset x ROI Offset y
Internal image buffer	1024 MB 84 images (Trigger Mode) 1 image (Free Running Mode)

### Interfaces and connectors

Data interface	10 Gigabit Ethernet, Transfer rate 10000 Mbits/sec, Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer rate 100 Mbits/sec, Connector: M12 / 8-pol x-coded (SACC-CI-M12FS-8CON-L180-10G)
----------------	--

### Interfaces and connectors

Process interface	M12 / 12 pins a-coded (SACC-CI-M12MS-12CON-L180)
Power supply	via M12/12 pins a-coded

### Mechanical data

Lens mount	C-mount
Width	60 mm
Height	60 mm
Depth	99.7 mm
Weight	≤ 485 g
Material	aluminum, hard-anodized

### Electrical data

Voltage supply range +Vs	19.2 ... 28.8 V DC (external power supply)
Power consumption	approx. 12.6 W @ 24 VDC and 100 fps

### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

### Environmental conditions

Operating temperature	0 ... +60 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40 IP 54 (with mounted tube and cable) IP 65 (with mounted tube and cable) IP 67 (with mounted tube and cable)

### Digital I/Os

Lines	2 input lines 4 power output lines with pulse width modulation (PWM) (max. 48 V / max. 2,5 A) RS232
Output line sources	Off Exposure Active Timer1 Readout Active User0 User1 User2 TriggerReady

### Conformity


Conformity	CE RoHS UL recognized
------------	-----------------------------

## VLXT-126M.I

Gigabit Ethernet, 12,2 Megapixel, Monochrome


Article number: 11702303

### Dimension drawing




### Principle

Optional accessories for protection class IP 65/67:




- hard-anodized, incl. sealing and screws  
Ø 49.5 mm (VCXG.I 11185373)  
Ø 65 mm (VCXG.I 11185377)  
Ø 65 mm (VLXT 11193125)



tube

- hard-anodized, cover glass PMMA  
Ø 49.5 mm, length 44 mm (11185370)  
Ø 65 mm, length 58 mm (11185374)
- hard-anodized, tempered laminated safety glass  
Ø 49.5 mm, length 44 mm (11701124)  
Ø 65 mm, length 58 mm (11701125)



distance  
ring

- hard-anodized, incl. sealing  
Ø 49.5 mm, length 6 mm (11185372)  
Ø 49.5 mm, length 12 mm (11185371)  
Ø 49.5 mm, length 36 mm (11211571)
- hard-anodized, incl. sealing  
Ø 65 mm, length 6 mm (11185376)  
Ø 65 mm, length 12 mm (11185375)  
Ø 65 mm, length 36 mm (111988906)