

Overview

- Computar lens
- 25 mm
- F 2,8-16
- format 2/3"
- M.O.D. 0,2 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount C-mount
Dimensions 29 mm × 31.5 mm
Max. outer diameter 29 mm (without knurled screws)
Max. length (excl. thread) 32 mm
Weight ≤ 42 g
Filter thread M 27 × 0,5

Lens data

Lens resolution 6 MP
Pixel resolution 2.74 μm

Lens data

Focal length 25 mm
Focal range ≥ 25 mm ... < 50 mm
Format 2/3"
Aperture F2.8-16
Aperture control Manual
M.O.D. 0.2 m
Horizontal angle of view 19.9 °
Vertical angle of view 15.0 °
Diagonal angle of view 24.6 °
At image format 8,8 × 6,6 mm

Environmental conditions

Operating temperature -10 ... +50 °C