


## EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)" (see [www.standard1288.org](http://www.standard1288.org) or the *Zenodo EMVA 1288 community*) release 3.0 with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 3, 15.08.2015, SN 0001(Baumer), recalibrated 28.08.2017. The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding specification and calibration report.

Measurements performed by Technical and Application Support Center, Baumer Optronic GmbH.



Vendor	Baumer
Model	LXC-500C
Serial number	700004556637
Sensor diagonal	34.49 mm
Lens category	M58 mount
Resolution	5304 × 5300, 12 bit
Pixel size	4.60 μm × 4.60 μm
Sensor	CMOSIS CMV50000
Sensor type	CMOS
Shutter type	Global shutter
Overlap capabilities	Overlapped
Maximum frame rate	0.0 Hz
Interface type	CL

Type of data presented	Single
<b>Operation point 1</b>	
Wavelength centroid	465.2 nm
Wavelength FWHM	20.8 nm
Gain / BlackLevel	1.0 / 254.0
<b>Operation point 2</b>	
Wavelength centroid	535.8 nm
Wavelength FWHM	31.9 nm
Gain / BlackLevel	1.0 / 254.0
<b>Operation point 3</b>	
Wavelength centroid	630.8 nm
Wavelength FWHM	13.3 nm
Gain / BlackLevel	1.0 / 254.0
<b>Optional data measured</b>	
None	



## EMVA 1288 Summary Sheet for Operating Point 1

Type of data	Single	Gain / BlackLevel	1.0 / 254.0
Exposure control	By irradiance	Environmental temperature	27.6°C
Exposure time	875.00 $\mu$ s	Camera body temperature	41.8°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerBG12	Wavelength, centr., FWHM	465 nm, 20.8 nm



### Quantum efficiency

$\eta$  44.8%

### Overall system gain

$K$  0.288 DN/e<sup>-</sup>  
 $1/K$  3.471 e<sup>-</sup>/DN

### Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$  2.38 DN  
 $\text{DSNU}_{1288}$  6.02 DN  
 $\sigma_d$  8.20 e<sup>-</sup>  
 $\text{DSNU}_{1288}$  20.90 e<sup>-</sup>

### Signal-to-noise ratio & PRNU

$\text{SNR}_{\text{max}}$  113  
 41.1 dB  
 6.8 bit  
 $1/\text{SNR}_{\text{max}}$  0.89 %  
 $\text{PRNU}_{1288}$  1.27 %

### Nonlinearity

LE 0.33%  
 $\text{LE}_{\text{min}}$  -0.18%  
 $\text{LE}_{\text{max}}$  0.48%

### Sensitivity & saturation

$\mu_{p,\text{min}}$  19.59 p  
 0.926 p/ $\mu\text{m}^2$   
 $\mu_{p,\text{sat}}$  28486 p  
 1346 p/ $\mu\text{m}^2$   
 $\mu_{e,\text{min}}$  8.77 e<sup>-</sup>  
 0.415 e<sup>-</sup>/ $\mu\text{m}^2$   
 $\mu_{e,\text{sat}}$  12753 e<sup>-</sup>  
 603 e<sup>-</sup>/ $\mu\text{m}^2$

### Dynamic range



DR 1454  
 63.3 dB  
 10.5 bit

### Dark current

$\mu_{c,\text{mean}}$  -0.4 DN/s  
 $\mu_{c,\text{mean}}$  -1.4 e<sup>-</sup>/s  
 $\mu_{c,\text{var}}$  4.7 e<sup>-</sup>/s

## EMVA 1288 Summary Sheet for Operating Point 2



Type of data	Single	Gain / BlackLevel	1.0 / 254.0
Exposure control	By irradiance	Environmental temperature	27.6°C
Exposure time	875.00 $\mu$ s	Camera body temperature	41.8°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerBG12	Wavelength, centr., FWHM	536 nm, 31.9 nm



<b>Quantum efficiency</b>	
$\eta$	48.8%
<b>Overall system gain</b>	
$K$	0.287 DN/e <sup>-</sup>
$1/K$	3.479 e <sup>-</sup> /DN
<b>Temporal dark noise &amp; DSNU</b>	
$\sigma_{y,\text{dark}}$	2.38 DN
DSNU <sub>1288</sub>	6.26 DN
$\sigma_d$	8.23 e <sup>-</sup>
DSNU <sub>1288</sub>	21.79 e <sup>-</sup>
<b>Signal-to-noise ratio &amp; PRNU</b>	
SNR <sub>max</sub>	113
	41.0 dB
	6.8 bit
$1/\text{SNR}_{\text{max}}$	0.89 %
PRNU <sub>1288</sub>	1.37 %
<b>Nonlinearity</b>	
LE	0.43%
LE <sub>min</sub>	-0.23%
LE <sub>max</sub>	0.63%
<b>Sensitivity &amp; saturation</b>	
$\mu_{p,\text{min}}$	18.05 p
	0.853 p/ $\mu\text{m}^2$
$\mu_{p,\text{sat}}$	26110 p
	1234 p/ $\mu\text{m}^2$
$\mu_{e,\text{min}}$	8.80 e <sup>-</sup>
	0.416 e <sup>-</sup> / $\mu\text{m}^2$
$\mu_{e,\text{sat}}$	12734 e <sup>-</sup>
	602 e <sup>-</sup> / $\mu\text{m}^2$
<b>Dynamic range</b>	
DR	1446
	63.2 dB
	10.5 bit
<b>Dark current</b>	
$\mu_{c,\text{mean}}$	0.0 DN/s
$\mu_{c,\text{mean}}$	0.0 e <sup>-</sup> /s
$\mu_{c,\text{var}}$	5.4 e <sup>-</sup> /s

## EMVA 1288 Summary Sheet for Operating Point 3

Type of data	Single	Gain / BlackLevel	1.0 / 254.0
Exposure control	By irradiance	Environmental temperature	27.6°C
Exposure time	875.00 $\mu$ s	Camera body temperature	41.8°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerBG12	Wavelength, centr., FWHM	631 nm, 13.3 nm



### Quantum efficiency

$\eta$  41.4%

### Overall system gain

$K$  0.287 DN/e<sup>-</sup>

1/ $K$  3.484 e<sup>-</sup>/DN

### Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$  2.39 DN

DSNU<sub>1288</sub> 6.24 DN

$\sigma_d$  8.25 e<sup>-</sup>

DSNU<sub>1288</sub> 21.74 e<sup>-</sup>

### Signal-to-noise ratio & PRNU

SNR<sub>max</sub> 113

41.1 dB

6.8 bit

1/SNR<sub>max</sub> 0.88 %

PRNU<sub>1288</sub> 1.50 %

### Nonlinearity

LE 0.26%

LE<sub>min</sub> -0.14%

LE<sub>max</sub> 0.37%

### Sensitivity & saturation

$\mu_{p,\text{min}}$  21.35 p

1.009 p/ $\mu$ m<sup>2</sup>

$\mu_{p,\text{sat}}$  31062 p

1468 p/ $\mu$ m<sup>2</sup>

$\mu_{e,\text{min}}$  8.83 e<sup>-</sup>

0.417 e<sup>-</sup>/ $\mu$ m<sup>2</sup>

$\mu_{e,\text{sat}}$  12847 e<sup>-</sup>

607 e<sup>-</sup>/ $\mu$ m<sup>2</sup>

### Dynamic range

DR 1455

63.3 dB

10.5 bit

### Dark current

$\mu_{c,\text{mean}}$  -0.3 DN/s

$\mu_{c,\text{mean}}$  -0.9 e<sup>-</sup>/s

$\mu_{c,\text{var}}$  4.9 e<sup>-</sup>/s