


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at www.standard1288.org and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 7, 21.08.2018, SN 0001(Baumer).

Measurements performed by Technical and Application Support Center, Baumer Optronic GmbH.


Vendor	Baumer	Type of data presented	Single
Model	VCXG-201C.R.I	Operation point 1	
Serial number	700006295828	Wavelength centroid	465.1 nm
Sensor diagonal	15.78 mm	Wavelength FWHM	20.5 nm
Lens category	C-Mount	Gain, black-level	1.0 / 43.0
Resolution	5472 × 3648, 12 bit	Operation point 2	
Pixel size (h×v)	2.40 μm × 2.40 μm	Wavelength centroid	535.7 nm
Sensor	Sony IMX183	Wavelength FWHM	31.9 nm
Sensor type	CMOS	Gain, black-level	1.0 / 43.0
Shutter type	Rolling shutter	Operation point 3	
Overlap cap.	Overlapped	Wavelength centroid	630.3 nm
Max. frame rate	0.0 Hz	Wavelength FWHM	13.2 nm
Interface type	GEV	Gain, black-level	1.0 / 43.0
		Optional data measured	
		None	




Summary Sheet for Operation Point 1 at a Wavelength of 465 nm

Type of data	Single	Gain, black-level	1.0 / 43.0
Exposure control	By irradiance	Environmental temperature	27.0°C
Exposure time	1.67 ms	Camera body temperature	33.5°C
Frame rate	9.6 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	465 nm, 20.5 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η 62.1%

Overall system gain

K 0.270 DN/e⁻

$1/K$ 3.707 e⁻/DN

Temporal dark noise

σ_d 3.06 e⁻

$\sigma_{y,\text{dark}}$ 0.88 DN

Signal-to-noise ratio

SNR_{max} 121

41.6 dB

6.9 bit

$1/\text{SNR}_{\text{max}}$ 0.83 %

Absolute sensitivity threshold

$\mu_{p,\text{min}}$ 6.09 p

$\mu_{p,\text{min,area}}$ 1.058 p/ μm^2

$\mu_{e,\text{min}}$ 3.78 e⁻

$\mu_{e,\text{min,area}}$ 0.657 e⁻/ μm^2

Saturation capacity

$\mu_{p,\text{sat}}$ 23412 p

$\mu_{p,\text{sat,area}}$ 4065 p/ μm^2

$\mu_{e,\text{sat}}$ 14542 e⁻

$\mu_{e,\text{sat,area}}$ 2525 e⁻/ μm^2

Dynamic range

DR 3843

71.7 dB

11.9 bit

Spatial nonuniformities

DSNU₁₂₈₈ 0.22 e⁻

0.06 DN

PRNU₁₂₈₈ 0.54 %

Linearity error

LE_{min} -0.48%

LE_{max} 1.14%

Dark current

$\mu_{c,\text{mean}}$ 0.71 ± 0.00 e⁻/s

0.19 DN/s


$\mu_{c,\text{var}}$ 0.72 ± 0.00 e⁻/s

T_d — °C


Summary Sheet for Operation Point 2 at a Wavelength of 536 nm

Type of data	Single	Gain, black-level	1.0 / 43.0
Exposure control	By irradiance	Environmental temperature	26.1 °C
Exposure time	3.23 ms	Camera body temperature	32.7 °C
Frame rate	9.6 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	536 nm, 31.9 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η 68.1%

Overall system gain

K 0.268 DN/e⁻

$1/K$ 3.730 e⁻/DN

Temporal dark noise

σ_d 3.08 e⁻

$\sigma_{y,\text{dark}}$ 0.87 DN

Signal-to-noise ratio

SNR_{max} 121

41.6 dB

6.9 bit

$1/\text{SNR}_{\text{max}}$ 0.83 %

Absolute sensitivity threshold

$\mu_{p,\text{min}}$ 5.57 p

$\mu_{p,\text{min,area}}$ 0.968 p/μm²

$\mu_{e,\text{min}}$ 3.80 e⁻

$\mu_{e,\text{min,area}}$ 0.659 e⁻/μm²

Saturation capacity

$\mu_{p,\text{sat}}$ 21459 p

$\mu_{p,\text{sat,area}}$ 3726 p/μm²

$\mu_{e,\text{sat}}$ 14617 e⁻

$\mu_{e,\text{sat,area}}$ 2538 e⁻/μm²

Dynamic range

DR 3850

71.7 dB

11.9 bit

Spatial nonuniformities

DSNU₁₂₈₈ 0.23 e⁻

0.06 DN

PRNU₁₂₈₈ 0.54 %

Linearity error

LE_{min} -0.69%

LE_{max} 1.91%

Dark current

$\mu_{c,\text{mean}}$ 0.74 ± 0.00 e⁻/s

0.20 DN/s


$\mu_{c,\text{var}}$ 0.75 ± 0.00 e⁻/s

T_d — °C


Summary Sheet for Operation Point 3 at a Wavelength of 630 nm

Type of data	Single	Gain, black-level	1.0 / 43.0
Exposure control	By irradiance	Environmental temperature	26.6°C
Exposure time	3.23 ms	Camera body temperature	32.9°C
Frame rate	9.6 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	630 nm, 13.2 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η 51.3%

Overall system gain

K 0.270 DN/e⁻

$1/K$ 3.709 e⁻/DN

Temporal dark noise

σ_d 3.07 e⁻

$\sigma_{y,\text{dark}}$ 0.88 DN

Signal-to-noise ratio

SNR_{max} 121

41.6 dB

6.9 bit

$1/\text{SNR}_{\text{max}}$ 0.83 %

Absolute sensitivity threshold

$\mu_{p,\text{min}}$ 7.39 p

$\mu_{p,\text{min,area}}$ 1.282 p/ μm^2

$\mu_{e,\text{min}}$ 3.79 e⁻

$\mu_{e,\text{min,area}}$ 0.658 e⁻/ μm^2

Saturation capacity

$\mu_{p,\text{sat}}$ 28474 p

$\mu_{p,\text{sat,area}}$ 4943 p/ μm^2

$\mu_{e,\text{sat}}$ 14610 e⁻

$\mu_{e,\text{sat,area}}$ 2536 e⁻/ μm^2

Dynamic range

DR 3855

71.7 dB

11.9 bit

Spatial nonuniformities

DSNU₁₂₈₈ 0.25 e⁻

0.07 DN

PRNU₁₂₈₈ 0.84 %

Linearity error

LE_{min} -0.35%

LE_{max} 0.76%

Dark current

$\mu_{c,\text{mean}}$ 0.72 ± 0.00 e⁻/s

0.19 DN/s

$\mu_{c,\text{var}}$ 0.74 ± 0.00 e⁻/s

T_d — °C