


## EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at [www.standard1288.org](http://www.standard1288.org) and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 7, 21.08.2018, SN 0001(Baumer).

Measurements performed by Technical and Application Support Center, Baumer Optronic GmbH.

Vendor	Baumer
Model	VCXG-201M.R.I
Serial number	700006561943
Sensor diagonal	15.78 mm
Lens category	C-Mount
Resolution	5472 × 3648, 12 bit
Pixel size (h×v)	2.40 μm × 2.40 μm
Sensor	Sony IMX183
Sensor type	CMOS
Shutter type	Rolling shutter
Overlap cap.	Overlapped
Max. frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
<b>Operation point 1</b>	
Wavelength centroid	535.7 nm
Wavelength FWHM	31.9 nm
Gain, black-level	1.0 / 43.0
<b>Optional data measured</b>	
None	







### Summary Sheet for Operation Point 1 at a Wavelength of 536 nm

Type of data	Single	Gain, black-level	1.0 / 43.0
Exposure control	By irradiance	Environmental temperature	26.8°C
Exposure time	1.67 ms	Camera body temperature	32.2°C
Frame rate	9.6 Hz	Internal temperature(s)	—
Data transfer mode	Mono12	Wavelength, centr., FWHM	536 nm, 31.9 nm

#### Photon Transfer



#### Signal-to-Noise Ratio



<b>Quantum efficiency</b>	$\eta$	80.6%
<b>Overall system gain</b>	$K$	0.265 DN/e <sup>-</sup>
	1/K	3.778 e <sup>-</sup> /DN
<b>Temporal dark noise</b>	$\sigma_d$	3.05 e <sup>-</sup>
	$\sigma_{y,\text{dark}}$	0.86 DN
<b>Signal-to-noise ratio</b>	SNR <sub>max</sub>	122
		41.7 dB
		6.9 bit
	1/SNR <sub>max</sub>	0.82 %
<b>Absolute sensitivity threshold</b>	$\mu_{p,\text{min}}$	4.68 p
	$\mu_{p,\text{min,area}}$	0.813 p/ $\mu\text{m}^2$
	$\mu_{e,\text{min}}$	3.78 e <sup>-</sup>
	$\mu_{e,\text{min,area}}$	0.656 e <sup>-</sup> / $\mu\text{m}^2$
<b>Saturation capacity</b>	$\mu_{p,\text{sat}}$	18352 p
	$\mu_{p,\text{sat,area}}$	3186 p/ $\mu\text{m}^2$
	$\mu_{e,\text{sat}}$	14799 e <sup>-</sup>
	$\mu_{e,\text{sat,area}}$	2569 e <sup>-</sup> / $\mu\text{m}^2$
<b>Dynamic range</b>	DR	3918
		71.9 dB
		11.9 bit
<b>Spatial nonuniformities</b>	DSNU <sub>1288</sub>	0.22 e <sup>-</sup>
		0.06 DN
	PRNU <sub>1288</sub>	0.53 %
<b>Linearity error</b>	LE <sub>min</sub>	-0.68%
	LE <sub>max</sub>	1.95%
<b>Dark current</b>	$\mu_{c,\text{mean}}$	0.71 ± 0.00 e <sup>-</sup> /s
		0.19 DN/s
	$\mu_{c,\text{var}}$	0.74 ± 0.01 e <sup>-</sup> /s
	$T_d$	— °C