


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)" (see www.standard1288.org or the *Zenodo EMVA 1288 community*) release 3.0 with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 3, 15.08.2015, SN 0001(Baumer) . The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding specification and calibration report.

Measurements performed by Technical and Application Support Center, Baumer Optronik GmbH.



Vendor	Baumer
Model	VCXG-24C
Serial number	700001878313
Sensor diagonal	13.27 mm
Lens category	C-Mount
Resolution	1920 × 1200, 12 bit
Pixel size	5.86 μm × 5.86 μm
Sensor	Sony IMX249
Sensor type	CMOS
Shutter type	Global shutter
Overlap capabilities	Overlapped
Maximum frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
Operation point 1	
Wavelength centroid	465.3 nm
Wavelength FWHM	20.7 nm
Gain / BlackLevel	1.0 / 39
Operation point 2	
Wavelength centroid	535.8 nm
Wavelength FWHM	32.0 nm
Gain / BlackLevel	1.0 / 39
Operation point 3	
Wavelength centroid	631.0 nm
Wavelength FWHM	13.4 nm
Gain / BlackLevel	1.0 / 39
Optional data measured	
None	



EMVA 1288 Summary Sheet for Operating Point 1

Type of data	Single	Gain / BlackLevel	1.0 / 39
Exposure control	By irradiance	Environmental temperature	25.3°C
Exposure time	837.00 μ s	Camera body temperature	34.4°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	465 nm, 20.7 nm



Quantum efficiency

η 56.2%

Overall system gain

K 0.125 DN/e⁻
 $1/K$ 8.013 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 0.83 DN
 DSNU_{1288} 0.12 DN
 σ_d 6.22 e⁻
 DSNU_{1288} 0.98 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 179
 45.0 dB
 7.5 bit
 $1/\text{SNR}_{\text{max}}$ 0.56 %
 PRNU_{1288} 0.44 %

Nonlinearity

LE 0.40%
 LE_{min} -0.46%
 LE_{max} 0.33%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 12.74 p
 0.371 p/ μm^2
 $\mu_{p,\text{sat}}$ 56781 p
 1654 p/ μm^2
 $\mu_{e,\text{min}}$ 7.16 e⁻
 0.208 e⁻/ μm^2
 $\mu_{e,\text{sat}}$ 31892 e⁻
 929 e⁻/ μm^2

Dynamic range



DR 4456
 73.0 dB
 12.1 bit

Dark current

$\mu_{c,\text{mean}}$ 1.1 DN/s
 $\mu_{c,\text{mean}}$ 8.9 e⁻/s
 $\mu_{c,\text{var}}$ 4.6 e⁻/s

EMVA 1288 Summary Sheet for Operating Point 2

Type of data	Single	Gain / BlackLevel	1.0 / 39
Exposure control	By irradiance	Environmental temperature	25.3°C
Exposure time	837.00 μ s	Camera body temperature	34.4°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	536 nm, 32.0 nm



Quantum efficiency

η 60.9%

Overall system gain

K 0.124 DN/e⁻
 $1/K$ 8.040 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 0.83 DN
 DSNU₁₂₈₈ 0.13 DN
 σ_d 6.27 e⁻
 DSNU₁₂₈₈ 1.02 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 180
 45.1 dB
 7.5 bit
 $1/\text{SNR}_{\text{max}}$ 0.56 %
 PRNU₁₂₈₈ 0.39 %

Nonlinearity

LE 0.33%
 LE_{min} -0.38%
 LE_{max} 0.27%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 11.83 p
 0.344 p/ μm^2
 $\mu_{p,\text{sat}}$ 52940 p
 1542 p/ μm^2
 $\mu_{e,\text{min}}$ 7.21 e⁻
 0.210 e⁻/ μm^2
 $\mu_{e,\text{sat}}$ 32261 e⁻
 939 e⁻/ μm^2

Dynamic range



DR 4476
 73.0 dB
 12.1 bit

Dark current

$\mu_{c,\text{mean}}$ 1.1 DN/s
 $\mu_{c,\text{mean}}$ 9.0 e⁻/s
 $\mu_{c,\text{var}}$ 4.7 e⁻/s

EMVA 1288 Summary Sheet for Operating Point 3

Type of data	Single	Gain / BlackLevel	1.0 / 39
Exposure control	By irradiance	Environmental temperature	25.3°C
Exposure time	837.00 μ s	Camera body temperature	34.4°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	631 nm, 13.4 nm



Quantum efficiency	
η	46.6%
Overall system gain	
K	0.124 DN/e ⁻
1/ K	8.056 e ⁻ /DN
Temporal dark noise & DSNU	
$\sigma_{y,\text{dark}}$	0.83 DN
DSNU ₁₂₈₈	0.11 DN
σ_d	6.30 e ⁻
DSNU ₁₂₈₈	0.91 e ⁻
Signal-to-noise ratio & PRNU	
SNR _{max}	181
	45.1 dB
	7.5 bit
1/SNR _{max}	0.55 %
PRNU ₁₂₈₈	0.51 %
Nonlinearity	
LE	0.55%
LE _{min}	-0.63%
LE _{max}	0.47%
Sensitivity & saturation	
$\mu_{p,\text{min}}$	15.52 p
	0.452 p/ μ m ²
$\mu_{p,\text{sat}}$	69978 p
	2038 p/ μ m ²
$\mu_{e,\text{min}}$	7.24 e ⁻
	0.211 e ⁻ / μ m ²
$\mu_{e,\text{sat}}$	32626 e ⁻
	950 e ⁻ / μ m ²
Dynamic range	
DR	4509
	73.1 dB
	12.1 bit
Dark current	
$\mu_{c,\text{mean}}$	1.1 DN/s
$\mu_{c,\text{mean}}$	9.0 e ⁻ /s
$\mu_{c,\text{var}}$	4.7 e ⁻ /s