


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at www.standard1288.org and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 7, 21.08.2018, SN 0018(AEON).

Measurements performed by Technical and Application Support Center, Baumer Optronic GmbH.

Vendor	Baumer
Model	VCXG.2-51M.XC
Serial number	700009468292
Sensor diagonal	11.01 mm
Lens category	C-Mount
Resolution	2448 × 2048, 12 bit
Pixel size (h×v)	3.45 μm × 3.45 μm
Sensor	Sony IMX264
Sensor type	CMOS
Shutter type	Global shutter
Overlap cap.	Overlapped
Max. frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
Operation point 1	
Wavelength centroid	533.3 nm
Wavelength FWHM	30.3 nm
Gain, black-level	1.0 / 39.0
Optional data measured	
None	







Summary Sheet for Operation Point 1 at a Wavelength of 533 nm

Type of data	Single	Gain, black-level	1.0 / 39.0
Exposure control	By irradiance	Environmental temperature	24.0°C
Exposure time	796.00 μs	Camera body temperature	34.8°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	Mono12	Wavelength, centr., FWHM	533 nm, 30.3 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency	η	64.6%
Overall system gain	K	0.415 DN/e ⁻
	$1/K$	2.408 e ⁻ /DN
Temporal dark noise	σ_d	2.07 e ⁻
	$\sigma_{y,\text{dark}}$	0.91 DN
Signal-to-noise ratio	SNR_{max}	97
		39.7 dB
		6.6 bit
	$1/\text{SNR}_{\text{max}}$	1.03 %
Absolute sensitivity threshold	$\mu_{p,\text{min}}$	4.25 p
	$\mu_{p,\text{min,area}}$	0.357 p/μm ²
	$\mu_{e,\text{min}}$	2.74 e ⁻
	$\mu_{e,\text{min,area}}$	0.230 e ⁻ /μm ²
Saturation capacity	$\mu_{p,\text{sat}}$	14594 p
	$\mu_{p,\text{sat,area}}$	1226 p/μm ²
	$\mu_{e,\text{sat}}$	9421 e ⁻
	$\mu_{e,\text{sat,area}}$	791 e ⁻ /μm ²
Dynamic range	DR	3437
		70.7 dB
		11.7 bit
Spatial nonuniformities	DSNU_{1288}	0.77 e ⁻
		0.32 DN
	PRNU_{1288}	0.59 %
Linearity error	LE_{min}	-0.46%
	LE_{max}	0.93%
Dark current	$\mu_{c,\text{mean}}$	-0.5 ± 0.1 e ⁻ /s
		-0.22 DN/s
	$\mu_{c,\text{var}}$	3.1 ± 0.2 e ⁻ /s
	T_d	— °C