


Magnetic angle sensors

MDRM 18U9504/S14A360

dimension drawing



general data

angular range	360° linear
resolution	1,41 °
system accuracy	± 0,6 %
temperature drift	± 0,1 % (Full Scale)
working distance max.	4 mm, with magnet rotor MSFS
axial misalignment max.	0,5 mm

electrical data

response time	< 2 ms
voltage supply range +Vs	4,75 ... 5,25 VDC
current consumption max. (no load)	20 mA
output signal	0 ... 5 VDC
load resistance	> 1000 Ohm
output circuit	voltage output
short circuit protection	no
reverse polarity protection	no

mechanical data

connection types	connector M12
type	cylindrical threaded
housing material	brass nickel plated
dimension	18 mm
material (sensing face)	PBTP


ambient conditions

operating temperature	-40 ... +85 °C
protection class	IP 67


photo



connection diagram



output signal



Magnetic angle sensors

MDRM 18U9504/S14A360



- Rotor is available as an accessory