

# Operating instructions.

*OM70 laser point / laser line distance sensors*



## Contents

|          |   |           |
|----------|---|-----------|
| <b>1</b> | <b>General information</b> .....                                  | <b>3</b>  |
| 1.1      | Concerning the contents of this document .....                    | 3         |
| 1.2      | Intended use .....  | 3         |
| 1.3      | Safety.....   | 4         |
| <b>2</b> | <b>Quick start-up guide</b> .....                                 | <b>5</b>  |
| <b>3</b> | <b>Mounting and connections</b> .....                             | <b>7</b>  |
| 3.1      | Dimensions .....  | 7         |
| 3.1      | Sensor reference levels .....                                     | 8         |
| 3.2      | Definition of the measuring range.....                            | 9         |
| 3.3      | Mounting .....  | 12        |
| 3.4      | Alignment.....  | 13        |
| 3.5      | Connection.....   | 16        |
| <b>4</b> | <b>Configuration</b> .....  | <b>18</b> |
| 4.1      | Overview of control elements .....                                | 18        |
| 4.2      | Function tree .....   | 21        |
| 4.3      | LIVE MONITOR .....  | 22        |
| 4.4      | PRECISION .....   | 23        |
| 4.5      | ANALOG OUT .....  | 25        |
| 4.6      | DIGITAL OUT.....  | 27        |
| 4.7      | SYSTEM .....  | 31        |
| 4.8      | SETTING .....   | 34        |
| 4.9      | Configuration using the RS-485 interface.....                     | 35        |
| <b>5</b> | <b>Operation</b> .....  | <b>36</b> |
| 5.1      | Measuring frequency, measuring repeat time and response time..... | 36        |
| 5.2      | Alarm output.....   | 36        |
| 5.3      | Influence of ambient light.....                                   | 37        |
| 5.4      | Focus distance and optimal measuring distance.....                | 37        |
| 5.5      | Error correction and tips .....                                   | 39        |
| <b>6</b> | <b>Safety instructions and maintenance</b> .....                  | <b>40</b> |
| 6.1      | General safety instructions .....                                 | 40        |
| 6.2      | Sensor inscriptions .....   | 41        |
| 6.3      | Front optic.....  | 42        |
| 6.4      | Cleaning the sensors .....  | 42        |
| 6.5      | Disposal .....  | 42        |
| <b>7</b> | <b>Sensor data sheet</b> .....                                    | <b>43</b> |
| 7.1      | Measuring range types 30...70 mm .....                            | 43        |
| 7.1      | Measuring range types 40...140 mm .....                           | 46        |
| 7.1      | Measuring range types 50...250 mm .....                           | 49        |
| 7.2      | Measuring range types 100...600 mm .....                          | 52        |
| 7.1      | Measuring range types 100...1000 mm .....                         | 55        |
| 7.2      | Measuring range types 150...1500 mm .....                         | 58        |
| <b>8</b> | <b>Revision history</b> .....                                     | <b>61</b> |

# 1 General information

## 1.1 Concerning the contents of this document

This manual contains information about the installation and initial setup of Baumer OM70 laser point / laser line sensors.

It is a supplement to the mounting instructions supplied with each sensor.




Read these operating instructions carefully and follow the safety instructions!

## 1.2 Intended use

The Baumer OM70 laser point / laser line sensor measures distances to objects. It was specially developed for easy handling, flexible use, and highly accurate measurement.

### 1.2.1 Functional principle of triangulation




In the triangulation principle, the sensor transmits a light point or light beam to the object to be measured, and the reflected light strikes a receiver line in the sensor at a special angle. Depending on the distance, the angle of incidence changes and thus so does the position of the light spot or light beam on the receiver. The micro-controller allows the suppression of interfering reflections, thus providing reliable data even on critical surfaces.

### 1.2.2 Laser point or laser line


#### OM70 laser point

For small objects, if accurate positioning of the laser point is important, or for sharp transitions, a sensor with a laser point is suitable.



#### OM70 laser line

Stable measurements on rough surfaces and textured color surfaces thanks to a fine laser line < 10 mm



### 1.3 Safety



#### NOTE

Provides helpful operation instructions or other general recommendations.




#### ATTENTION!

Indicates a potentially hazardous situation. Avoid these situations in order to prevent any personal injury or damage to the device.

## 2 Quick start-up guide


After connection and installation, the sensor is configured using the display. The sensor is then ready for operation and shows the measured value in mm on the screen. Optionally, the analog output can also be limited or the switching output configured.



### 1 Connection

Connect the sensor according to the connection diagram. A shielded connection cable (8-pole M12) must be used.

When everything is correctly connected, the sensor starts up.



#### Key functions

- ESC = Back
- ESC 2 sec. = Run mode
- UP = Up/increase value
- DOWN = Down/decrease value
- SET = OK
- SET 2 sec. = Save value

Slide over all 4 keys:

- > = Enables the panel if locked
- <---- = Jump to run mode



#### Setting the language


The language is selected and confirmed by pressing SET for 2 seconds.

- English
- Deutsch
- Italiano
- Français

## 2 Installation

For standard applications, the sensor is mounted and aligned at right angles to the measuring axis. See Alignment Chapter.

The object must be within the measuring range  $M_r$ , i.e. between the start of the measuring range  $S_{dc}$ , and the end of the measuring range  $S_{de}$ .



## 3 Application-specific settings

The sensor indicates the distance to the object, measured from the front surface.

### Precision (filter)

To achieve better resolution, it is possible to alternate between Standard, High, Very High and Highest by filtering the output values.

### Analog Out

With SCALE OUT, the start of measuring range  $S_{dc}$  and the end of measuring range  $S_{de}$  can be changed, thus optimizing resolution and linearity of the analog output. 0V or 4 mA apply for the start of measuring range  $S_{dc}$ , and 10V or 20 mA apply for the point at the end of measuring range  $S_{de}$ . The voltage or current output is also selected under ANALOG OUT. The characteristic curve can also be inverted under CHARACTERISTIC.


### Digital output (switching point)

The sensor is equipped with a switching output that can be configured either as a THRESHOLD or as a WINDOW using the DIGITAL OUT function.

**Threshold:** As soon as the measured value exceeds the specified threshold, the switching output is switched.

**Window:** As soon as the measured value is outside the specified window, the switching output is switched. The output level can also be inverted and the hysteresis set here.


|              |  |   |
|--------------|--|---|
| LIVE MONITOR |  |   |
| PRECISION    | Standard<br>High<br>Very High<br>Highest |   |
| ANALOG OUT   | SCALE OUT                                | DIST NEAR<br>DIST FAR<br>SET MAX VALUES |
|              | ANALOG OUT                               | Current / Voltage                       |
|              | CHARACTERISTIC                           | Pos. slope / Neg. slope                 |
| DIGITAL OUT  | DIGITAL OUT                              | Point / Window                          |
|              | SWITCH POINT                             | Value in mm                             |
|              | WINDOW P1                                | Value in mm                             |
|              | WINDOW P2                                | Value in mm                             |
|              | OUTPUT LEVEL                             | Active high / Active low                |
|              | HYSTERESIS                               | Value in mm                             |



## 4 Let's get started


The sensor continuously shows the measured value in mm on the display and transmits it to the controller through the analog output. Alternatively, the measuring value can also be retrieved from the RS-485 interface.

### 3 Mounting and connections



**ATTENTION!**  
 Connection, installation and commissioning may only be performed by qualified personnel. Protect optical surfaces from moisture and dirt.

#### 3.1 Dimensions




\*Optical axis

### 3.1 Sensor reference levels

The sensor can be aligned by the following surfaces:


The laser beam of the sensor runs parallel ( // ) to level R3 and is at a right angle to levels R1 and R2. Levels R1, R2, and R3 serve as a reference for sensor alignment during installation.





### 3.2 Definition of the measuring range

The sensor measures distances within the measuring range. The important definitions are described in the following figure. The reference level R2 applies as a reference for 0.



#### 3.2.1 Blind region

The area from the reference level R2 up to the start of measuring range Sdc is called the blind region, the sensor cannot detect any objects there.

If there are any objects in this region, this can lead to incorrect measured values.



#### NOTE



See chapter ANALOG OUT for further information on the analog output.

### 3.2.2 Transmitter and receiver axis

The transmitter and receiver axes must not be covered by obstacles, since this could adversely affect precise measurements.



### 3.2.3 qTarget

The field of view is aligned with the housing reference surfaces at the factory. The beam position is in the same place for every sensor, which simplifies planning and sensor replacement.




### 3.3 Mounting

The sensor has four mounting holes for flexible alignment and mounting. The use of 2 M4x35 screws as well as suitable washers is recommended for mounting. The tightening torque is max. 1.2 Nm.



#### 3.3.1 Mounting kit for standard installation Order no. 11120705

With the mounting bracket for standard installation, the sensor can be mounted quickly and easily at a 90° angle to the reference surface.



#### Mounting kit 11120705


Contents of this set:

- 90° mounting bracket
- Threaded plate
- 2x spherical head screw M4x35 Torx
- 1x Torx tool T20

### 3.4 Alignment


To achieve as reliable and exact measured values as possible, the following hints and tips for mounting should be followed.

#### 3.4.1 Steps / edges




If measurements are carried out directly beside steps/edges, make sure that the reception beam is not covered by the step/edge. The same applies when the depth of holes and cracks is measured.

#### 3.4.2 Shiny surfaces




With shiny surfaces, it is important to ensure that the direct reflection does not strike the receiver. This can be prevented by tilting the sensor slightly. To check this, place a sheet of white paper on the disc of the receiver; the direct reflection can then be seen clearly.


#### 3.4.3 Round, shiny surfaces




With round, shiny surfaces, the sensor should be aligned in the same axis as the round object in order to avoid reflections.

**3.4.4 Shiny objects with evenly aligned structure**


Particularly with shiny objects, for example turned parts, ground surfaces, extruded surfaces and the like, the installation position affects the measuring result.


**3.4.5 Objects with evenly aligned colored edges**


In the correct orientation, the influence on the measuring accuracy is low. In the wrong orientation, the deviations depend on the differences in reflectivity of the various colors.

**3.4.6 Moving objects**



If the contour of an object is measured, it is important to ensure that the object moves at right angles to the sensor, to avoid shadowing and reflections on the receiver.

**3.4.7 Protection from ambient light**




When installing optical sensors, it is important to ensure that there is no strong ambient light in the area of detection of the receiver.

**3.4.8 Reciprocal influence**




If several optical sensors are used, they may mutually influence one another. During installation, ensure that only the sensor's own laser spot is in the detection range of the receiver. Up to a measuring range of 600 mm, the sensors can be lined up in a row without them influencing each other (picture in the middle). If the mutual interference cannot be avoided through installation, the sensors can be operated asynchronously using the Sync-In input, see chapter TRIGGER MODE.


### 3.5 Connection




**ATTENTION!**  
Incorrect supply voltage will destroy the device!



**ATTENTION!**  
Connection, installation and commissioning may only be performed by qualified personnel.





**ATTENTION!**  
The IP protection class is valid only if all connections are connected as described in the technical documentation.




**ATTENTION!**  
Products with laser class 1 laser beams in accordance with EN 60825-1:2014 can be operated safely without additional safety precautions. Nevertheless direct contact between the eye and beam should be avoided.

#### 3.5.1 Pin assignment and connection diagram

|       | Color       | Function | Description                          |
|-------|-------------|----------|--------------------------------------|
| Pin 1 | WH = white  | Rx/Tx-   | RS 485 receive/transmit- (B)         |
| Pin 2 | BN = brown  | + Vs     | Voltage supply (+15...+28 VDC)       |
| Pin 3 | GN = green  | analog   | Analog output (4...20 mA or 0...10V) |
| Pin 4 | YE = yellow | out      | Switching output, push-pull          |
| Pin 5 | GY = gray   | alarm    | Alarm output, push-pull              |
| Pin 6 | PK = pink   | Rx/Tx+   | RS-485 receive/transmit+ (A)         |
| Pin 7 | BU = blue   | 0V       | Ground GND                           |
| Pin 8 | RD = red    | sync in  | Input synchronization                |



Top view of plug



**NOTE**  
We recommend that you connect unused cables to GND (0V).



### 3.5.2 Connection cable

An 8-pole, shielded connection cable (connector) is required.

Baumer connection cables with the following order codes are recommended:

- 10127844 ESG 34FH0200G (length 2 m, straight plug)
- 11053961 ESW 33FH0200G (length 2 m, angled plug)
- 10129333 ESG 34FH1000G (length 10 m, straight plug)
- 10170054 ESW 33FH1000G (length 10 m, angled plug)

Other cable lengths are available.

When the analog output is used, the cable length affects signal noise. Signal noise increases the longer the connection cable is.

#### Analog output I\_OUT

Noise: 5.92  $\mu$ A (1 sigma) (10m cable and 680 Ohm)  
3.59  $\mu$ A (1 sigma) (2m cable and 680 ohms)


#### Analog output U\_OUT

Noise: 4.80 mV (1 sigma) (10m cable and 100 kOhm)  
3.03 mV (1 sigma) (2m cable and 100 kOhm)


We recommend that you use the RS-485 interface for high-precision applications.

## 4 Configuration



### 4.1 Overview of control elements



#### 4.1.1 Display modes

|  |   |  |
|--|---|--|
| 112,422 mm   |   | <b>Run mode</b><br>The sensor is in run mode, the measuring value is displayed in large characters.  |
| DISTANCE<br>112,422 mm   |   | <b>Main menu</b><br>In the main menu the active mode is displayed at the top, and the measuring value is displayed at the bottom.  |
| PRECISION<br>STANDARD  | ▮ | <b>Scroll bar</b><br>The square on the right indicates the position within the current menu. The next menu item can be accessed using the arrow keys.  |
| PRECISION<br>VERY HIGH   | ▮ | <b>Change value</b><br>If the function/mode at the top is highlighted in black, the value of the lower line can be adjusted using the UP/DOWN keys and saved with SET (hold).                        |
| OK   |   | <b>Process successful</b><br>The display background lights up green: Value successfully saved  |
| FAILURE  |   | <b>Error</b><br>The display background lights up red: Error during the save process or wrong value entered.  |
|  |   | <b>Setting mode</b><br>As soon as the sensor is in setup mode, the display background lights up blue.  |
| ⊙<br>112,422 mm  |   | <b>Keys locked</b><br>If this symbol is on the left side of the screen, the four pushbuttons are locked for operation.   |
| DISTANCE <br>112,422 mm |   | <b>Warming up</b><br>The warm-up sign appears in the top right of the display. The sensor is not yet in thermal equilibrium; optimum measurement performance is reached after the symbol disappears. |

#### 4.1.2 Functions of the individual keys

| Key  | Pressed briefly         | Pressed >2 s.    |
|--|-------------------------|------------------|
| ESC  | Back                    | Jump to run mode |
| UP    | Up/increase value       |                  |
| DOWN  | Down/decrease value     |                  |
| SET  | OK/submenu/next entry** | Save new value*  |


\*Only in setup mode menu when the top line is highlighted in black (change value)

\*\*When entering strings of numbers, use OK to jump to the right. Once the end is reached, the cursor jumps back to the left to the beginning

#### 4.1.3 Locking the touch panel

The keys on the control panel are locked when they are not pressed for 5 minutes. A key symbol appears, and the measuring value is displayed in large lettering.

When it is pressed, the following text appears:




To re-enable the touch panel, it is required to quickly slide a finger over all four keys from left to right (slide over ESC, UP, DOWN, and SET).



#### When controlled via RS-485:


When the sensor is controlled using RS-485, it cannot be operated with the display at the same time. The keys are disabled. When the keys are pressed, the following text appears on the display:



Disconnect briefly from the power supply or use an RS-485 command to enable the display and operate the sensor using the display.

#### Locking via RS-485 command:

The sensor keys can be permanently locked with a RS-485 command. This locking remains activated even if the sensor is no longer controlled via RS-485. The keys must be unlocked with a RS-485 command. When the locked keys are touched, the following text appears on the display:



**4.1.4 Further key functions**

| Action                                 | Reaction  |
|--|---|
| Slide over all keys from left to right | <b>Unlock locked touch panel</b><br>Only if touch panel is locked |
| Slide over all keys from right to left | <b>Jump directly to run mode</b><br>Can be used from any menu     |


**4.1.5 LEDs on the sensor**

| LED           | Lights up  | Flashes   |
|---------------|--|---|
| <b>Yellow</b> | <b>out1 activated</b><br>Switching output1 active  | -   |
| <b>Red</b>    | <b>out2 activated</b><br>Alarm output active. No measuring object within the field of measurement or signal quality is inadequate. | <b>Insufficient excess gain</b><br>Object close to signal reserve or signal quality not ideal |
| <b>Green</b>  | <b>Supply voltage</b><br>Sensor ready for operation.   | <b>Short circuit</b><br>Check connection at switch or alarm output.                           |




## 4.2 Function tree

The menu that can be accessed via the touch panel is shown below.



### 4.3 LIVE MONITOR

The installation conditions can be checked quickly and easily by displaying the lighting reserve as well as the measuring frequency.



#### 4.3.1 Lighting reserve

This factor specifies by how many times an object may become darker in order to obtain a valid measurement nevertheless. For a valid measurement, a minimum of factor 1 is required.

The higher this value is, the shorter the object has to be exposed, which increases the measuring frequency. Below factor 1, the sensor gets too little light back and does not specify any measured value, the alarm output is active.

#### 4.3.2 Measuring frequency in Hz

Displays the current measuring frequency in Hz.

For more information, see the chapter on measuring frequency, measuring repeat time and response time.

#### NOTE



For the fastest response time as well as maximum exposure reserve, the object should be as bright as possible (not shiny).

## 4.4 PRECISION

Activating filtering can reduce noise and thus increase resolution and repeat accuracy. This increases the response time, but the measuring frequency remains unchanged.

|           |   |
|-----------|---|
| Standard  | = normal resolution <sup>12</sup>                         |
| High      | = resolution is approximately twice as high <sup>12</sup> |
| Very high | = resolution about three times as high <sup>12</sup>      |
| Highest   | = resolution about four times as high <sup>12</sup>       |


### 4.4.1 Influences of the PRECISION filter

The higher the precision is set, the more response times and release times increase, which means that the response time for moving objects slows down. The measuring frequency is not affected by the use of this filter.

PRECISION works with moving median as well as moving average filters.

#### Moving median

The median of a finite list is the measurement with the middle measured value of a string of numbers (e.g. median of {3, 3, 5, 9, 11} is 5). The number of measured values saved in an array is called the number of measured values, e.g. {3, 3, 5, 9, 11} corresponds to 5 measured values. When a new measured value is added, the oldest is removed (moving filter). A sudden change in measured values will only lead to a changed after half of the saved number of measured values (e.g. number of measured values = 5 means that the measured value at the output is only affected after 3 measured values).




This diagram shows the effects of the median (number of measured values 5). The filter is used to suppress measurement errors. The output only changes after a defined number of measured values (number of measured values/2). The measuring frequency is not affected by this filter, but the response time is.

<sup>1</sup> In accordance with chapter Sensor Data Sheet

<sup>2</sup> Depending on the object to be measured

### Moving average

The output value of the moving average filter is the average of the defined number of measured values which have been saved. When a new measured value is added, the oldest is removed (moving filter).



As shown in the diagram, the moving average evens out the output value. In contrast to the median filter, it is possible that with the moving average, the displayed measured values were never measured as such. The measuring frequency is not affected by this filter, but the response time is.

Number of measured values required until the correct measured value is displayed:

- In the PRECISION = HIGH mode, the distance must be stable for 4 + 16 measured values before the correct value is displayed
- In the PRECISION = VERY HIGH mode, the distance must be stable for 8 + 128 measured values before the correct value is displayed

### Example

Calculate the response time with a measurement frequency of 500 Hz, PRECISION = VERY HIGH

$$1 / 500 \text{ Hz} = \mathbf{0.002 \text{ s}}$$

$$\text{Median} = 9 / 2 \text{ (formula: measured value} / 2 \text{)} = 4.5 = 5$$

$$\text{Average} = \mathbf{16}$$

$$\text{Response time} = \mathbf{0.002 * (5 + 16) = 0.042 \text{ s} = 42 \text{ ms}}$$




## 4.5 ANALOG OUT

The settings of the analog output are defined here.

The display shows the sensitivity of the analog output in  $\mu\text{A}/\text{mm}$  or  $\text{mV}/\text{mm}$  (depending on the setting ANALOG OUT current/voltage). Adjusting the analog calibration curve using DIST NEAR and DIST FAR changes the displayed sensitivity value of the analog output. This value can be used to convert the analog signal ( $\mu\text{A}/\text{mm}$  or  $\text{mV}/\text{mm}$ ) into a value in mm or vice versa.

### 4.5.1 SCALE OUT

In the factory setting, the analog output runs across the entire measuring range  $M_r$  (start of measuring range  $S_{dc}$  - end of measuring range  $S_{de}$ ) from 0...10V (voltage mode) or from 4...20mA (current mode). The start and end of the measuring range can be reset (taught) with SCALE OUT, reducing the measuring field and changing the calibration curve.



#### 4.5.1.1 DIST NEAR

Scaled start of measuring range  $S_{dc}$  in mm for analog output value 4 mA / 0V.

DIST NEAR  $\geq$  Start of measuring range  $S_{dc}$

DIST NEAR  $\leq$  DIST FAR (observe the minimum analog output window size)

#### 4.5.1.2 DIST FAR

Scaled end of measuring range  $S_{de}$  in mm for analog output value 20 mA/10V.

DIST FAR  $\leq$  End of measuring range  $S_{de}$

DIST FAR  $\geq$  DIST NEAR (observe the minimum analog output window size)

#### 4.5.1.3 SET MAX VALUES

SCALE OUT is reset to the standard setting (maximum measuring field) with the "set max values" command.

#### Example Scaling the measuring range with SCALE OUT

The sensor should display 4 mA at a distance of 110 mm and 20 mA at a distance of 140 mm.

Set DIST NEAR to 110 mm

Set DIST FAR to 140 mm

#### NOTE



As soon as the alarm output is active, the analog and switching outputs for 75 measuring cycles are kept at the last valid value. See chapter Alarm Output.


#### 4.5.2 ANALOG OUT

The analog output can be reset to voltage (0-10 V ) or current (4-20 mA), depending on the intended purpose. In order to minimize interference in the wiring, we recommend using the current output.

- Current
- Voltage

#### 4.5.3 CHARACTER.

The calibration curve can be inverted here. In a positive curve, the output signal increases when the measured value rises, while the output signal decreases in a negative curve.




## 4.6 DIGITAL OUT

With Pin 4 (out), the user has a configurable switching output.

This can be defined as a threshold or as a window. Pin 4 switches as soon as the defined values are exceeded or undershot.

The switching points can be set within as well as outside the analog measuring field limited by SCALE OUT, as long as they are within the maximum measuring range (see also SCALE OUT).

For a reliable switching signal, there is an adjustable hysteresis.



### 4.6.1 DIGITAL OUT

Whether Pin 4 is to be operated as a **threshold** or as a **window** is defined here.

### 4.6.2 THRESHOLD

The switching point is defined from the sensor reference level in mm. The point must be within the measuring field, but is independent of the analog measuring field SCALE OUT.

### 4.6.3 WINDOW P1

Window Point 1 (for WINDOW) is defined from the sensor reference level in mm. The point must be within the measuring range and must be smaller than WINDOW P2, but is independent of the analog measuring field SCALE OUT.

See the minimum digital output window size in accordance with chapter Sensor Data Sheet.

### 4.6.4 WINDOW P2

Window Point 2 (for WINDOW) is defined from the sensor reference level in mm. The point must be within the measuring range and must be greater than WINDOW P1, but is independent of the analog measuring field SCALE OUT.

See the minimum digital output window size in accordance with chapter Sensor Data Sheet.


#### 4.6.5 LEVEL

The output level can be inverted with **active high** or **active low** here. The inversion applies equally to the yellow LED on the sensor.

#### 4.6.6 HYSTERESIS


The hysteresis is the difference between the switching point and the reset point, and is specified as a value in mm. Without hysteresis,  $H$  objects in the border area of the switching point could lead to the switching output switching on and off continuously, or to bouncing. For reasons of reliability, the use of hysteresis is recommended (at least as great as the resolution of the sensor).

With THRESHOLD, a positive value (+) means away from the sensor, with WINDOW towards the outside. A negative value (-) means closer to the sensor (THRESHOLD), or inside (WINDOW).




**Behavior of the switching output for THRESHOLD**

Example: HYSTERESIS positive




Example: Hysteresis negative




**Behavior of the switching output for WINDOW**

Example: HYSTERESIS positive



Example: Hysteresis negative



## 4.7 SYSTEM

### 4.7.1 TRIGGER MODE

In **Continuous** mode, the sensor measures permanently as long as the Sync line is set to Low. As soon as the Sync line is set to High, the sensor goes into hold mode shows no new measured values (the last measured value is frozen), the laser is disabled.

In **Single shot** mode the sensor measures exactly once on the trailing edge of the Sync signal and outputs the value. In single-shot measurements, the preset filters (see chapter PRECISION) have no effect.

#### Properties

- The previous measurement cycle is always completed first, even if Sync-In is on high
- While Hold is high, all outputs are frozen at their last state
- During the waiting time (Hold) the power of the laser beam is reduced (Laser off)
- Sync-In must remain on low for at least 5  $\mu$ s in order for the sensor to begin measuring again

| Sync-In      | Level                        | Measurement |
|--------------|------------------------------|-------------|
| Sync-In low  | 0...2.5 V                    | Run         |
| Sync-In high | 8 V...UB (operating voltage) | Hold        |

#### NOTE



As soon as the Sync-In is set to high (Hold), all output functions are frozen at their last state until the next measurement, and the laser is switched off.

#### 4.7.2 RS485 BAUD

The baud rate is the number of symbols transmitted per second. The baud rate of data transmission must be identical on the transmit and receive sides.

The sensor can be operated at the following baud rates:

- 38400
- 57600
- 115200
- 230400
- 460800
- 921600
- 1500000

#### 4.7.3 RS485 ADDR

Every sensor has its own RS485 address, allowing the selected sensor to be addressed directly. This address is preset to 001 and can be changed in 3 digits. Sensors must not have the same address in the same network, to prevent the occurrence of bus conflicts. No more than 32 sensors may be connected to one bus.

#### 4.7.4 SENSOR INFO

The sensor type and serial number are displayed here to enable clear identification of the sensor.

- SENSOR TYPE
- SERIAL NUMBER

#### 4.7.5 LANGUAGE

Language selection:

- English
- Deutsch
- Italiano
- Français



#### 4.7.6 RESET (factory settings)

This resets all settings in sensor parameters to the factory settings.

|                   |  |
|-------------------|--|
| PRECISION         | = Very high  |
| SCALE OUT         | = Max. values  |
| ANALOG OUT        | = Current  |
| CALIBRATION CURVE | = Positive sensitivity                                 |
| DIGITAL OUT       | = THRESHOLD (set to the center of the measuring range) |
| WINDOW P1         | = Start of measuring range $S_{dc} + 10$ mm            |
| WINDOW P2         | = End of measuring range $S_{de} - 10$ mm              |
| LEVEL             | = Active High  |
| HYSTERESIS        | = % Mr   |
| TRIGGER MODE      | = continuous   |
| RS485 lock        | = 1 (activated)  |
| RS485 BAUD        | = 57600  |
| RS485 ADR         | = 1  |
| ANALOG OUT        | = Current  |

#### NOTE



With "Reset", the current configuration in the sensor is overwritten and the stored configurations are also deleted from the memory. The unit is reset to the factory settings.

## 4.8 SETTING

The settings entered in the sensor can be applied, stored or displayed here.

### 4.8.1 APPLY

The settings saved under SAVE can be activated here.

- Setting 1
- Setting 2
- Setting 3

### 4.8.2 SAVE

The settings entered in the sensor can be stored here.

Three storage spaces are available.

- Setting 1
- Setting 2
- Setting 3

### 4.8.3 SHOW

SHOW

Displays the setting values.


SHOW Active

Displays the active settings.

SHOW settings 1-3

Displays the settings stored in storage spaces 1-3

The values are displayed successively; it is possible to jump to the next value using the DOWN key.



PRECISION  
DIST NEAR  
DIST FAR  
ANALOG OUT  
CHARACTER.  
DIGITAL OUT  
THRESHOLD  
WINDOW P1  
WINDOW P2  
LEVEL  
HYSTERESIS  
TRIGGER MODE

#### 4.9 Configuration using the RS-485 interface

The precision (resolution, repeat accuracy and linearity) of the output values is higher through RS-485 than through the analog output. The use of this interface is recommended for high-precision applications. No more than 32 sensors may be connected to one bus during operation with RS-485.

When the RS-485 interface is activated, the analog output, digital output and alarm output are deactivated or switched as if there were no object within the measuring range. Then the sensor can only be configured through RS-485; the display is locked for operation.


If required, the digital outputs as well as the display control can be reactivated using the relevant RS-485 commands.

See separate RS-485 manual for further information.

## 5 Operation

### 5.1 Measuring frequency, measuring repeat time and response time

A complete measuring cycle consists of exposure, calculation and measuring value display. In order to increase the measuring speed, process steps are executed simultaneously.



#### 5.1.1 Measuring frequency and measuring repeat time

The time between two exposure times is referred to as measuring repeat time. This time can be converted into a frequency (Hz), which indicates how many measured values can be issued by the sensor in one second.

$$\text{Measuring frequency [kHz]} = 1 / \text{measuring repeat time [ms]}$$

#### 5.1.2 Automatic exposure control

The color and surface of the object have an influence on the amount of reflected light. A longer exposure time is required for dark objects than for light objects. The sensor automatically controls the exposure time on the basis of the amount of light reflected by the object. This slows down the measuring frequency and the response time. In this case, the degree of slowdown is dependent on the laser class of the sensor.

## 5.2 Alarm output

The alarm signal is output as a push-pull signal (active high) when the object is outside the measuring range or the signal quality is insufficient for evaluation. If the signal quality is insufficient, the analog and switching outputs for 75 measuring cycles are kept at the last valid value. After this time has elapsed, the analog and switching outputs are set as if an object were at the start of the measuring range.

#### NOTE



As soon as the alarm output is active, the analog and switching outputs for 75 measuring cycles are kept at the last valid value.

### 5.3 Influence of ambient light

Ambient light from lamps, the sun, etc. in the view field of the sensor can lead to malfunctions or a reduction of accuracy and should be avoided as much as possible.


### 5.4 Focus distance and optimal measuring distance

The size of the light spot can have a large influence on the measurement accuracy. The measured value will not always be stable when the surface moves sideways, especially with surfaces that are inhomogeneous in color or structure. The reason for this is the so-called color edge effect. Differences in the reflectivity or gloss of the surface lead to a shift in the measured light distribution and thus to a distorted measured value.

#### 5.4.1 Inhomogeneous surfaces and colored edge effect

The colour edge effect occurs with inhomogeneous surfaces. The measured value is distorted by the light/dark surface and changes when the inhomogeneous object is moved across the laser beam.

**Color edge effect:**




**Examples for inhomogeneous objects:**



### 5.4.2 Influence of the light spot size

The size of the light spot has a great influence on the colour edge effect. This influence can be greatly minimized by a small light spot and thus the accuracy of the measured value can be improved.



The focus distance determines the smallest light spot diameter, around this focus point lies the optimal measuring distance  $S_{do}$ , in which the light spot is very small.

#### Summarized:

- To measure inhomogeneous surfaces robustly and accurately, it is recommended to measure as close as possible to the sensor and as close as possible to the focus point
- If the entire measuring range is to be used, it is recommended to use the sensor type with the focus point as far away from the sensor as possible

## 5.5 Error correction and tips

| Error   | Error correction  |
|---|---|
| No function   | <ul style="list-style-type: none"> <li>• Check connection. Power supply 15...28 VDC on pin 2 (+Vs, brown) and pin 7 (GND, blue)</li> </ul>  |
| Green LED flashes   | <ul style="list-style-type: none"> <li>• Short circuit on switching outputs. Check connection.</li> </ul>   |
| Red LED lights up   | <ul style="list-style-type: none"> <li>• Object outside measuring field (near, far or to the side)</li> <li>• Amplitude of the received signal is insufficient (e.g. in case of soiling)</li> </ul>   |
| Touch panel cannot be operated  | <ul style="list-style-type: none"> <li>• Touch panel locked. Re-enable panel for operation by sliding a finger over the 4 keys from left to right.</li> <li>• RS-485 controls the sensor--&gt; operation via the touch panel not possible at the same time</li> <li>• RS-485 locks the touch keys--&gt; the touch panel was locked via RS-485 and can only be re-enabled with a command via RS-485</li> </ul> |
| Touch panel does not react  | <ul style="list-style-type: none"> <li>• Clean panel. The panel is dirty or wet, which makes it harder to press the keys</li> </ul>   |
| Sensor does not provide the expected measuring results                  | <ul style="list-style-type: none"> <li>• The object is not in the measuring range</li> <li>• Bright object, avoid direct reflexes from the transmitter to the receiver</li> </ul>   |
| Unreliable measuring value:<br>The measuring value jumps back and forth | <ul style="list-style-type: none"> <li>• The object is not in the measuring range</li> <li>• Avoid bright object</li> <li>• Avoid very dark object</li> <li>• Too much ambient light</li> </ul>   |
| Transmitting laser light is dim   | Sync-In input is on High--> set to Low  |

## **6 Safety instructions and maintenance**

### **6.1 General safety instructions**

#### **Intended use**

This product is a precision device and is used for object detection and the preparation and/or provision of measuring values as electrical quantities for a subsequent system. Unless this product is specially labeled, it must not be used for operation in potentially explosive environments.

#### **Commissioning**

Installation, mounting and adjustment of this product may be performed only by a qualified person.

#### **Installation**


For mounting, use only the mechanical mountings and mechanical mounting accessories intended for this product. Unused outputs must not be wired. In cable versions with unused cores, these cores must be insulated. Always comply with admissible cable bending radii. Prior to electrical connection of the product, the system must be disconnected from the power supply. In areas where shielded cables are mandatory, they must be used as protection against electromagnetic disturbances. If the customer makes plug connections to shielded cables, an EMC version of the connectors should be used, and the shield must be connected to the connector housing across a large area.


#### **Caution**

Deviation from the procedures and settings specified here can lead to hazardous radiation effects.



## 6.2 Sensor inscriptions



|                               |  |   |
|-------------------------------|--|---|
| Information and warning plate | <p><b>Class 1: No risk for eyes</b></p> <div style="border: 2px solid black; padding: 5px; display: inline-block;"> <p><b>CLASS 1 LASER PRODUCT</b></p> </div> <p>Class 1 lasers are safe under reasonably foreseeable operational conditions of normal use, including direct long-term viewing of the beam, even when exposure occurs using a magnifying optic.</p> | <p><b>Class 2:</b></p> <div style="border: 2px solid black; padding: 5px; display: inline-block;">  </div> <p>Accidental short-term exposure (up to 0.25 s) does not damage the eye, because the corneal reflex can automatically protect the eye sufficiently from longer radiation. Class 2 lasers may be used without any further protection if intentional staring into the beam is not required for the application.</p> |
|                               | FDA certification plate  | <p>IEC 60825-1/2014<br/>Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019</p>   |

### 6.3 Front optic

In the event of a broken front optic, defective display, or loose or exposed laser lens, the sensor must be disconnected from the power supply immediately. It must not be put into operation again. Non-compliance with these safety instructions may lead to the release of hazardous laser beams.

**ATTENTION!**

The use of a sensor with a broken front optic or loose or exposed lens can lead to hazardous laser radiation.

### 6.4 Cleaning the sensors

The laser distance sensors do not require any maintenance, except that the front window must be kept clean. Dust and fingerprints can impair sensor function. It is normally sufficient to wipe the windows with a dry, clean (!), soft lens cleaning cloth. Alcohol or soapy water can be used in case of severe soiling. The display and the keys must be kept free from dirt and moisture. Water and dirt on the keys can impair their function.

### 6.5 Disposal

This sensor contains electronic components. Dispose of parts according to country-specific provisions.

## 7 Sensor data sheet

### 7.1 Measuring range types 30...70 mm

| General data  | 11200060<br>Laser class 1<br>Laser point<br>Focal dist. 48 mm   | 11200056<br>Laser class 1<br>Laser line<br>Focal dist. 48 mm | 11195785<br>Laser class 1<br>Laser point<br>Focal dist. 65 mm   | 11112017<br>Laser class 1<br>Laser line<br>Focal dist. 65 mm |
|---|---|--|---|--|
| Beam shape  | Laser point   | Laser line   | Laser point   | Laser line   |
| Laser class   | 1   |  | 1   |  |
| Function  | Distance  |  | Distance  |  |
| Measuring range (distance)  | 30...70 mm  |  | 30...70 mm  |  |
| Start of measuring range Sdc  | 30 mm   |  | 30 mm   |  |
| End of measuring range Sde  | 70 mm   |  | 70 mm   |  |
| Blind region  | 0...30 mm   |  | 0...30 mm   |  |
| Measuring range Mr  | 40 mm   |  | 40 mm   |  |
| Sweet spot  | 48 mm   |  | 65 mm   |  |
| Focal range   | 40...55 mm  |  | 55...70 mm  |  |
| Measuring frequency   | 2500 Hz <sup>12</sup>   |  | 2500 Hz <sup>12</sup>   |  |
| Response time<br>- Single shot<br>- Continuous  | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>  |  | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>  |  |
| Resolution<br>Without filter<br>Precision high<br>Precision very high<br>Precision highest              | 2.6...4 µm <sup>12</sup><br>1.3...2 µm <sup>123</sup><br>0.9...1.4 µm <sup>123</sup><br>0.7...1 µm <sup>123</sup>       |  | 2.6...4 µm <sup>12</sup><br>1.3...2 µm <sup>123</sup><br>0.9...1.4 µm <sup>123</sup><br>0.7...1 µm <sup>123</sup>       |  |
| Spatial repeatability   | 14 µm   |  | 14 µm   |  |
| Repeat accuracy in time<br>Without filter<br>Precision high<br>Precision very high<br>Precision highest | 0.4...1.2 µm <sup>12</sup><br>0.2...0.6 µm <sup>123</sup><br>0.2...0.4 µm <sup>123</sup><br>0.1...0.3 µm <sup>123</sup> |  | 0.4...1.2 µm <sup>12</sup><br>0.2...0.6 µm <sup>123</sup><br>0.2...0.4 µm <sup>123</sup><br>0.1...0.3 µm <sup>123</sup> |  |
| Linearity error   | ± 22 µm <sup>12</sup>   |  | ± 22 µm <sup>12</sup>   |  |
| Linearity deviation in % of Mr  | ± 0.06% <sup>12</sup>   |  | ± 0.06% <sup>12</sup>   |  |
| Temperature drift   | ± 0.01% Sde/K <sup>12</sup>   |  | ± 0.01% Sde/K <sup>12</sup>   |  |
| PRECISION filter values:<br>Standard<br>High<br>Very high<br>Highest                                    | Median<br>Off<br>9<br>9<br>9  | Average<br>Off<br>Off<br>16<br>128                           | Median<br>Off<br>9<br>9<br>9  | Average<br>Off<br>Off<br>16<br>128                           |

<sup>1</sup> Measurements with standard Baumer measuring equipment and objects dependent on measuring range Sd

<sup>2</sup> Measurement on 90% reflectivity (white)

<sup>3</sup> Measurement with filtering

|  |                         |                         |
|--|-------------------------|-------------------------|
| Hysteresis digital output              | Adjustable in mm        | Adjustable in mm        |
| Minimum window size for digital output | 0.07 mm                 | 0.07 mm                 |
| Minimum window size for analog output  | 1 mm                    | 1 mm                    |
| Power on indication                    | Green LED               | Green LED               |
| Output indicator                       | Yellow LED / red LED    | Yellow LED / red LED    |
| Switch-on delay                        | <1200 ms                | <1200 ms                |
| Light source                           | Red laser diode, pulsed | Red laser diode, pulsed |
| Setting                                | Touch display, RS-485   | Touch display, RS-485   |

| <b>Electrical data</b>             | <b>11200060</b><br>Laser class 1<br>Laser point<br>Focal dist. 48 mm | <b>11200056</b><br>Laser class 1<br>Laser line<br>Focal dist. 48 mm | <b>11195785</b><br>Laser class 1<br>Laser point<br>Focal dist. 65 mm | <b>11112017</b><br>Laser class 1<br>Laser line<br>Focal dist. 65 mm |
|------------------------------------|--|---|--|---|
| Voltage supply range +Vs           | 15 ... 28 VDC  |   | 15 ... 28 VDC  |   |
| Max. supply current (without load) | 120 mA   |   | 120 mA   |   |
| Output circuit                     | Analog and RS-485  |   | Analog and RS-485  |   |
| Output signal                      | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                              |   | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                              |   |
| Switching output                   | Push-pull  |   | Push-pull  |   |
| Output function                    | Out 1 / alarm  |   | Out 1 / alarm  |   |
| Output current                     | < 100 mA   |   | < 100 mA   |   |
| Baud rate                          | Adjustable   |   | Adjustable   |   |
| Reverse polarity protection        | Yes, Vs to GND   |   | Yes, Vs to GND   |   |
| Short circuit protection           | Yes  |   | Yes  |   |

| <b>Mechanical data</b>  | <b>11200060</b><br>Laser class 1<br>Laser point<br>Focal dist. 48 mm | <b>11200056</b><br>Laser class 1<br>Laser line<br>Focal dist. 48 mm | <b>11195785</b><br>Laser class 1<br>Laser point<br>Focal dist. 65 mm | <b>11112017</b><br>Laser class 1<br>Laser line<br>Focal dist. 65 mm |
|-------------------------|--|---|--|---|
| Width / Height / Length | 26 / 74 / 55 mm  |   | 26 / 74 / 55 mm  |   |
| Design                  | Rectangular, front view  |   | Rectangular, front view  |   |
| Housing material        | Aluminum   |   | Aluminum   |   |
| Front optic             | Glass  |   | Glass  |   |
| Connection method       | Plug M12 8-pole  |   | Plug M12 8-pole  |   |
| Weight                  | 130 g  |   | 130 g  |   |

| <b>Ambient conditions</b> | <b>11200060</b><br>Laser class 1<br>Laser point<br>Focal dist. 48 mm | <b>11200056</b><br>Laser class 1<br>Laser line<br>Focal dist. 48 mm | <b>11195785</b><br>Laser class 1<br>Laser point<br>Focal dist. 65 mm | <b>11112017</b><br>Laser class 1<br>Laser line<br>Focal dist. 65 mm |
|---------------------------|--|---|--|---|
| Ambient light immunity    | < 28 kLux  | < 28 kLux   | < 28 kLux  | < 28 kLux   |

|                                    |  |  |
|------------------------------------|--|--|
| Operating temperature              | -10 ... +50 °C   | -10 ... +50 °C   |
| Storage temperature                | -20 ... +60 °C   | -20 ... +60 °C   |
| Heating period                     | 20 min.  | 20 min.  |
| protection class                   | IP 67  | IP 67  |
| Vibration resistance (sinusoidal)  | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |
| Shock resistance (semi-sinusoidal) | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |

| <b>Optical properties</b>                          | <b>11200060</b><br>Laser class 1<br>Laser point<br>Focal dist. 48 mm | <b>11200056</b><br>Laser class 1<br>Laser line<br>Focal dist. 48 mm | <b>11195785</b><br>Laser class 1<br>Laser point<br>Focal dist. 65 mm | <b>11112017</b><br>Laser class 1<br>Laser line<br>Focal dist. 65 mm |
|--|--|---|--|---|
| Light source                                       | AlGaInP laser diode  |   | AlGaInP laser diode  |   |
| Wave length  | 660 nm   |   | 660 nm   |   |
| Operating mode                                     | pulsed   |   | pulsed   |   |
| Pulse duration                                     | 4 µs...2.5 ms  | 4 µs...2.5 ms   | 4 µs...2.5 ms  | 4 µs...2.5 ms   |
| Pulse period                                       | 0.4...5 ms   | 0.4...5 ms  | 0.4...5 ms   | 0.4...5 ms  |
| Total emitted pulse power                          | 0.24mW   | 0.29mW  | 0.24mW   | 0.24mW  |
| Beam shape   | Point laser  | Short line  | Point laser  | Short line  |
| Receiver position                                  | L1<br>L2   |   | 34 mm<br>50 mm   |   |
| Focal distance df                                  | 48 mm  |   | 65 mm  |   |
| Nominal ocular hazard distance (NOHD) <sup>1</sup> | N/A  | N/A   | N/A  | N/A   |
| Laser classification (as per IEC 60825-1/2014)     | Laser class 1  |   | Laser class 1  |   |

<sup>1</sup> Outside the "Nominal ocular hazard distance", the radiation exposure is below the limit value of laser class 1

## 7.1 Measuring range types 40...140 mm

| General data  | 11200061<br>Laser class 1<br>Laser point<br>Focal dist. 70 mm   | 11200062<br>Laser class 1<br>Laser line<br>Focal dist. 70 mm | 11200063<br>Laser class 1<br>Laser point<br>Focal dist. 100 mm  | 11200064<br>Laser class 1<br>Laser line<br>Focal dist. 100 mm | 11112018<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm  | 11112019<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm |
|---|---|--|---|---|---|---|
| Beam shape  | Laser point   | Laser line   | Laser point   | Laser line  | Laser point   | Laser line  |
| Laser class   | 1   |  | 1   |   | 1   |   |
| Function  | Distance  |  | Distance  |   | Distance  |   |
| Measuring range (distance)  | 40...140 mm   |  | 40...140 mm   |   | 40...140 mm   |   |
| Start of measuring range Sdc  | 40 mm   |  | 40 mm   |   | 40 mm   |   |
| End of measuring range Sde  | 140 mm  |  | 140 mm  |   | 140 mm  |   |
| Blind region  | 0...40 mm   |  | 0...40 mm   |   | 0...40 mm   |   |
| Measuring range Mr  | 100 mm  |  | 100 mm  |   | 100 mm  |   |
| Sweet spot  | 70 mm   |  | 100 mm  |   | 130 mm  |   |
| Focal range   | 50...90 mm  |  | 80...120 mm   |   | 110...140 mm  |   |
| Measuring frequency   | 2500 Hz <sup>12</sup>   |  | 2500 Hz <sup>12</sup>   |   | 2500 Hz <sup>12</sup>   |   |
| Response time<br>- Single shot<br>- Continuous  | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>  |  | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>  |   | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>  |   |
| Resolution<br>Without filter<br>Precision high<br>Precision very high<br>Precision highest              | 4.8...10 µm <sup>12</sup><br>2.4...5 µm <sup>123</sup><br>1.6...3.4 µm <sup>123</sup><br>1.2...2.5 µm <sup>123</sup>  |  | 4.8...10 µm <sup>12</sup><br>2.4...5 µm <sup>123</sup><br>1.6...3.4 µm <sup>123</sup><br>1.2...2.5 µm <sup>123</sup>  |   | 4.8...10 µm <sup>12</sup><br>2.4...5 µm <sup>123</sup><br>1.6...3.4 µm <sup>123</sup><br>1.2...2.5 µm <sup>123</sup>  |   |
| Spatial repeatability   | 22 µm   |  | 22 µm   |   | 22 µm   |   |
| Repeat accuracy in time<br>Without filter<br>Precision high<br>Precision very high<br>Precision highest | 1...2.5 µm <sup>12</sup><br>0.5...1.3 µm <sup>123</sup><br>0.4...0.9 µm <sup>123</sup><br>0.3...0.7 µm <sup>123</sup> |  | 1...2.5 µm <sup>12</sup><br>0.5...1.3 µm <sup>123</sup><br>0.4...0.9 µm <sup>123</sup><br>0.3...0.7 µm <sup>123</sup> |   | 1...2.5 µm <sup>12</sup><br>0.5...1.3 µm <sup>123</sup><br>0.4...0.9 µm <sup>123</sup><br>0.3...0.7 µm <sup>123</sup> |   |
| Linearity error   | ± 65 µm <sup>12</sup>   |  | ± 65 µm <sup>12</sup>   |   | ± 65 µm <sup>12</sup>   |   |
| Linearity deviation in % of Mr  | ± 0.07% <sup>12</sup>   |  | ± 0.07% <sup>12</sup>   |   | ± 0.07% <sup>12</sup>   |   |
| Temperature drift   | ± 0.015% Sde/K <sup>12</sup>  |  | ± 0.015% Sde/K <sup>12</sup>  |   | ± 0.015% Sde/K <sup>12</sup>  |   |
| PRECISION filter values:  | Median Average  |  | Median Average  |   | Median Average  |   |

<sup>1</sup> Measurements with standard Baumer measuring equipment and objects dependent on measuring range Sd

<sup>2</sup> Measurement on 90% reflectivity (white)

<sup>3</sup> Measurement with filtering

|  |                         |     |                         |     |                         |     |
|--|-------------------------|-----|-------------------------|-----|-------------------------|-----|
| Standard                               | Off                     | Off | Off                     | Off | Off                     | Off |
| High                                   | 9                       | Off | 9                       | Off | 9                       | Off |
| Very high                              | 9                       | 16  | 9                       | 16  | 9                       | 16  |
| Highest                                | 9                       | 128 | 9                       | 128 | 9                       | 128 |
| Hysteresis digital output              | Adjustable in mm        |     | Adjustable in mm        |     | Adjustable in mm        |     |
| Minimum window size for digital output | 0.14 mm                 |     | 0.14 mm                 |     | 0.14 mm                 |     |
| Minimum window size for analog output  | 1 mm                    |     | 1 mm                    |     | 1 mm                    |     |
| Power on indication                    | Green LED               |     | Green LED               |     | Green LED               |     |
| Output indicator                       | Yellow LED / red LED    |     | Yellow LED / red LED    |     | Yellow LED / red LED    |     |
| Switch-on delay                        | <1200 ms                |     | <1200 ms                |     | <1200 ms                |     |
| Light source                           | Red laser diode, pulsed |     | Red laser diode, pulsed |     | Red laser diode, pulsed |     |
| Setting                                | Touch display, RS-485   |     | Touch display, RS-485   |     | Touch display, RS-485   |     |

| Electrical data                    | 11200061<br>Laser class 1<br>Laser point<br>Focal dist. 70 mm | 11200062<br>Laser class 1<br>Laser line<br>Focal dist. 70 mm | 11200063<br>Laser class 1<br>Laser point<br>Focal dist. 100 mm | 11200064<br>Laser class 1<br>Laser line<br>Focal dist. 100 mm | 11112018<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm | 11112019<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm |
|------------------------------------|---|--|--|---|--|---|
| Voltage supply range +Vs           | 15 ... 28 VDC   |  | 15 ... 28 VDC  |   | 15 ... 28 VDC  |   |
| Max. supply current (without load) | 120 mA  |  | 120 mA   |   | 120 mA   |   |
| Output circuit                     | Analog and RS-485   |  | Analog and RS-485  |   | Analog and RS-485  |   |
| Output signal                      | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                       |  | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                        |   | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                        |   |
| Switching output                   | Push-pull   |  | Push-pull  |   | Push-pull  |   |
| Output function                    | Out 1 / alarm   |  | Out 1 / alarm  |   | Out 1 / alarm  |   |
| Output current                     | < 100 mA  |  | < 100 mA   |   | < 100 mA   |   |
| Baud rate                          | Adjustable  |  | Adjustable   |   | Adjustable   |   |
| Reverse polarity protection        | Yes, Vs to GND  |  | Yes, Vs to GND   |   | Yes, Vs to GND   |   |
| Short circuit protection           | Yes   |  | Yes  |   | Yes  |   |

| Mechanical data         | 11200061<br>Laser class 1<br>Laser point<br>Focal dist. 70 mm | 11200062<br>Laser class 1<br>Laser line<br>Focal dist. 70 mm | 11200063<br>Laser class 1<br>Laser point<br>Focal dist. 100 mm | 11200064<br>Laser class 1<br>Laser line<br>Focal dist. 100 mm | 11112018<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm | 11112019<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm |
|-------------------------|---|--|--|---|--|---|
| Width / Height / Length | 26 / 74 / 55 mm   |  | 26 / 74 / 55 mm  |   | 26 / 74 / 55 mm  |   |
| Design                  | Rectangular, front view                                       |  | Rectangular, front view  |   | Rectangular, front view  |   |
| Housing material        | Aluminum  |  | Aluminum   |   | Aluminum   |   |
| Front optic             | Glass   |  | Glass  |   | Glass  |   |
| Connection method       | Plug M12 8-pole   |  | Plug M12 8-pole  |   | Plug M12 8-pole  |   |
| Weight                  | 130 g   |  | 130 g  |   | 130 g  |   |

| Ambient conditions                                 |  | 11200061<br>Laser class 1<br>Laser point<br>Focal dist. 70 mm  | 11200062<br>Laser class 1<br>Laser line<br>Focal dist. 70 mm | 11200063<br>Laser class 1<br>Laser point<br>Focal dist. 100 mm   | 11200064<br>Laser class 1<br>Laser line<br>Focal dist. 100 mm | 11112018<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm   | 11112019<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm |
|--|--|--|--|--|---|--|---|
| Ambient light immunity                             |  | < 35 kLux  |  | < 35 kLux  |   | < 35 kLux  |   |
| Operating temperature                              |  | -10 ... +50 °C   |  | -10 ... +50 °C   |   | -10 ... +50 °C   |   |
| Storage temperature                                |  | -20 ... +60 °C   |  | -20 ... +60 °C   |   | -20 ... +60 °C   |   |
| Heating period                                     |  | 20 min.  |  | 20 min.  |   | 20 min.  |   |
| protection class                                   |  | IP 67  |  | IP 67  |   | IP 67  |   |
| Vibration resistance (sinusoidal)                  |  | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |  | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   |
| Shock resistance (semi-sinusoidal)                 |  | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |  | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   |
| Optical properties                                 |  | 11200061<br>Laser class 1<br>Laser point<br>Focal dist. 70 mm  | 11200062<br>Laser class 1<br>Laser line<br>Focal dist. 70 mm | 11200063<br>Laser class 1<br>Laser point<br>Focal dist. 100 mm   | 11200064<br>Laser class 1<br>Laser line<br>Focal dist. 100 mm | 11112018<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm   | 11112019<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm |
| Light source                                       |  | AlGaInP laser diode  |  | AlGaInP laser diode  |   | AlGaInP laser diode  |   |
| Wave length  |  | 660 nm   |  | 660 nm   |   | 660 nm   |   |
| Operating mode                                     |  | pulsed   |  | pulsed   |   | pulsed   |   |
| Pulse duration                                     |  | 4 µs...2.5ms   | 4 µs...2.5ms   | 4 µs...2.5ms   | 4 µs...2.5ms  | 4 µs...2.5ms   | 4 µs...2.5ms  |
| Pulse period                                       |  | 0.4...5 ms   | 0.4...5 ms   | 0.4...5 ms   | 0.4...5 ms  | 0.4...5 ms   | 0.4...5 ms  |
| Total emitted pulse power                          |  | 0.2 mW   | 0.2 mW   | 0.2 mW   | 0.2 mW  | 0.28 mW  | 0.27 mW   |
| Beam shape   |  | Point laser  | Short line   | Point laser  | Short line  | Point laser  | Short line  |
| Receiver position L1                               |  | 36 mm  |  | 36 mm  |   | 36 mm  |   |
| Receiver position L2                               |  | 53 mm  |  | 53 mm  |   | 53 mm  |   |
| Focal distance df                                  |  | 70 mm  |  | 100 mm   |   | 130 mm   |   |
| Nominal ocular hazard distance (NOHD) <sup>1</sup> |  | N/A  | N/A  | N/A  | N/A   | N/A  | N/A   |
| Laser classification (as per IEC 60825-1/2014)     |  | Laser class 1  |  | Laser class 1  |   | Laser class 1  |   |

<sup>1</sup> Outside the "Nominal ocular hazard distance", the radiation exposure is below the limit value of laser class 1



## 7.1 Measuring range types 50...250 mm

| General data  | 11200065<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm  | 11200066<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm | 11200067<br>Laser class 1<br>Laser point<br>Focal dist. 180 mm  | 11200068<br>Laser class 1<br>Laser line<br>Focal dist. 180 mm | 11112060<br>Laser class 1<br>Laser point<br>Focal dist. 240 mm  | 11200061<br>Laser class 1<br>Laser line<br>Focal dist. 240 mm |
|---|---|---|---|---|---|---|
| Beam shape  | Laser point   | Laser line  | Laser point   | Laser line  | Laser point   | Laser line  |
| Laser class   | 1   |   | 1   |   | 1   |   |
| Function  | Distance  |   | Distance  |   | Distance  |   |
| Measuring range (distance)  | 50...250 mm   |   | 50...250 mm   |   | 50...250 mm   |   |
| Start of measuring range Sdc  | 50 mm   |   | 50 mm   |   | 50 mm   |   |
| End of measuring range Sde  | 250 mm  |   | 250 mm  |   | 250 mm  |   |
| Blind region  | 0...50 mm   |   | 0...50 mm   |   | 0...50 mm   |   |
| Measuring range Mr  | 200 mm  |   | 200 mm  |   | 200 mm  |   |
| Sweet spot  | 130 mm  |   | 180 mm  |   | 240 mm  |   |
| Focal range   | 100...150 mm  |   | 140...210 mm  |   | 200...250 mm  |   |
| Measuring frequency   | 2500 Hz <sup>12</sup>   |   | 2500 Hz <sup>12</sup>   |   | 2500 Hz <sup>12</sup>   |   |
| Response time<br>- Single shot<br>- Continuous  | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>  |   | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>  |   | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>  |   |
| Resolution<br>Without filter<br>Precision high<br>Precision very high<br>Precision highest              | 5.3...25 µm <sup>12</sup><br>2.7...12.5 µm <sup>123</sup><br>1.8...8.4 µm <sup>123</sup><br>1.4...6.3 µm <sup>123</sup> |   | 5.3...25 µm <sup>12</sup><br>2.7...12.5 µm <sup>123</sup><br>1.8...8.4 µm <sup>123</sup><br>1.4...6.3 µm <sup>123</sup> |   | 5.3...25 µm <sup>12</sup><br>2.7...12.5 µm <sup>123</sup><br>1.8...8.4 µm <sup>123</sup><br>1.4...6.3 µm <sup>123</sup> |   |
| Spatial repeatability   | 60 µm   |   | 60 µm   |   | 60 µm   |   |
| Repeat accuracy in time<br>Without filter<br>Precision high<br>Precision very high<br>Precision highest | 1...8 µm <sup>12</sup><br>0.5...4 µm <sup>123</sup><br>0.4...2.7 µm <sup>123</sup><br>0.3...2 µm <sup>123</sup>         |   | 1...8 µm <sup>12</sup><br>0.5...4 µm <sup>123</sup><br>0.4...2.7 µm <sup>123</sup><br>0.3...2 µm <sup>123</sup>         |   | 1...8 µm <sup>12</sup><br>0.5...4 µm <sup>123</sup><br>0.4...2.7 µm <sup>123</sup><br>0.3...2 µm <sup>123</sup>         |   |
| Linearity error   | ± 170 µm <sup>12</sup>  |   | ± 170 µm <sup>12</sup>  |   | ± 170 µm <sup>12</sup>  |   |
| Linearity deviation in % of Mr  | ± 0.09% <sup>12</sup>   |   | ± 0.09% <sup>12</sup>   |   | ± 0.09% <sup>12</sup>   |   |
| Temperature drift   | ± 0.024% Sde/K <sup>12</sup>  |   | ± 0.024% Sde/K <sup>12</sup>  |   | ± 0.024% Sde/K <sup>12</sup>  |   |

<sup>1</sup> Measurements with standard Baumer measuring equipment and objects dependent on measuring range Sd

<sup>2</sup> Measurement on 90% reflectivity (white)

<sup>3</sup> Measurement with filtering

|  |                         |                         |                         |
|--|-------------------------|-------------------------|-------------------------|
| PRECISION filter values:               | Median Average          | Median Average          | Median Average          |
| Standard                               | Off Off                 | Off Off                 | Off Off                 |
| High                                   | 9 Off                   | 9 Off                   | 9 Off                   |
| Very high                              | 9 16                    | 9 16                    | 9 16                    |
| Highest                                | 9 128                   | 9 128                   | 9 128                   |
| Hysteresis digital output              | Adjustable in mm        | Adjustable in mm        | Adjustable in mm        |
| Minimum window size for digital output | 0.25 mm                 | 0.25 mm                 | 0.25 mm                 |
| Minimum window size for analog output  | 1 mm                    | 1 mm                    | 1 mm                    |
| Power on indication                    | Green LED               | Green LED               | Green LED               |
| Output indicator                       | Yellow LED / red LED    | Yellow LED / red LED    | Yellow LED / red LED    |
| Switch-on delay                        | <1200 ms                | <1200 ms                | <1200 ms                |
| Light source                           | Red laser diode, pulsed | Red laser diode, pulsed | Red laser diode, pulsed |
| Setting                                | Touch display, RS-485   | Touch display, RS-485   | Touch display, RS-485   |

| Electrical data                    | 11200065<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm | 11200066<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm | 11200067<br>Laser class 1<br>Laser point<br>Focal dist. 180 mm | 11200068<br>Laser class 1<br>Laser line<br>Focal dist. 180 mm | 11112060<br>Laser class 1<br>Laser point<br>Focal dist. 240 mm | 11200061<br>Laser class 1<br>Laser line<br>Focal dist. 240 mm |
|------------------------------------|--|---|--|---|--|---|
| Voltage supply range +Vs           | 15 ... 28 VDC  |   | 15 ... 28 VDC  |   | 15 ... 28 VDC  |   |
| Max. supply current (without load) | 120 mA   |   | 120 mA   |   | 120 mA   |   |
| Output circuit                     | Analog and RS-485  |   | Analog and RS-485  |   | Analog and RS-485  |   |
| Output signal                      | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                        |   | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                        |   | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                        |   |
| Switching output                   | Push-pull  |   | Push-pull  |   | Push-pull  |   |
| Output function                    | Out 1 / alarm  |   | Out 1 / alarm  |   | Out 1 / alarm  |   |
| Output current                     | < 100 mA   |   | < 100 mA   |   | < 100 mA   |   |
| Baud rate                          | Adjustable   |   | Adjustable   |   | Adjustable   |   |
| Reverse polarity protection        | Yes, Vs to GND   |   | Yes, Vs to GND   |   | Yes, Vs to GND   |   |
| Short circuit protection           | Yes  |   | Yes  |   | Yes  |   |

| Mechanical data         | 11200065<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm | 11200066<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm | 11200067<br>Laser class 1<br>Laser point<br>Focal dist. 180 mm | 11200068<br>Laser class 1<br>Laser line<br>Focal dist. 180 mm | 11112060<br>Laser class 1<br>Laser point<br>Focal dist. 240 mm | 11200061<br>Laser class 1<br>Laser line<br>Focal dist. 240 mm |
|-------------------------|--|---|--|---|--|---|
| Width / Height / Length | 26 / 74 / 55 mm  |   | 26 / 74 / 55 mm  |   | 26 / 74 / 55 mm  |   |
| Design                  | Rectangular, front view  |   | Rectangular, front view  |   | Rectangular, front view  |   |
| Housing material        | Aluminum   |   | Aluminum   |   | Aluminum   |   |
| Front optic             | Glass  |   | Glass  |   | Glass  |   |
| Connection method       | Plug M12 8-pole  |   | Plug M12 8-pole  |   | Plug M12 8-pole  |   |
| Weight                  | 130 g  |   | 130 g  |   | 130 g  |   |

| Ambient conditions                                 |  | 11200065<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm   | 11200066<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm | 11200067<br>Laser class 1<br>Laser point<br>Focal dist. 180 mm   | 11200068<br>Laser class 1<br>Laser line<br>Focal dist. 180 mm | 11112060<br>Laser class 1<br>Laser point<br>Focal dist. 240 mm   | 11200061<br>Laser class 1<br>Laser line<br>Focal dist. 240 mm |
|--|--|--|---|--|---|--|---|
| Ambient light immunity                             |  | < 170 kLux   |   | < 170 kLux   |   | < 170 kLux   |   |
| Operating temperature                              |  | -10 ... +50 °C   |   | -10 ... +50 °C   |   | -10 ... +50 °C   |   |
| Storage temperature                                |  | -20 ... +60 °C   |   | -20 ... +60 °C   |   | -20 ... +60 °C   |   |
| Heating period                                     |  | 20 min.  |   | 20 min.  |   | 20 min.  |   |
| protection class                                   |  | IP 67  |   | IP 67  |   | IP 67  |   |
| Vibration resistance (sinusoidal)                  |  | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   |
| Shock resistance (semi-sinusoidal)                 |  | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   |
| Optical properties                                 |  | 11200065<br>Laser class 1<br>Laser point<br>Focal dist. 130 mm   | 11200066<br>Laser class 1<br>Laser line<br>Focal dist. 130 mm | 11200067<br>Laser class 1<br>Laser point<br>Focal dist. 180 mm   | 11200068<br>Laser class 1<br>Laser line<br>Focal dist. 180 mm | 11112060<br>Laser class 1<br>Laser point<br>Focal dist. 240 mm   | 11200061<br>Laser class 1<br>Laser line<br>Focal dist. 240 mm |
| Light source                                       |  | AlGaInP laser diode  |   | AlGaInP laser diode  |   | AlGaInP laser diode  |   |
| Wave length  |  | 660 nm   |   | 660 nm   |   | 660 nm   |   |
| Operating mode                                     |  | pulsed   |   | pulsed   |   | pulsed   |   |
| Pulse duration                                     |  | 4 µs...2.5 ms  | 4 µs...2.5 ms   | 4 µs...2.5 ms  | 4 µs...2.5 ms   | 4 µs...2.5 ms  | 4 µs...2.5 ms   |
| Pulse period                                       |  | 0.4...6 ms   | 0.4...6 ms  | 0.4...6 ms   | 0.4...6 ms  | 0.4...6 ms   | 0.4...9 ms  |
| Total emitted pulse power                          |  | 0.65 mW  | 0.65 mW   | 0.65 mW  | 0.65 mW   | 0.65 mW  | 0.95 mW   |
| Beam shape   |  | Point laser  | Short line  | Point laser  | Short line  | Point laser  | Short line  |
| Receiver position                                  |  | L1<br>L2<br>38 mm<br>55 mm   |   | 38 mm<br>55 mm   |   | 38 mm<br>55 mm   |   |
| Focal distance df                                  |  | 130 mm   | 130 mm  | 180 mm   | 180 mm  | 240 mm   | 240 mm  |
| Nominal ocular hazard distance (NOHD) <sup>1</sup> |  | N/A  | N/A   | N/A  | N/A   | N/A  | N/A   |
| Laser classification (as per IEC 60825-1/2014)     |  | Laser class 1  |   | Laser class 1  |   | Laser class 1  |   |

<sup>1</sup> Outside the "Nominal ocular hazard distance", the radiation exposure is below the limit value of laser class 1

## 7.2 Measuring range types 100...600 mm

| General data  | 11200069<br>Laser class 2<br>Laser point<br>Focal dist. 350 mm   | 11200090<br>Laser class 2<br>Laser line<br>Focal dist. 350 mm | 11112064<br>Laser class 1<br>Laser point<br>Focal dist. 500 mm   | 11112065<br>Laser class 1<br>Laser line<br>Focal dist. 500 mm | 11112066<br>Laser class 2<br>Laser point<br>Focal dist. 500 mm   | 11200067<br>Laser class 2<br>Laser line<br>Focal dist. 500 mm |
|---|--|---|--|---|--|---|
| Beam shape  | Laser point  | Laser line  | Laser point  | Laser line  | Laser point  | Laser line  |
| Laser class   | 2  |   | 1  |   | 2  |   |
| Function  | Distance   |   | Distance   |   | Distance   |   |
| Measuring range (distance)  | 100...600 mm   |   | 100...600 mm   |   | 100...600 mm   |   |
| Start of measuring range Sdc  | 100mm  |   | 100mm  |   | 100mm  |   |
| End of measuring range Sde  | 600 mm   |   | 600 mm   |   | 600 mm   |   |
| Blind region  | 0...100 mm   |   | 0...100 mm   |   | 0...100 mm   |   |
| Measuring range Mr  | 500 mm   |   | 500 mm   |   | 500 mm   |   |
| Sweet spot  | 350 mm   |   | 500 mm   |   | 500 mm   |   |
| Focal range   | 250...450 mm   |   | 400...600 mm   |   | 400...600 mm   |   |
| Measuring frequency   | 2500 Hz <sup>12</sup>  |   | 2500 Hz <sup>12</sup>  |   | 2500 Hz <sup>12</sup>  |   |
| Response time<br>- Single shot<br>- Continuous  | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>   |   | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>   |   | 0.8 ms <sup>12</sup><br>1.2 ms <sup>12</sup>   |   |
| Resolution<br>Without filter<br>Precision high<br>Precision very high<br>Precision highest              | 10...95 µm <sup>12</sup><br>5...48 µm <sup>123</sup><br>4...32 µm <sup>123</sup><br>3...24 µm <sup>123</sup> |   | 10...95 µm <sup>12</sup><br>5...48 µm <sup>123</sup><br>4...32 µm <sup>123</sup><br>3...24 µm <sup>123</sup> |   | 10...95 µm <sup>12</sup><br>5...48 µm <sup>123</sup><br>4...32 µm <sup>123</sup><br>3...24 µm <sup>123</sup> |   |
| Spatial repeatability   | 250 µm   |   | 250 µm   |   | 250 µm   |   |
| Repeat accuracy in time<br>Without filter<br>Precision high<br>Precision very high<br>Precision highest | 3...36 µm <sup>12</sup><br>2...18 µm <sup>123</sup><br>1...12 µm <sup>123</sup><br>1...9 µm <sup>123</sup>   |   | 3...36 µm <sup>12</sup><br>2...18 µm <sup>123</sup><br>1...12 µm <sup>123</sup><br>1...9 µm <sup>123</sup>   |   | 3...36 µm <sup>12</sup><br>2...18 µm <sup>123</sup><br>1...12 µm <sup>123</sup><br>1...9 µm <sup>123</sup>   |   |
| Linearity error   | ± 600 µm <sup>12</sup>   |   | ± 600 µm <sup>12</sup>   |   | ± 600 µm <sup>12</sup>   |   |
| Linearity deviation in % of Mr  | ± 0.12% <sup>12</sup>  |   | ± 0.12% <sup>12</sup>  |   | ± 0.12% <sup>12</sup>  |   |
| Temperature drift   | ± 0.04% Sde/K <sup>12</sup>  |   | ± 0.04% Sde/K <sup>12</sup>  |   | ± 0.04% Sde/K <sup>12</sup>  |   |
| PRECISION filter values:  | Median Average   |   | Median Average   |   | Median Average   |   |

<sup>1</sup> Measurements with standard Baumer measuring equipment and objects dependent on measuring range Sd

<sup>2</sup> Measurement on 90% reflectivity (white)

<sup>3</sup> Measurement with filtering

|  |                         |     |                         |     |                         |     |
|--|-------------------------|-----|-------------------------|-----|-------------------------|-----|
| Standard                               | Off                     | Off | Off                     | Off | Off                     | Off |
| High                                   | 9                       | Off | 9                       | Off | 9                       | Off |
| Very high                              | 9                       | 16  | 9                       | 16  | 9                       | 16  |
| Highest                                | 9                       | 128 | 9                       | 128 | 9                       | 128 |
| Hysteresis digital output              | Adjustable in mm        |     | Adjustable in mm        |     | Adjustable in mm        |     |
| Minimum window size for digital output | 0.6 mm                  |     | 0.6 mm                  |     | 0.6 mm                  |     |
| Minimum window size for analog output  | 1 mm                    |     | 1 mm                    |     | 1 mm                    |     |
| Output indicator                       | Yellow LED / red LED    |     | Yellow LED / red LED    |     | Yellow LED / red LED    |     |
| Switch-on delay                        | <1200 ms                |     | <1200 ms                |     | <1200 ms                |     |
| Light source                           | Red laser diode, pulsed |     | Red laser diode, pulsed |     | Red laser diode, pulsed |     |
| Setting                                | Touch display, RS-485   |     | Touch display, RS-485   |     | Touch display, RS-485   |     |

| <b>Electrical data</b>             | <b>11200069</b><br>Laser class 2<br>Laser point<br>Focal dist. 350 mm | <b>11200090</b><br>Laser class 2<br>Laser line<br>Focal dist. 350 mm | <b>11112064</b><br>Laser class 1<br>Laser point<br>Focal dist. 500 mm | <b>11112065</b><br>Laser class 1<br>Laser line<br>Focal dist. 500 mm | <b>11112066</b><br>Laser class 2<br>Laser point<br>Focal dist. 500 mm | <b>11200067</b><br>Laser class 2<br>Laser line<br>Focal dist. 500 mm |
|------------------------------------|---|--|---|--|---|--|
| Voltage supply range +Vs           | 15 ... 28 VDC   |  | 15 ... 28 VDC   |  | 15 ... 28 VDC   |  |
| Max. supply current (without load) | 120 mA  |  | 120 mA  |  | 120 mA  |  |
| Output circuit                     | Analog and RS-485   |  | Analog and RS-485   |  | Analog and RS-485   |  |
| Output signal                      | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                               |  | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                               |  | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                               |  |
| Switching output                   | Push-pull   |  | Push-pull   |  | Push-pull   |  |
| Output function                    | Out 1 / alarm   |  | Out 1 / alarm   |  | Out 1 / alarm   |  |
| Output current                     | < 100 mA  |  | < 100 mA  |  | < 100 mA  |  |
| Baud rate                          | Adjustable  |  | Adjustable  |  | Adjustable  |  |
| Reverse polarity protection        | Yes, Vs to GND  |  | Yes, Vs to GND  |  | Yes, Vs to GND  |  |
| Short circuit protection           | Yes   |  | Yes   |  | Yes   |  |

| <b>Mechanical data</b>  | <b>11200069</b><br>Laser class 2<br>Laser point<br>Focal dist. 350 mm | <b>11200090</b><br>Laser class 2<br>Laser line<br>Focal dist. 350 mm | <b>11112064</b><br>Laser class 1<br>Laser point<br>Focal dist. 500 mm | <b>11112065</b><br>Laser class 1<br>Laser line<br>Focal dist. 500 mm | <b>11112066</b><br>Laser class 2<br>Laser point<br>Focal dist. 500 mm | <b>11200067</b><br>Laser class 2<br>Laser line<br>Focal dist. 500 mm |
|-------------------------|---|--|---|--|---|--|
| Width / Height / Length | 26 / 74 / 55 mm   |  | 26 / 74 / 55 mm   |  | 26 / 74 / 55 mm   |  |
| Design                  | Rectangular, front view   |  | Rectangular, front view   |  | Rectangular, front view   |  |
| Housing material        | Aluminum  |  | Aluminum  |  | Aluminum  |  |
| Front optic             | Glass   |  | Glass   |  | Glass   |  |
| Connection method       | Plug M12 8-pole   |  | Plug M12 8-pole   |  | Plug M12 8-pole   |  |
| Weight                  | 130 g   |  | 130 g   |  | 130 g   |  |

| Ambient conditions                                 | 11200069<br>Laser class 2<br>Laser point<br>Focal dist. 350 mm   | 11200090<br>Laser class 2<br>Laser line<br>Focal dist. 350 mm | 11112064<br>Laser class 1<br>Laser point<br>Focal dist. 500 mm   | 11112065<br>Laser class 1<br>Laser line<br>Focal dist. 500 mm | 11112066<br>Laser class 2<br>Laser point<br>Focal dist. 500 mm   | 11200067<br>Laser class 2<br>Laser line<br>Focal dist. 500 mm |
|--|--|---|--|---|--|---|
| Ambient light immunity                             | < 300 kLux   | < 170 kLux  | < 300 kLux   | < 170 kLux  | < 300 kLux   | < 170 kLux  |
| Operating temperature                              | -10 ... +50 °C   |   | -10 ... +50 °C   |   | -10 ... +50 °C   |   |
| Storage temperature                                | -20 ... +60 °C   |   | -20 ... +60 °C   |   | -20 ... +60 °C   |   |
| Heating period                                     | 20 min.  |   | 20 min.  |   | 20 min.  |   |
| protection class                                   | IP 67  |   | IP 67  |   | IP 67  |   |
| Vibration resistance (sinusoidal)                  | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   |
| Shock resistance (semi-sinusoidal)                 | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   |
| Optical properties                                 | 11200069<br>Laser class 2<br>Laser point<br>Focal dist. 350 mm   | 11200090<br>Laser class 2<br>Laser line<br>Focal dist. 350 mm | 11112064<br>Laser class 1<br>Laser point<br>Focal dist. 500 mm   | 11112065<br>Laser class 1<br>Laser line<br>Focal dist. 500 mm | 11112066<br>Laser class 2<br>Laser point<br>Focal dist. 500 mm   | 11200067<br>Laser class 2<br>Laser line<br>Focal dist. 500 mm |
| Light source                                       | AlGaInP laser diode  |   | AlGaInP laser diode  |   | AlGaInP laser diode  |   |
| Wave length  | 660 nm   |   | 660 nm   |   | 660 nm   |   |
| Operating mode                                     | pulsed   |   | pulsed   |   | pulsed   |   |
| Pulse duration                                     | 4 µs...2.5 ms  | 4 µs...2.5 ms   | 4 µs...2.5 ms  | 4 µs...2.5 ms   | 4 µs...2.5 ms  | 4 µs...2.5 ms   |
| Pulse period                                       | 0.4...5 ms   | 0.4...5 ms  | 0.4...9 ms   | 0.4...8 ms  | 0.4...5 ms   | 0.4...5 ms  |
| Total emitted pulse power                          | 0.98 mW  | 0.88 mW   | 0.98 mW  | 0.88 mW   | 0.98 mW  | 0.88 mW   |
| Beam shape   | Point laser  | Short line  | Point laser  | Short line  | Point laser  | Short line  |
| Receiver position                                  | L1<br>L2   |   | 41 mm<br>57 mm   |   | 41 mm<br>57 mm   |   |
| Focal distance df                                  | 350  | 350 mm  | 500 mm   | 500 mm  | 500 mm   | 500 mm  |
| Nominal ocular hazard distance (NOHD) <sup>1</sup> | N/A  | N/A   | N/A  | N/A   | N/A  | N/A   |
| Laser classification (as per IEC 60825-1/2014)     | Laser class 2  |   | Laser class 1  |   | Laser class 2  |   |

<sup>1</sup> Outside the "Nominal ocular hazard distance", the radiation exposure is below the limit value of laser class 1

## 7.1 Measuring range types 100...1000 mm

| General data                   | 11199108<br>Laser class 2<br>Laser point<br>Focal dist. 500 mm | 11199109<br>Laser class 2<br>Laser line<br>Focal dist. 500 mm | 11200091<br>Laser class 2<br>Laser point<br>Focal dist. 700 mm | 11200095<br>Laser class 2<br>Laser line<br>Focal dist. 700 mm | 11195787<br>Laser class 1<br>Laser point<br>Focal dist. 1000 mm | 11195788<br>Laser class 1<br>Laser line<br>Focal dist. 1000 mm | 11199089<br>Laser class 2<br>Laser point<br>Focal dist. 1000 mm | 11199100<br>Laser class 2<br>Laser line<br>Focal dist. 1000 mm |
|--------------------------------|--|---|--|---|---|--|---|--|
| Beam shape                     | Laser point  | Laser line  | Laser point  | Laser line  | Laser point   | Laser line   | Laser point   | Laser line   |
| Laser class                    | 2  |   | 2  |   | 1   |  | 2   |  |
| Function                       | Distance   |   | Distance   |   | Distance  |  | Distance  |  |
| Measuring range (distance)     | 100...1000 mm  |   | 100...1000 mm  |   | 100...1000 mm   |  | 100...1000 mm   |  |
| Start of measuring range Sdc   | 100 mm   |   | 100 mm   |   | 100 mm  |  | 100 mm  |  |
| End of measuring range Sde     | 1000 mm  |   | 1000 mm  |   | 1000 mm   |  | 1000 mm   |  |
| Blind region                   | 0...100 mm   |   | 0...100 mm   |   | 0...100 mm  |  | 0...100 mm  |  |
| Measuring range Mr             | 900 mm   |   | 900 mm   |   | 900 mm  |  | 900 mm  |  |
| Sweet spot                     | 500 mm   |   | 700 mm   |   | 1000 mm   |  | 1000 mm   |  |
| Focal range                    | 400...600 mm   |   | 550...850 mm   |   | 750...1000 mm   |  | 750...1000 mm   |  |
| Measuring frequency            | 2500 Hz <sup>12</sup>  |   | 2500 Hz <sup>12</sup>  |   | 2500 Hz <sup>12</sup>   |  | 2500 Hz <sup>12</sup>   |  |
| Response time                  |  |   |  |   |   |  |   |  |
| - Single shot                  | 0.8 ms <sup>12</sup>   |   | 0.8 ms <sup>12</sup>   |   | 0.8 ms <sup>12</sup>  |  | 0.7 ms <sup>12</sup>  |  |
| - Continuous                   | 1.2 ms <sup>12</sup>   |   | 1.2 ms <sup>12</sup>   |   | 1.2 ms <sup>12</sup>  |  | 1.2 ms <sup>12</sup>  |  |
| Resolution                     |  |   |  |   |   |  |   |  |
| Without filter                 | 10...250 µm <sup>12</sup>                                      | 10...250 µm <sup>12</sup>                                     | 10...250 µm <sup>12</sup>                                      | 10...250 µm <sup>12</sup>                                     | 10...250 µm <sup>12</sup>                                       | 10...250 µm <sup>12</sup>                                      | 10...250 µm <sup>12</sup>                                       | 10...250 µm <sup>12</sup>                                      |
| Precision high                 | 5...125 µm <sup>123</sup>                                      | 5...125 µm <sup>123</sup>                                     | 5...125 µm <sup>123</sup>                                      | 5...125 µm <sup>123</sup>                                     | 5...125 µm <sup>123</sup>                                       | 5...125 µm <sup>123</sup>                                      | 5...125 µm <sup>123</sup>                                       | 5...125 µm <sup>123</sup>                                      |
| Precision very high            | 4...84 µm <sup>123</sup>                                       | 4...84 µm <sup>123</sup>                                      | 4...84 µm <sup>123</sup>                                       | 4...84 µm <sup>123</sup>                                      | 4...84 µm <sup>123</sup>  | 4...84 µm <sup>123</sup>                                       | 4...84 µm <sup>123</sup>  | 4...84 µm <sup>123</sup>                                       |
| Precision highest              | 3...63 µm <sup>123</sup>                                       | 3...63 µm <sup>123</sup>                                      | 3...63 µm <sup>123</sup>                                       | 3...63 µm <sup>123</sup>                                      | 3...63 µm <sup>123</sup>  | 3...63 µm <sup>123</sup>                                       | 3...63 µm <sup>123</sup>  | 3...63 µm <sup>123</sup>                                       |
| Spatial repeatability          | 650 µm   | 650 µm  | 650 µm   | 650 µm  | 650 µm  | 650 µm   | 650 µm  | 650 µm   |
| Repeat accuracy in time        |  |   |  |   |   |  |   |  |
| Without filter                 | 3...125 µm <sup>12</sup>                                       |   | 3...125 µm <sup>12</sup>                                       |   | 3...125 µm <sup>12</sup>  |  | 3...125 µm <sup>12</sup>  |  |
| Precision high                 | 2...63 µm <sup>123</sup>                                       |   | 2...63 µm <sup>123</sup>                                       |   | 2...63 µm <sup>123</sup>  |  | 2...63 µm <sup>123</sup>  |  |
| Precision very high            | 1...42 µm <sup>123</sup>                                       |   | 1...42 µm <sup>123</sup>                                       |   | 1...42 µm <sup>123</sup>  |  | 1...42 µm <sup>123</sup>  |  |
| Precision highest              | 1...32 µm <sup>123</sup>                                       |   | 1...32 µm <sup>123</sup>                                       |   | 1...32 µm <sup>123</sup>  |  | 1...32 µm <sup>123</sup>  |  |
| Linearity error                | ± 1700 µm <sup>12</sup>  |   | ± 1700 µm <sup>12</sup>  |   | ± 1700 µm <sup>12</sup>   |  | ± 1700 µm <sup>12</sup>   |  |
| Linearity deviation in % of Mr | ± 0.19% <sup>12</sup>  |   | ± 0.19% <sup>12</sup>  |   | ± 0.19% <sup>12</sup>   |  | ± 0.19% <sup>12</sup>   |  |
| Temperature drift              | ± 0.065% Sde/K <sup>12</sup>                                   |   | ± 0.065% Sde/K <sup>12</sup>                                   |   | ± 0.065% Sde/K <sup>12</sup>                                    |  | ± 0.065% Sde/K <sup>12</sup>                                    |  |
| PRECISION filter values:       | Median Average   |   | Median Average   |   | Median Average  |  | Median Average  |  |
| Standard                       | Off Off  |   | Off Off  |   | Off Off   |  | Off Off   |  |
| High                           | 9 Off  |   | 9 Off  |   | 9 Off   |  | 9 Off   |  |
| Very high                      | 9 16   |   | 9 16   |   | 9 16  |  | 9 16  |  |
| Highest                        | 9 128  |   | 9 128  |   | 9 128   |  | 9 128   |  |

<sup>1</sup> Measurements with standard Baumer measuring equipment and objects dependent on measuring range Sd

<sup>2</sup> Measurement on 90% reflectivity (white)

<sup>3</sup> Measurement with filtering

|  |                         |                         |                         |                         |
|--|-------------------------|-------------------------|-------------------------|-------------------------|
| Hysteresis digital output              | Adjustable in mm        | Adjustable in mm        | Adjustable in mm        | Adjustable in mm        |
| Minimum window size for digital output | 1 mm                    | 1 mm                    | 1 mm                    | 1 mm                    |
| Minimum window size for analog output  | 1 mm                    | 1 mm                    | 1 mm                    | 1 mm                    |
| Output indicator                       | Yellow LED / red LED    | Yellow LED / red LED    | Yellow LED / red LED    | Yellow LED / red LED    |
| Switch-on delay                        | <1200 ms                | <1200 ms                | <1200 ms                | <1200 ms                |
| Light source                           | Red laser diode, pulsed | Red laser diode, pulsed | Red laser diode, pulsed | Red laser diode, pulsed |
| Setting                                | Touch display, RS-485   | Touch display, RS-485   | Touch display, RS-485   | Touch display, RS-485   |

| Electrical data                    | 11199108<br>Laser class 2<br>Laser point<br>Focal dist. 500 mm | 11199109<br>Laser class 2<br>Laser line<br>Focal dist. 500 mm | 11200091<br>Laser class 2<br>Laser point<br>Focal dist. 700 mm | 11200095<br>Laser class 2<br>Laser line<br>Focal dist. 700 mm | 11195787<br>Laser class 1<br>Laser point<br>Focal dist. 1000 mm | 11195788<br>Laser class 1<br>Laser line<br>Focal dist. 1000 mm | 11199089<br>Laser class 2<br>Laser point<br>Focal dist. 1000 mm | 11199100<br>Laser class 2<br>Laser line<br>Focal dist. 1000 mm |
|------------------------------------|--|---|--|---|---|--|---|--|
| Voltage supply range +Vs           | 15 ... 28 VDC  |   | 15 ... 28 VDC  |   | 15 ... 28 VDC   |  | 15 ... 28 VDC   |  |
| Max. supply current (without load) | 120 mA   |   | 120 mA   |   | 120 mA  |  | 120 mA  |  |
| Output circuit                     | Analog and RS-485  |   | Analog and RS-485  |   | Analog and RS-485   |  | Analog and RS-485   |  |
| Output signal                      | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                        |   | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                        |   | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                         |  | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                         |  |
| Switching output                   | Push-pull  |   | Push-pull  |   | Push-pull   |  | Push-pull   |  |
| Output function                    | Out 1 / alarm  |   | Out 1 / alarm  |   | Out 1 / alarm   |  | Out 1 / alarm   |  |
| Output current                     | < 100 mA   |   | < 100 mA   |   | < 100 mA  |  | < 100 mA  |  |
| Baud rate                          | Adjustable   |   | Adjustable   |   | Adjustable  |  | Adjustable  |  |
| Reverse polarity protection        | Yes, Vs to GND   |   | Yes, Vs to GND   |   | Yes, Vs to GND  |  | Yes, Vs to GND  |  |
| Short circuit protection           | Yes  |   | Yes  |   | Yes   |  | Yes   |  |

| Mechanical data         | 11199108<br>Laser class 2<br>Laser point<br>Focal dist. 500 mm | 11199109<br>Laser class 2<br>Laser line<br>Focal dist. 500 mm | 11200091<br>Laser class 2<br>Laser point<br>Focal dist. 700 mm | 11200095<br>Laser class 2<br>Laser line<br>Focal dist. 700 mm | 11195787<br>Laser class 1<br>Laser point<br>Focal dist. 1000 mm | 11195788<br>Laser class 1<br>Laser line<br>Focal dist. 1000 mm | 11199089<br>Laser class 2<br>Laser point<br>Focal dist. 1000 mm | 11199100<br>Laser class 2<br>Laser line<br>Focal dist. 1000 mm |
|-------------------------|--|---|--|---|---|--|---|--|
| Width / Height / Length | 26 / 74 / 55 mm  |   | 26 / 74 / 55 mm  |   | 26 / 74 / 55 mm   |  | 26 / 74 / 55 mm   |  |
| Design                  | Rectangular, front view  |   | Rectangular, front view  |   | Rectangular, front view   |  | Rectangular, front view   |  |
| Housing material        | Aluminum   |   | Aluminum   |   | Aluminum  |  | Aluminum  |  |
| Front optic             | Glass  |   | Glass  |   | Glass   |  | Glass   |  |
| Connection method       | Plug M12 8-pole  |   | Plug M12 8-pole  |   | Plug M12 8-pole   |  | Plug M12 8-pole   |  |
| Weight                  | 130 g  |   | 130 g  |   | 130 g   |  | 130 g   |  |



| Ambient conditions                                 | 11199108<br>Laser class 2<br>Laser point<br>Focal dist. 500 mm   | 11199109<br>Laser class 2<br>Laser line<br>Focal dist. 500 mm | 11200091<br>Laser class 2<br>Laser point<br>Focal dist. 700 mm   | 11200095<br>Laser class 2<br>Laser line<br>Focal dist. 700 mm | 11195787<br>Laser class 1<br>Laser point<br>Focal dist. 1000 mm  | 11195788<br>Laser class 1<br>Laser line<br>Focal dist. 1000 mm | 11199089<br>Laser class 2<br>Laser point<br>Focal dist. 1000 mm  | 11199100<br>Laser class 2<br>Laser line<br>Focal dist. 1000 mm |
|--|--|---|--|---|--|--|--|--|
| Ambient light immunity                             | < 100 kLux   | < 100 kLux  | < 100 kLux   | < 100 kLux  | < 100 kLux   | < 100 kLux   | < 100 kLux   | < 100 kLux   |
| Operating temperature                              | -10 ... +50 °C   |   | -10 ... +50 °C   |   | -10 ... +50 °C   |  | -10 ... +50 °C   |  |
| Storage temperature                                | -20 ... +60 °C   |   | -20 ... +60 °C   |   | -20 ... +60 °C   |  | -20 ... +60 °C   |  |
| Heating period                                     | 20 min.  |   | 20 min.  |   | 20 min.  |  | 20 min.  |  |
| protection class                                   | IP 67  |   | IP 67  |   | IP 67  |  | IP 67  |  |
| Vibration resistance (sinusoidal)                  | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |   | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |  | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |  |
| Shock resistance (semi-sinusoidal)                 | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |   | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |  | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |  |
| Optical properties                                 | 11199108<br>Laser class 2<br>Laser point<br>Focal dist. 500 mm   | 11199109<br>Laser class 2<br>Laser line<br>Focal dist. 500 mm | 11200091<br>Laser class 2<br>Laser point<br>Focal dist. 700 mm   | 11200095<br>Laser class 2<br>Laser line<br>Focal dist. 700 mm | 11195787<br>Laser class 1<br>Laser point<br>Focal dist. 1000 mm  | 11195788<br>Laser class 1<br>Laser line<br>Focal dist. 1000 mm | 11199089<br>Laser class 2<br>Laser point<br>Focal dist. 1000 mm  | 11199100<br>Laser class 2<br>Laser line<br>Focal dist. 1000 mm |
| Light source                                       | AlGaInP laser diode  |   | AlGaInP laser diode  |   | AlGaInP laser diode  |  | AlGaInP laser diode  |  |
| Wave length  | 660 nm   |   | 660 nm   |   | 660 nm   |  | 660 nm   |  |
| Operating mode                                     | pulsed   |   | pulsed   |   | pulsed   |  | pulsed   |  |
| Pulse duration                                     | 4 µs...2.5 ms  |   | 4 µs...2 ms  |   | 4 µs...2 ms  |  | 4 µs...2 ms  |  |
| Pulse period                                       | 0.4...5 ms   |   | 0.4...7 ms   |   | 0.4...8 ms   |  | 0.4...7 ms   |  |
| Total emitted pulse power                          | 1.01 mW  | 1.9 mW  | 2.1 mW   | 1.9 mW  | 1.01 mW  | 1.9 mW   | 2.1 mW   | 1.9 mW   |
| Beam shape   | Point laser  | Short line  | Point laser  | Short line  | Point laser  | Short line   | Point laser  | Short line   |
| Receiver position                                  | L1<br>L2   |   | 42 mm<br>57 mm   |   | 42 mm<br>57 mm   |  | 42 mm<br>57 mm   |  |
| Focal distance df                                  | 500 mm   | 500 mm  | 700 mm   | 700 mm  | 1000 mm  | 1000 mm  | 1000 mm  | 1000 mm  |
| Nominal ocular hazard distance (NOHD) <sup>1</sup> | N/A  | N/A   | inf  | 7.0 m   | inf  | 7.0 m  | inf  | 7.0 m  |
| Laser classification (as per IEC 60825-1/2014)     | Laser class 2  |   | Laser class 2  |   | Laser class 1  |  | Laser class 2  |  |

<sup>1</sup> Outside the "Nominal ocular hazard distance", the radiation exposure is below the limit value of laser class 1

## 7.2 Measuring range types 150...1500 mm

| General data                   | 11111994<br>Laser class 1<br>Laser point<br>Focal dist. 1500<br>mm | 11112012<br>Laser class 1<br>Laser line<br>Focal dist. 1500<br>mm | 11112013<br>Laser class 2<br>Laser point<br>Focal dist. 1500<br>mm | 11112015<br>Laser class 2<br>Laser line<br>Focal dist. 1500<br>mm |
|--------------------------------|--|---|--|---|
| Beam shape                     | Laser point  | Laser line  | Laser point  | Laser line  |
| Laser class                    | 1  |   | 2  |   |
| Function                       | Distance   |   | Distance   |   |
| Measuring range (distance)     | 150...1500 mm  |   | 150...1500 mm  |   |
| Start of measuring range Sdc   | 150 mm   |   | 150 mm   |   |
| End of measuring range Sde     | 1500 mm  |   | 1500 mm  |   |
| Blind region                   | 0...150 mm   |   | 0...150 mm   |   |
| Measuring range Mr             | 1350 mm  |   | 1350 mm  |   |
| Sweet spot                     | 1500 mm  |   | 1500 mm  |   |
| Focal range                    | 1000...1500 mm   |   | 1000...1500 mm   |   |
| Measuring frequency            | 2500 Hz <sup>12</sup>  |   | 2500 Hz <sup>12</sup>  |   |
| Response time                  |  |   |  |   |
| - Single shot                  | 0.8 ms <sup>12</sup>   |   | 0.8 ms <sup>12</sup>   |   |
| - Continuous                   | 1.2 ms <sup>12</sup>   |   | 1.2 ms <sup>12</sup>   |   |
| Resolution                     |  |   |  |   |
| Without filter                 | 50...500 µm <sup>12</sup>  | 50...500 µm <sup>12</sup>   | 50...500 µm <sup>12</sup>  | 50...500 µm <sup>12</sup>   |
| Precision high                 | 25...225 µm <sup>123</sup>   | 15...250 µm <sup>123</sup>  | 25...225 µm <sup>123</sup>   | 15...250 µm <sup>123</sup>  |
| Precision very high            | 17...150 µm <sup>123</sup>   | 10...167 µm <sup>123</sup>  | 17...150 µm <sup>123</sup>   | 10...167 µm <sup>123</sup>  |
| Precision highest              | 13...113 µm <sup>123</sup>   | 8...125 µm <sup>123</sup>   | 13...113 µm <sup>123</sup>   | 8...125 µm <sup>123</sup>   |
| Spatial repeatability          | 1.5 mm   | 1.5 mm  | 1.5 mm   | 1.5 mm  |
| Repeat accuracy in time        |  |   |  |   |
| Without filter                 | 10...250 µm <sup>12</sup>  |   | 10...250 µm <sup>12</sup>  |   |
| Precision high                 | 5...125 µm <sup>123</sup>  |   | 5...125 µm <sup>123</sup>  |   |
| Precision very high            | 4...84 µm <sup>123</sup>   |   | 4...84 µm <sup>123</sup>   |   |
| Precision highest              | 3...63 µm <sup>123</sup>   |   | 3...63 µm <sup>123</sup>   |   |
| Linearity error                | ± 4320 µm <sup>12</sup>  |   | ± 4320 µm <sup>12</sup>  |   |
| Linearity deviation in % of Mr | ± 0.32% <sup>12</sup>  |   | ± 0.32% <sup>12</sup>  |   |
| Temperature drift              | ± 0.1% Sde/K <sup>12</sup>   |   | ± 0.1% Sde/K <sup>12</sup>   |   |
| PRECISION filter values:       | Median   | Average   | Median   | Average   |
| Standard                       | Off  | Off   | Off  | Off   |
| High                           | 9  | Off   | 9  | Off   |
| Very high                      | 9  | 16  | 9  | 16  |
| Highest                        | 9  | 128   | 9  | 128   |

<sup>1</sup> Measurements with standard Baumer measuring equipment and objects dependent on measuring range Sd

<sup>2</sup> Measurement on 90% reflectivity (white)

<sup>3</sup> Measurement with filtering

|  |                         |                         |
|--|-------------------------|-------------------------|
| Hysteresis digital output              | Adjustable in mm        | Adjustable in mm        |
| Minimum window size for digital output | 1.5 mm                  | 1.5 mm                  |
| Minimum window size for analog output  | 1 mm                    | 1 mm                    |
| Output indicator                       | Yellow LED / red LED    | Yellow LED / red LED    |
| Switch-on delay                        | <1200 ms                | <1200 ms                |
| Light source                           | Red laser diode, pulsed | Red laser diode, pulsed |
| Setting                                | Touch display, RS-485   | Touch display, RS-485   |

| Electrical data                    | 11111994<br>Laser class 1<br>Laser point<br>Focal dist. 1500 mm | 11112012<br>Laser class 1<br>Laser line<br>Focal dist. 1500 mm | 11112013<br>Laser class 2<br>Laser point<br>Focal dist. 1500 mm | 11112015<br>Laser class 2<br>Laser line<br>Focal dist. 1500 mm |
|------------------------------------|---|--|---|--|
| Voltage supply range +Vs           | 15 ... 28 VDC   |  | 15 ... 28 VDC   |  |
| Max. supply current (without load) | 120 mA  |  | 120 mA  |  |
| Output circuit                     | Analog and RS-485   |  | Analog and RS-485   |  |
| Output signal                      | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                         |  | 4 ... 20 mA / 0 ... 10 VDC (adjustable)                         |  |
| Switching output                   | Push-pull   |  | Push-pull   |  |
| Output function                    | Out 1 / alarm   |  | Out 1 / alarm   |  |
| Output current                     | < 100 mA  |  | < 100 mA  |  |
| Baud rate                          | Adjustable  |  | Adjustable  |  |
| Reverse polarity protection        | Yes, Vs to GND  |  | Yes, Vs to GND  |  |
| Short circuit protection           | Yes   |  | Yes   |  |

| Mechanical data         | 11111994<br>Laser class 1<br>Laser point<br>Focal dist. 1500 mm | 11112012<br>Laser class 1<br>Laser line<br>Focal dist. 1500 mm | 11112013<br>Laser class 2<br>Laser point<br>Focal dist. 1500 mm | 11112015<br>Laser class 2<br>Laser line<br>Focal dist. 1500 mm |
|-------------------------|---|--|---|--|
| Width / Height / Length | 26 / 74 / 55 mm   |  | 26 / 74 / 55 mm   |  |
| Design                  | Rectangular, front view   |  | Rectangular, front view   |  |
| Housing material        | Aluminum  |  | Aluminum  |  |
| Front optic             | Glass   |  | Glass   |  |
| Connection method       | Plug M12 8-pole   |  | Plug M12 8-pole   |  |
| Weight                  | 130 g   |  | 130 g   |  |

| Ambient conditions | 11111994<br>Laser class 1<br>Laser point<br>Focal dist. 1500 mm | 11112012<br>Laser class 1<br>Laser line<br>Focal dist. 1500 mm | 11112013<br>Laser class 2<br>Laser point<br>Focal dist. 1500 mm | 11112015<br>Laser class 2<br>Laser line<br>Focal dist. 1500 mm |
|--------------------|---|--|---|--|
|--------------------|---|--|---|--|

|                                    |  |           |  |           |
|------------------------------------|--|-----------|--|-----------|
| Ambient light immunity             | < 35 kLux  | < 35 kLux | < 35 kLux  | < 35 kLux |
| Operating temperature              | -10 ... +50 °C   |           | -10 ... +50 °C   |           |
| Storage temperature                | -20 ... +60 °C   |           |  |           |
| Heating period                     | 20 min.  |           | 20 min.  |           |
| protection class                   | IP 67  |           | IP 67  |           |
| Vibration resistance (sinusoidal)  | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |           | <b>IEC 60068-2-6:2008</b><br>1 mm p-p at f = 10 - 55 Hz, duration 5 min per axis<br>30 min endurance at f = 55 Hz per axis |           |
| Shock resistance (semi-sinusoidal) | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |           | <b>IEC 60068-2-27:2009</b><br>30 g / 11 ms, 6 jolts per axis and direction   |           |

| Optical properties                                 | 11111994<br>Laser class 1<br>Laser point<br>Focal dist. 1500 mm | 11112012<br>Laser class 1<br>Laser line<br>Focal dist. 1500 mm | 11112013<br>Laser class 2<br>Laser point<br>Focal dist. 1500 mm | 11112015<br>Laser class 2<br>Laser line<br>Focal dist. 1500 mm |
|--|---|--|---|--|
| Light source                                       | AlGaInP laser diode   |  | AlGaInP laser diode   |  |
| Wave length  | 660 nm  |  | 660 nm  |  |
| Operating mode                                     | pulsed  |  | pulsed  |  |
| Pulse duration                                     | 4 µs...2.5 ms   |  | 4 µs...2.5 ms   |  |
| Pulse period                                       | 0.4...19 ms   | 0.4...17 ms  | 0.4...19 ms   | 0.4...17 ms  |
| Total emitted pulse power                          | 2.1 mW  | 1.9 mW   | 2.1 mW  | 1.9 mW   |
| Beam shape   | Point laser   | Short line   | Point laser   | Short line   |
| Receiver position L1                               | 42 mm   |  | 42 mm   |  |
| Receiver position L2                               | 57 mm   |  | 57 mm   |  |
| Focal distance df                                  | 1500 mm   | 1500 mm  | 1500 mm   | 1500 mm  |
| Nominal ocular hazard distance (NOHD) <sup>1</sup> | N/A   | N/A  | inf   | 7.0 m  |
| Laser classification (as per IEC 60825-1/2014)     | Laser class 1   |  | Laser class 2   |  |

<sup>1</sup> Outside the "Nominal ocular hazard distance", the radiation exposure is below the limit value of laser class 1

## 8 Revision history

|            |     |  |
|------------|-----|--|
| 12/8/2017  | tof | Manual released in version 1.0   |
| 01/11/2018 | tof | Structural changes. Complete revision  |
| 05/30/2018 | fof | New focal distance articles integrated, data sheet optimizations. Chapter "Focal distance" |



Baumer Group  
International Sales  
P.O. Box · Hummelstrasse 17 · CH-8501 Frauenfeld  
Phone +41 (0)52 728 1122 · Fax +41 (0)52 728 1144  
sales@baumer.com · www.baumer.com